


EP100

EPIC SBC with AMD G-Series APU, AMD A50M FCH, Dual DisplayPort/VGA/LVDS, Dual LANs and Audio

Features

- AMD G-Series APU T40R (1.0 GHz)/ T56N (1.65 GHz)
- 1 DDR3 DDR3-1066/1333 SO-DIMM, up to 4GB
- 6 USB 2.0 ports
- 4 COM ports
- DirectX 11 supported



Core System



CPU	AMD G-Series APU T40R 1.0 GHz single core or T56N 1.65 GHz dual core onboard
System Memory	1 x 204-pin DDR3-1066/1333 SO-DIMM, up to 4GB
Chipset	AMD A50M FCH
BIOS	AMI UEFI BIOS
SSD	1 x CFast™
Watchdog Timer	255 levels, 1~255 sec.
Expansion Interface	1 x PCI Express Mini Card 1 x PCI Express Mini Card with SIM slot
Battery	Lithium 3V/220mAH
Power Input	2 x 2-pin connector +12V DC-in only AT Auto Power ON function supported
Power Requirements	AMD G-Series APU T56N @1.65 GHz, 1GB DDR3 Max. RMS: +12V @ 1.74A AMD G-Series APU T40R @ 1.0 GHz, 1GB DDR3 Max. RMS: +12V @ 1.24A
Size	165 x 115 mm
Board Thickness	1.6 mm
Operating Temperature	0°C ~ +60°C (32°F ~ 140°F), operation
Relative Humidity	10% ~ 95% relative humidity, non-condensing

I/O

MIO	1 x RS-232/422/485 (COM 1; +5V/+12V powered) 3 x RS-232 (COM 2/3/4; +5V/+12V powered)
SATA	2 x SATA-600
Hardware Monitoring	Detect CPU/system temperature, voltage and fan speed
Ethernet	2 ports as 10/100/1000 Mbps supports Wake-on-LAN, RPL/PXE Boot ROM with Realtek RTL8111E
Audio	HD Codec audio as Mic-in/Line-in/Line-out/Speaker-out with Realtek ALC662
USB	6 x USB 2.0
SMBus	System Management Bus for advanced monitoring/control
Digital I/O	8 channels IN/OUT programmable

Display

Chipset	AMD G-Series APU integrated graphics engine T56N - Radeon™ HD6320 T40R - Radeon™ HD6250
Memory Size	Up to 2GB in 4GB DDR3 module
Display Interface	1 x VGA, 2 x DisplayPort or 1 x VGA, 1 x DisplayPort, 1 x LVDS; 18/24-bit single/dual channel



▲ Slim I/O

Packing List

Standard

Quick installation guide, user's manual/utility CD, cable

Cable

Part Number	Description	Qty
59382620000E	1 x COM w/ bracket, P=2.0 mm, L=300 mm	1
59384500100E	Audio cable w/ bracket, P=2.0 mm, L=450 mm	1
59382631000E	2 x USB 2.0 wafer cable w/ bracket, 180 mm	1

Optional

59380000300E	2 x COM w/ bracket, P=1.27 x 2.54, L=300 mm
59070213000E	DisplayPort to VGA cable, L=100 mm
59040131000E	DisplayPort to DVI cable, L=220 mm
59050203000E	DisplayPort to HDMI cable, L=185 mm
59091501000E	DisplayPort to DisplayPort cable, L=1500 mm

Ordering Information

Standard

EP100VPGGA-T56N w/ slim I/O (P/N: E38B100100)	EPIC SBC with AMD G-Series APU T56N 1.65 GHz, A50M FCH, VGA/Dual DisplayPort, 2 GbE LANs and audio
EP100VLGGA-T40R w/ rich I/O (fanless) (P/N: E38B100102)	EPIC SBC with AMD G-Series APU T40R 1.0 GHz, A50M FCH, VGA/DisplayPort/LVDS, 2 GbE LANs and audio

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Axiomtek:](#)

[EP100VLGGA-T40R-RC w/rich I/O](#) [EP100VPGGA-T56N-RC w/slim I/O](#)