


OPS883-H


Open Pluggable Specification (OPS) Digital Signage Player with 4th Gen Intel® Core™ i7/i5/i3 & Celeron® Processor, Intel® H81 and TPM 1.2

Features

- Intel® Open Pluggable Specification (OPS) compliance
- LGA1150 socket 4th gen Intel® Core™ i7/i5/i3 & Celeron® processor (Haswell Refresh)
- DDR3-1600 SO-DIMM 1600, up to 8GB
- 1 PCIe Mini Card slot
- Supports TPM 1.2
- Easy Installation and maintenance
- HDMI for 2nd display with 4K resolution



- | | | |
|---------------------|---------------------|----------------------|
| 1. JAE TX-25 | 6. Power Switch | 11. 2 x USB 2.0 |
| 2. Optional Antenna | 7. Reset | 12. 1 x USB 3.0 |
| 3. RS-232 | 8. HDD indicator | 13. Optional Antenna |
| 4. Ethernet | 9. Audio (Line-out) | 14. 2.5" SATA HDD |
| 5. HDMI Output | 10. Audio (Mic-in) | |



Specifications

Main System	CPU	LGA1150 socket 4th generation Intel® Core™ i7/i5/i3 & Celeron® processor (Haswell Refresh)
	Chipset	Intel® H81
	System Memory	1 x 204 pin DDR3-1600 SO-DIMM, up to 8 GB
	Storage	1 x 2.5" SATA HDD tray
	Watchdog Timer	255 levels, 1-255 sec.
I/O	2 x USB 2.0	
	1 x USB 3.0	
	1 x 10/100/1000 Mbps Ethernet (Intel® i217LM)	
	1 x HDMI with 4K Resolution	
	1 x RS-232 (COM 2)	
	1 x Power on/off button	
	1 x Reset button	
	1 x Audio (Line-out)	
	1 x Audio (Mic-in)	
	1 x Displayport (via OPS JAE interconnector)	
	2 x USB 2.0 (via OPS JAE interconnector)	
	1 x USB 3.0 (via OPS JAE interconnector)	
	1 x Audio (Line-out, via OPS JAE interconnector)	
1 x UART (TX/RX, via OPS JAE interconnector) (COM 1)		
Indicator	1 x LED for system power on	
	1 x LED for HDD active	
WiFi	802.11 b/g/n (optional)	
Expansion Slot	1 x full-size PCIe Mini Card (USB+PCI Express Signal)	
Dimensions	200 mm (7.87") (W) x 119 mm (4.68") x 30 mm (1.18")	
Packing Dimension	270 mm (10.63") (W) x 197 mm (7.76") x 70 mm (2.76")	
Weight (net/gross)	1 kg (2.21lb)/ 1.5 kg (3.3 lb)	
Environmental	0°C ~ +45°C (+32°F ~ +113°F) (with airflow 1.2m/s)	

Packing

- 1 x Driver CD
- 1 x Thermal grease
- 2 x M2 x 5 screw
- 2 x M4 x 6 screw

Optional OS Installation

Windows® 7, Windows® 8.1, Windows®10

Ordering Information

Standard


OPS883-H OPS digital signage player with LGA1150 socket Intel® Core™ i7/i5/i3 & Celeron® processor

Optional

AX93167 OPS docking board with 4K solution

* Specifications and certifications may vary contingent on options.

Dimensions



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Axiomtek:](#)

[OPS883](#) [OPS883-H](#) [OPS883-H-i7](#) [OPS883-H-i7-NP\(PH\)](#) [OPS883-H-NP\(PH\)](#)