



DATE	REV	ECN	APP'D. BY
12/22/20	A0	RELEASED	ADB
-	-	-	-



PIN ASSIGNMENT



Notes:

- Cable:
 -USB 3.1 [34AWG(7/0.06TC)+EAM]*4P+32AWG(7/0.08TC)
 *2C+26AWG (7/0.16TC)*2C+32AWG(7/0.08TC)*4C+AB
 (16/10/0.08 85%TC)OD: 4.2MM
 -JACKET COLOR: BLACK.
 -CABLE MARKING: E515987 兎 AWM STYLE 2725 80°C 30V VW-1 RoHS C1
- Connector P1:
 USB C MALE 3.1, GOLD FLASH ON SHELL, WITH PCB, BLACK INSULATOR.
- Molded Boot: 45P PVC color Black
- DP M ABS SHELL Color: Black
- TRANSPARENT DUST COVER
- Connector P2:
 UTCDP-6FT(VIA) With PCB SHELL Gold Plated
- Electrical Test:
 100%Test(Open ,Short ,Wire Map)
 CONTACT RESISTANCE 3 OHM MAX
 INSULATION RESISTANCE: 10M OHM MIN
 HI-POT: 300V DC/10 ms
 RESOLUTION: 4K*2K@60Hz
- PACKAGING: EACH CABLE ASSEMBLY TO BE INDIVIDUALLY BAGGED

P/N	LENGTH
BC-DC003F	3 FT ±.79" [915 mm ±20 mm]
BC-DC006F	6 FT ±1.18" [1830 mm± 30mm]
BC-DC010F	10 FT ±1.97" [3050 MM± 50mm]

THIRD ANGLE PROJECTION		206 Van Vorst Street Jersey City, NJ 07302 +1 201 432 0463 http://www.belfuse.com	
DO NOT SCALE DRAWING DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE		TITLE: USB TYPE C 3.1 MALE TO DISPLAY PORT CABLE ASSEMBLY	
DIMENSIONS: INCHES [METRIC]		DRN BY: GL	DATE 12/18/20
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ±.005 [0.13] ANGLES ARE ± 1°		APPD BY: ADB	DATE 12/21/20
SHEET NO. 1 OF 1		DWG NO. CT999236	REV. A0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bel:

[BC-DC003F](#) [BC-DC006F](#) [BC-DC010F](#)