

Specification Sheet

Part Number: 553-50193

Flexible, flame retardant, heat shrinkable polyolefin tubing meets all military specification.

3:1 shrink ratio enables a wide range of wire sizes to be covered.

Standard colors - yellow, white and black.

Larger pack options result in less box changes.


Center slit and multiple slit versions reduce or eliminate hand cutting.

Nonslip printable liner allows additional marker data to be printed on the reverse side for records and placement instructions.

Use HellermannTyton's Durattach ribbon system for the highest print performance on the market.

Custom box opening allows markers to dispense directly into HellermannTyton thermal transfer printers.

Dispense markers faster and easier with waxed core dispenser.



ShrinkTrak Labels, 1-Sided, Unslit, .5" (12.7mm), PO-X, White, 1000/box

Article Number	553-50193
Type	HST12-4WH
Color	White (WH)
Quantity Per	reel

Product Description	HellermannTyton's ShrinkTrak™ heat shrinkable markers make it easy to mark wire, cable and other components. The military approved heat shrink tubing is flattened and assembled in a ladder style carrier system for easy printing using a thermal transfer printer. The ladder system creates a kit of markers that can be sorted, removed and applied in any order thus saving time, labor and speeding production.
Short Description	ShrinkTrak Labels, 1-Sided, Unslit, .5" (12.7mm), PO-X, White, 1000/box
Global Part Name	HST12-4WH-PO-X-WH
Variant	Thin-Wall
Width W (Imperial)	1.9
Width W (Metric)	48.26
Thickness T (Imperial)	.003
Thickness T (Metric)	.0762
Height H (Imperial)	0.42
Height H (Metric)	10.67
Width of Liner (Metric)	76.2
Width of Liner (Imperial)	3.0
Outside Diameter Max (Imperial)	0.5

Outside Diameter Max (Metric)	12.7
Wall Thickness WT (Imperial)	0.033
Wall Thickness WT (Metric)	0.84
Material	Polyolefin, cross-linked (PO-X)
Material Shortcut	PO-X
US MIL SPEC	SAE-AMS-DTL-23053/5 Class 1 and 3 SAE-AS81531 MIL-STD-202G Method 215K
Flammability	UL 224 VW-1
Halogen Free	No
Operating Temperature	-67°F to +275°F (-55°C to +135°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	SAE - AS81531 SAE - AMS - DTL-23053/5 Class 1 and 3 UL 224 125 °C 600V VW-1
Package Quantity (Imperial)	1000

Package Quantity (Metric)	1000
----------------------------------	------

Customs Number	3917320000
-----------------------	------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[553-50193](#)