

CT2176

Banana Plug Test Lead

4 mm Straight Banana Plug to Right-Angle Banana Plug Test...

Description

4 mm Straight Banana Plug to Right-Angle Banana Plug Test Lead. Most common lead for handheld DMMs. Right-Angle Banana Plug for the meter and straight banana plug for the probe or clip.

- Banana Contact: BeCu, Nickel Plt.
- Available in 6 standard lengths



Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com

Datasheet

All specifications apply to the unit after a temperature stabilization time of 20 minutes over an ambient temperature range of 25°C ± 5°C.

Specifications

IEC Rating	1,000 V CAT III / 600 V CAT IV
Current, Max	12 A
Resistance, Max	15 milliohms
Jacket Material	Silicone
Conductor Area	0.75 mm ²
Wire Gauge	18 AWG
Stranding (# x dia.)	195 x 0.07 mm
Jacket OD	3.7 mm (0.146")
Temperature (degrees)	-20 to +80C
RoHS (2011/65/EU)	Compliant

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website: caltestelectronics.com

Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cal Test Electronics:

[CT2176-10-0](#) [CT2176-10-2](#) [CT2176-10-4](#) [CT2176-10-5](#) [CT2176-10-6](#) [CT2176-10-9](#) [CT2176-50-0](#) [CT2176-50-2](#)
[CT2176-50-4](#) [CT2176-50-5](#) [CT2176-50-6](#) [CT2176-50-9](#) [CT2176-25-0](#) [CT2176-25-2](#) [CT2176-25-4](#) [CT2176-25-5](#)
[CT2176-25-6](#) [CT2176-25-9](#) [CT2176-150-6](#) [CT2176-150-9](#) [CT2176-200-4](#) [CT2176-200-5](#) [CT2176-200-6](#) [CT2176-200-9](#) [CT2176-100-4](#) [CT2176-100-5](#) [CT2176-100-6](#) [CT2176-100-9](#) [CT2176-150-4](#) [CT2176-150-5](#)