


THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WRITTEN CONSENT OF CAL TEST ELECTRONICS, INC.

REVISIONS			
REV.	DESCRIPTIONS	DATE	APPROVED
—	CLASS A RELEASED (REF. DWG. P279900)	7/22/2020	

NOTES:

- SPECIFICATION:
 JACKET: SILICONE. MULTI-LAYER, 1ST LAYER WHITE; 2ND LAYER "COLOR" OD: 3.7 ± 0.2 (.146 ± .008)
 CONDUCTOR: BARE COPPER, STRANDING 195 x 0.07 mm = 0.75 mm², 18 AWG.
- RATING:
 VOLTAGE: 1,000 V CAT IV PER IEC 61010-031
 CURRENT: 12 A MAX.
 TEMPERATURE: -60° C TO +180° C.
- AVAILABLE IN 3 STANDARD LENGTHS AND 6 COLORS – SEE MODEL NUMBER BELOW.
- RoHS2 COMPLIANT.



MODEL NUMBER

CT2799A-#-XXX

LENGTH: 10 – 10 m PACKAGE
 50 – 50 m SPOOL
 100 – 100 m SPOOL

COLOR: 0 – BLACK
 2 – RED
 4 – YELLOW
 5 – GREEN
 6 – BLUE
 9 – WHITE

METRIC	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS TOLERANCES ARE: DECIMALS ANGLE .X ± 0.8 ± 2° .XX ± 0.25 DO NOT SCALE DRAWING	CONTRACT NO.		Cal Test Electronics 22820 Savi Ranch Parkway Yorba Linda, CA 92887-4610	
	MATERIAL	APPROVALS	DATE	TITLE	
THIRD ANGLE PROJECTION	FINISH	DRAWN WDH	7/22/2020	WIRE, TEST LEAD, SILICONE JACKET, 0.75 mm², 18 AWG, 12 A	
		CHECKED		SIZE A	CAGE CODE 43F45
		ENGR.		DWG. NO. P2799A0	REV. —
		DESIGN ACTIVITY		SCALE NONE	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cal Test Electronics:](#)

[CT4403](#)