



Picture may differ from original product.

### Contents

Device	Part number	Quantity	Calibration Option <sup>a</sup>
Gauge (including gauge block)	07W001-000	1	FC

a. See "Declaration of calibration options" for explanation.

### Mechanical specifications

Gauge block	0.00 mm
Gauge range	0.00 mm ± 0.5 mm
Scale gradation	1 µm
Limit of measurement error <sup>1, 2</sup>	≤ 10 µm
Typical measurement error <sup>1, 2</sup>	≤ 6 µm
Measuring force	1.5 N

<sup>1</sup> When zeroed with gauge block

<sup>2</sup> 0.12 mm recession to 0.04 mm protrusion

**Documentation**

This kit is delivered with

- **Calibration Certificate**  
Details see "Declaration of calibration options"
- **Operating Manual**

**Declaration of calibration options**

**Factory Calibration**

Standard delivery for this gauge includes a Factory Calibration. The Calibration Certificate issued reports individual mechanical calibration results, traceable to national / international standards.

**Accredited Calibration**

Not available.

*For further, more detailed information see application note AN001 on the Rosenberger homepage.*

**Calibration interval**

Recommendation 12 months

*For further, more detailed information please visit our homepage [www.rosenberger.com](http://www.rosenberger.com).*

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
Martin Moder	23.11.15	Roland Neuhauser	06.11.18	b00	18-0004	M.Ruf	06.11.18
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany <a href="http://www.rosenberger.de">www.rosenberger.de</a>					Tel. : +49 8684 18-0 Email : <a href="mailto:info@rosenberger.de">info@rosenberger.de</a>		Page 2 / 2

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rosenberger:](#)

[07GK001-010](#)