

Mini-ITX Series

NEW

VIA

VB7009

Flexible Mini-ITX board with advanced multimedia, I/O, and connectivity features

Features

- Compact 17cm x 17cm Mini-ITX form factor
- Choice of VIA Eden® X4, VIA C7®-D, and VIA C7® processors
- DX9 graphics with MPEG-2/WMV9/VC1/H.264 decoding acceleration
- Rich I/O and connectivity features
- Supports up to six onboard COM ports




Board Placement

PS2 Keyboard/Mouse

Parallel Port/COM/VGA

Gigabit Ethernet/USB

Audio Jacks



ATX Power Connector

VIA CPU

DDR3 DIMM

VIA VX900 Chipset


SATA

PCI


Specifications

Model Name	VB7009-12QCE	VB7009-16	VB7009-10E
Processor	1.2GHz VIA Eden® X4 (Fanless)	1.6GHz VIA C7®-D (With fan)	1.0GHz VIA C7® (Fanless)
Chipset	VIA VX900 Media System Processor		
BIOS	AMI BIOS, 8Mbit Flash memory		
System Memory	1 DDR3 1066 DIMM slot Up to 4GB memory size		
Storage	2 SATA connectors		
Graphics	Integrated VIA Chrome®9 HD DX9 3D/2D graphics with MPEG-2, WMV9, VC1 and H.264 video decoding acceleration		
LAN	2 VIA VT6130 PCIe Gigabit Ethernet controllers		
Audio	VIA VT1708S High Definition Audio Codec		
Super I/O	Fintek F81865F-I		
Expansion I/O	1 PCI slot		
Onboard I/O	2 SATA connectors 2 USB 2.0 pin headers for 4 ports 1 Dual-channel 18/24 bit LVDS panel connector 1 LVDS panel power selector (5V/3.3V) 1 LVDS inverter pin header 1 LVDS inverter power selector (5V/12V) 5 COM port pin headers 2 optional (powered with selectable 5V/12V) 1 LPC pin header 1 SMBus pin header 1 S/PDIF-out connector 1 Digital I/O pin header (4 GPI + 4 GPO) 1 Front audio pin header for Line-out, Mic-in 2 Smart Fan pin headers for CPU and system 1 ATX power connector 1 PCI slot		
Back Panel I/O	4 USB 2.0 ports 1 VGA port 1 COM port 1 Parallel port 2 Gigabit Ethernet ports 3 Audio jacks: Line-in, Line-out, and Mic-in 2 PS/2 keyboard/mouse ports		
Power Supply	ATX power connector		
Operating System	Windows 7, WES 7, Windows CE, Linux, POSReady 7		
System Monitoring & Management	AC power failure recovery, RTC timer to power on, Wake-on LAN, Wake-on keyboard, Wake-on mouse		
Operating Temperature	0°C ~ 60°C		
Operating Humidity	0% ~ 95% (non-condensing)		
Form Factor	Mini-ITX (17cm x 17cm, 6.7" x 6.7")		
Compliance	CE/FCC		

Back Panel I/O



Accessories



Ordering Information

Model Name	CPU Frequency	Description
VB7009-12QCE	VIA Eden® X4 @ 1.2GHz	Mini-ITX Board with 1.2GHz VIA Eden® X4 E-Series CPU with VGA, LVDS, 8 USB 2.0, 6 COM, 2 Gigabit Ethernet, 2 SATA, PCI, ATX connector
VB7009-16	VIA C7®-D @ 1.6GHz	Mini-ITX Board with 1.6GHz VIA C7®-D CPU with VGA, LVDS, 8 USB 2.0, 4 COM, 2 Gigabit Ethernet, 2 SATA, PCI, ATX connector
VB7009-10E	VIA C7® @ 1.0GHz	Mini-ITX Board with 1.0GHz VIA C7® CPU with VGA, LVDS, 8 USB 2.0, 4 COM, 2 Gigabit Ethernet, 2 SATA, PCI, ATX connector

Optional Accessories


I/O Expansion Cards

Part Number	Description
LPC-01	Expansion module for four COM ports
LPC-02	Expansion module for four COM ports (5V or 12V)
LPC-04	Expansion module for two or four COM ports (5V or 12V)
PWB-M120	120W DC-DC power board, voltage range from 12V~24V
EXT-PCI	One to two PCI riser card

Wireless Modules

Part Number	Description
EMIO-1533-00A2	VNT9271 IEEE 802.11 b/g/n USB Wi-Fi module with assembly kit

Block Diagram



Packing List

Items
SATA cable
I/O bracket

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[VIA Technologies:](#)

[VB7009-10E](#) [VB7009-16](#) [VB7009-12QCE](#)