




THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO CW INDUSTRIES INCORPORATED AND ITS AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN CW INDUSTRIES PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM CW INDUSTRIES INCORPORATED, SOUTHAMPTON, PENNSYLVANIA USA.

Rating	8A 125V, 4A 250V AC 10A 125V, 6A 250V AC  6A 250V ~		Mounting Hole		Circuit Diagram												
	Contact Resistance	50m ohm max.															
Insulation Resistance	DC 500V 100M ohm min.		<table><tr><th>Thickness</th><th>X</th><th>Y</th></tr><tr><td>0.75 - 1.25</td><td>19.2 - 0.1</td><td>13.1 + 0.1</td></tr><tr><td>1.25 - 2.00</td><td>19.4 - 0.1</td><td>13.1 + 0.1</td></tr><tr><td>2.00 - 3.00</td><td>19.8 - 0.1</td><td>13.1 + 0.1</td></tr></table>			Thickness	X	Y	0.75 - 1.25	19.2 - 0.1	13.1 + 0.1	1.25 - 2.00	19.4 - 0.1	13.1 + 0.1	2.00 - 3.00	19.8 - 0.1	13.1 + 0.1
Thickness	X	Y															
0.75 - 1.25	19.2 - 0.1	13.1 + 0.1															
1.25 - 2.00	19.4 - 0.1	13.1 + 0.1															
2.00 - 3.00	19.8 - 0.1	13.1 + 0.1															
Dielectric Strength	AC 1500V 1 minute																
Operating Temperature	-25° C ~ 85° C																

BASE COLOR: Black
BUTTON COLOR: Black / Red
PRINTING: White, Hot Stamping



RoHS Compliant

 INDUSTRIES Southampton, Pa. 18966 Tel 215.355.7080/www.cwind.com	Date Drawn: 12/17/09	Rev. 0	Unit: mm	Checked By: G. Guld
	Title: ROCKER SWITCH		CW P/N: GRB073A202BB	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CW Industries:](#)

[GRB073A202BB](#)