# CUSTOMER PRODUCT SPECIFICATION SHEET

RoHS Compliant

## CAB461RF: I-PEX MHF 4L LK PLUG + FRONT MOUNT SMA S/T BULKHEAD JACK WITH O-RING RATED TO IP67/68 + Ø1.37MM CABLE, 6GHz

#### SPECIFICATIONS:


- 1. I-PEX MHF 4L LK PLUG, P/N: 20632-001R-37. LOCK: 3615-000.
- 2. Ø1.37MM COAXIAL CABLE, COLOR: BLACK.
- 3. FRONT MOUNT SMA STRAIGHT BULKHEAD JACK WITH O-RING RATED TO IP67/68, P/N: RFCT-SMA087-F78.


#### ENVIRONMENTAL:


- A. BULKHEAD MOUNTED CONNECTOR (RFCT-SMA087-F78) RATED TO THE FOLLOWING SPECIFICATION:
  - i. IP6X DUST TIGHT NO PARTICLE INGRESS.
  - ii. IPX7 WATERPROOF FOR 30 MINUTES UP TO 1 METER UNDERWATER.
- iii. IPX8 WATERPROOF FOR 48 HOURS AT 1 METER UNDERWATER.

### NOTES:

- 1. THE ORIENTATION OF CONNECTORS ON DRAWING IS FOR REFERENCE ONLY, IF THE ORDER IS LEFT BLANK THE CONNECTOR WILL NOT HAVE FIXED ORIENTATION.
- 2. FIXED ORIENTATION IS SUGGESTED FOR CABLE LENGTH 25MM TO 100MM. PLEASE SPECIFY THE FIXED ORIENTATIONS FROM THE ORDER CODE (F1. F2. ETC)
- 3. CONTACT GCT IF THE ORIENTATION YOU REQUIRE IS NOT SHOWN.
- 4. WORKING FREQUENCY RANGE: DC-6GHz.
- 5. OPERATING TEMPERATURE: -40°C~+85°C.
- 6. IMPEDANCE: 50 OHM.
- 7. IT IS INTENDED THAT MOUNTING OF THIS CONNECTOR IS ACHIEVED USING THE NUT AND WASHER PROVIDED. PLEASE CONTACT GCT FOR ADVISE IF PLANNING TO USE A DIFFERENT METHOD OF MOUNTING.







IP Rated (RF Products



Drawing Number: CAB461RF

www.gct.co www.gradconn.com

Sheet 1 of 1

DATE & DRN
PSY04/71 - NYW RELEASE
8/01/74 - CC
D IP RATING VIEW
6/02/75 - CC

C THIS DO

(SEE NOTES 1, 2, 3 AND DIAGRAMS FOR MORE INFORMATION)

THIS DRAWING IS CONFIDENTIAL AND MUST NOT BE COPIED OR DISCLOSED WITHOUT WRITTEN CONSENT