CUSTOMER PRODUCT SPECIFICATION SHEET

RoHS Compliant

CAB466RF: I-PEX MHF 4L LK PLUG + RP FRONT MOUNT SMA S/T BULKHEAD JACK WITH 0-RING RATED TO IP67/68 + \$\phi 1.37MM CABLE. 6GHz

SPECIFICATIONS:


- 1. I-PEX MHF 4L LK PLUG. P/N: 20632-001R-37. LOCK: 3615-000.
- 2. \$\phi 1.37MM COAXIAL CABLE. COLOR: BLACK.
- 3. RP FRONT MOUNT SMA STRAIGHT BULKHEAD JACK WITH O-RING RATED TO IP67/68, P/N: RFCT-SMA088-F78.

ENVIRONMENTAL:

- A. BULKHEAD MOUNTED CONNECTOR (RFCT-SMA088-F78) RATED TO THE FOLLOWING SPECIFICATION:
 - i. IP6X DUST TIGHT NO PARTICLE INGRESS.
 - ii. IPX7 WATERPROOF FOR 30 MINUTES UP TO 1 METER UNDERWATER.
- iii. IPX8 WATERPROOF FOR 48 HOURS AT 1 METER UNDERWATER


NOTES:


- 1. THE ORIENTATION OF CONNECTORS ON DRAWING IS FOR REFERENCE ONLY, IF THE ORDER IS LEFT BLANK THE CONNECTOR WILL NOT HAVE FIXED ORIENTATION.
- 2. FIXED ORIENTATION IS SUGGESTED FOR CABLE LENGTH 25MM TO 100MM, PLEASE SPECIFY THE FIXED ORIENTATIONS FROM THE ORDER CODE (F1, F2, ETC)
- 3. CONTACT GCT IF THE ORIENTATION YOU REQUIRE IS NOT SHOWN.
- 4. WORKING FREQUENCY RANGE: DC-6GHz.
- 5. OPERATING TEMPERATURE: -40°C~+85°C.
- 6. IMPEDANCE: 50 OHM.
- 7. IT IS INTENDED THAT MOUNTING OF THIS CONNECTOR IS ACHIEVED USING THE NUT AND WASHER PROVIDED. PLEASE CONTACT GCT FOR ADVISE IF PLANNING TO USE A DIFFERENT METHOD OF MOUNTING.



USAGE PRECAUTIONS: CABLES USING 'MICRO' COAX ARE DELICATE:

- (i) HANDLE WITH CARE.
- (ii) DO NOT TWIST: APPLY EXCESSIVE FORCES OR SHARP BENDS TO THE CABLE. DO NOT FORCEFULLY DEFORM WIRES.
- (iii) CONSULT CONNECTOR MANUFACTURER'S DATASHEETS FOR DETAILED NOTES ON HANDLING INSTRUCTIONS.





BLANK = DOES NOT HAVE A FIXED ORIENTATION


F1 = MHF CONNECTION DOWN (L=50-200MM)

F2 = MHF CONNECTION UP (L=50-200MM)

F3 = MHF CONNECTION AND D FLAT SAME ORIENTATION (L=50-200MM)

F4 = MHF CONNECTION AND D FLAT OPPOSITE ORIENTATION (L=50-200MM)

(SEE NOTES 1, 2, 3 AND DIAGRAMS FOR MORE INFORMATION)



SMA DETAIL DRAWING

					_				
29/04/721 - NYW 28/01/724 - CC	-X	il view.	·\$	1d GCT 10go.	Scale:	NTS	THIRD ANGLE	Unstated .X .XX	Tolerance ±0.2 ±0.2
	VIEW	.c 1HF deta	τ		Drawn:	СС	→	1	±0.2 N/A
	¥ 5 5	7/"24 – (! I-PEX I	2/"25 - C T logo.		App'd:	XXX	Title CABLE ASSEMBLY		
	1 28/0 ADD IP	2 10/07 Remove	.3 16/0: Add GC		Date: 16	Feb. '25	Revision: 1.3	Unit: n	חת

IP Rated RF Products



CAB466RF

Drawing Number:

() THIS DRAWING IS CONFIDENTIAL AND MUST NOT BE COPIED OR DISCLOSED WITHOUT WRITTEN CONSENT

Sileer	01 1
Drawing (C	E and O f