



Important notes about Classic Panel Mount Indicator Catalog Pages

SCROLL DOWN TO VIEW CATALOG PAGE

This catalog page is out-of-print and is used with the understanding that the information shown could be out-of-date. In many cases, part numbers shown on this page are discontinued. Most notably, many “Complete Assembly” parts, which consist of a cap and a base, can no longer be ordered by the 14-digit ordering code. To obtain these parts, please order the cap and base part numbers separately. This process provides the components contained with the original “Complete Assembly” part number.

All Dialight Classic Panel Mount Indicators need a leading 3-digit numerical series. In some cases, this catalog will show a 2-digit series. In this case, please add a leading zero. For example, 81-0211-300 becomes 081-0211-300.

Part numbers listed on Dialight catalog pages designate parts with Red lenses. For ordering lens colors other than red, consult the chart below. In most cases, the color is dictated by the 7th digit. For example, 095-0932-003 for a green cap.

Lens Colors	
1 - Red	5 - White
2 - Green	6 - Light Yellow
3 - Yellow	7 - Clear
4 - Blue	


[Click here for a cross reference guide to assembly part numbers.](#)

[Click here to view Frequently Asked Questions concerning Panel Mount Indicators.](#)

SCROLL DOWN TO VIEW CATALOG PAGE

Miniature Incandescent Indicators

FOR MOUNTING IN 1/16" CLEARANCE HOLE
FOR 2 TO 120V OPERATION



T-3 1/4
MINIATURE
BAYONET BASE

See lamp ratings
on page K.

Recognized under the component
program of Underwriters'
Laboratories Inc.

75W., 125V.



How to designate the three digit part number suffix (-XXX)

FINISH	RESISTOR	HARDWARE
1 - White nickel	0 - None	1 - Brass
2 - Black nickel		3 - Water-tight, on the face of the panel.
3 - Polished chrome		
4 - Satin chrome		


NOTE: The part numbers given in this catalog indicate **standard** indicator lights. The table above provides the standard and optional designations for **Finish** and **Hardware** where appropriate. Example: 95-1310-0931-203 (black nickel finish with water-tight construction).

Part numbers listed in this catalog designate products with **RED** lens. For ordering lens colors other than red, consult chart on page 2D.

MATERIALS AND FINISHES

- **Mounting Bushing and Lens Holder:** Standard—Brass, polished chrome. Optional—White nickel, black nickel or satin chrome finish.
- **Mounting Nut:** Brass, white nickel finish.
- **Internal-tooth Lockwasher:** Phosphor bronze, white nickel finish.
- **Terminals: Solder** —Brass, hot tinned with elongated slot.
Screw—Brass, white nickel finish.
Quick Connect—Brass, tinned. Mate with standard female receptacles.

These assemblies also accommodate T-3 bulbs with miniature bayonet base, incandescent—in voltages from 6-120V. When lamps rated 2 watts or over are used, lens caps of high temperature plastic are required. Contact the factory for additional data and correct catalog number designations.



26-0410-1111-301
Screw-in lens cap

26 SERIES

BASE PART NUMBERS

WITH SCREW-IN LENS CAPS

	solder terminals	screw terminals	quick connect terminals
	26-0410-11-301	26-1310-11-301	26-5710-11-301
CAP PART NUMBERS	COMPLETE ASSEMBLY PART NUMBERS		
<p>STOVEPIPE</p>			
26-1131-300 transparent	26-0410-1131-301	26-1310-1131-301	26-5710-1131-301
26-1191-300 internal fluting	26-0410-1191-301	26-1310-1191-301	26-5710-1191-301
26-1111-300 back frosted	26-0410-1111-301	26-1310-1111-301	26-5710-1111-301

These assemblies should be specified when lamps rated over 2 watts are used.

Part numbers shown in gray are normally in inventory at your Dialight Distributor.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dialight:

[026-1113-300](#) [026-1114-300](#) [026-5710-11-300](#) [026-1111-300](#) [026-5710-11-301](#) [026-1114-203](#) [026-1113-203](#) [026-1112-300](#) [026-1112-203](#) [026-1111-200](#) [026-1111-203](#) [026-1116-300](#)