



## 4 Watt Flip-Plug Compact Adapter PSM04A Wall Plug Adapter Meets CEC and EISA Requirements



### Features

- No Load Power Consumption < 0.5 Watt
- Flip Plug Design
- EISA Compliant\*
- Low Leakage Current
- Low Cost

### Applications

- Wireless Communications
- Peripherals
- Portable Equipment
- PDA

### Safety Approvals

- cUL/UL

### Mechanical Characteristics

- Length: 69.4mm (2.73in)
- Width: 48mm (1.89in)
- Height: 25mm (0.98in)
- Weight: 145g (5.12oz)

### Output Specifications

Model	DC Output Voltage	Load		Ripple (1) P-P (max)	Regulation		Efficiency Level
		Min.	Max.		Line	Load	
PSM04A-050(STD)	5V	0A	0.75A	55mV	±5%		IV 115VAC III

Note: (1) Measured with by-pass capacitors 0.1uf/10uf at output connector terminal and oscilloscope set at 20Mhz.

\*EISA Compliant Level IV<sub>115VAC</sub>

Phihong is not responsible for any errors or changes. Content is subject to change without notice. Please consult the factory and visit [www.phihong.com](http://www.phihong.com) for the most up-to-date specifications.



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phihong:](#)

[PSM04A-050\(STD\)](#) [PSM04A-050\(STD\)-R](#)