

## 1U Rack-Mount Power Strip, 120V, 15A, 5-15P, 12 Outlets (Right-Angled Widely Spaced), 15-ft. Cord

MODEL NUMBER: RS-1215-RA



### Highlights

- Outlets placed at **right angle** to accommodate bulky transformers
- 12 widely spaced outlets (6 front / 6 rear)
- Designed for standard 19-in. racks (1U high)
- 15-ft. cord
- 15A circuit breaker

### Package Includes

- RS-1215-RA 1U Rackmount Power Strip
- Instruction manual with warranty information

### Description

Tripp Lite's RS-1215-RA Power Strip offers 15A capacity AC power distribution in a versatile multi-mount cabinet. Detachable mounting flanges are configurable for rackmount, wallmount and under-counter installation. Uses only 1 rack space (1U) when installed in any 19-in. rack meeting EIA standards. Unfiltered electrical pass-through makes RS-1215-RA ideal for distributing alternate waveform UPS or generator power in rack enclosures, network closets and more. Features 12 NEMA5-15R outlets (6 front/6 rear) placed at a right angle (with ground pin at bottom), 15-ft. AC power cord and lighted power switch with cover that prevents risk of accidental turn-off.

PLUG/OUTLETS: Input: NEMA 5-15P

Output: 12 x NEMA 5-15R (6 front/6 rear)

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA 5-15R wall receptacle)

FORMAT: 19-in. rackmount (uses 1 rack space/1U), wallmount, under-counter and more

### Features

- Versatile all-metal cabinet with detachable mounting flanges allows rackmount, wallmount, undercounter and other creative mounting options
- Uses one rack space (1U) in standard 19-in. rack ("zero U" mounting possible in many racks)
- Unfiltered electrical pass-through reliably distributes alternate waveform AC power from UPS or generator to supported equipment
- 12 x NEMA5-15R output receptacles (6 front/6 rear)
- 15-ft. AC cord with NEMA5-15P plug
- Right-angle outlet orientation with ground pin at the bottom
- Lighted power switch confirms power on/off status
- Snap-in switch guard prevents accidental turn off
- 15A electrical capacity with circuit breaker
- 120V AC, 50/60Hz electrical compatibility

## Specifications



<b>OUTPUT</b>	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(12) 5-15R
Circuit Breaker (amps)	15
Outlet Orientation	6 front-facing / 6 rear-facing, all with ground pin oriented to the bottom (when viewed in 1U rackmount configuration)
Right-Angle Outlets	Yes
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Connection Type	NEMA 5-15P
Input Cord Length (ft.)	15
Input Cord Length (m)	4.572
Voltage Compatibility (VAC)	120
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	Red illuminated - position switch controls power to all outlets
Locking Switch Cover	Transparent locking switch cover prevents accidental shutoff
<b>PHYSICAL</b>	
Unit Dimensions (hwd / in.)	1.75 x 17.5 x 4.5
Unit Dimensions (hwd / cm)	4.445 x 44.45 x 11.4
Unit Weight (lbs.)	4.6
Unit Weight (kg)	2.09
Material of Construction	Sheet metal
Receptacle Color	Black
Color (AC Line Cord)	Black
Form Factors Supported	1U rackmount, wall-mount and undercounter installation supported
Outlets Measurement (Center to Center)	Distance between Front outlets = 51.6mm; Distance between Rear outlets = 71.1mm
<b>SPECIAL FEATURES</b>	
TVSS Grounding	Back panel nut-and-bolt grounding lug
<b>CERTIFICATIONS</b>	
UL1363 (Power Tap)	UL1363 (UR status)



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

cUL / CSA (Canada)	cUL
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[RS1215-RA](#)