






Datasheet

DF & BDF Series

Available Distribution




LED



Recommend Applications



General Information



- Lens Material PMMA 8N
- Operating Temperature -40°C~+70°C
- UL Flammability HB @1.5mm
- UL RTI Elec 90°C @1.5mm
- Light Transmission Rate 400nm~900nm > 90%
- ☑ If necessary, Clean lenses with mild soap, water and soft cloth.
- ⚠ Never use any commercial cleaning solvents on lenses, like alcohol.
- ⚠ Please handle or install lenses with wearing gloves, skin oils may damage lens or its optical characteristic.


Dimensions

Part Number	Diameter	Height
LL01CR-DFxxL06	Ø11.8	6.5
LL01CR-DFxxL06-Mx-T		
LL01LU-DFxxL06-Ux-T	Ø13.5	7.35
LL01HS-DFxxL06-Mx-T		
LL01CR-QKxxL06-Mx-T		
LL01OS-BDF25L06 / LL01CR-BDFxxL06	Ø11.8	6.55
LL01CR-BDFxxL06-Ux-T		
LL01CR-CRxxL06-Mx-T		
LL01LU-BDFxxL06-Ux-T	Ø13.5	7.35
LL01OS-BDFxxL06-Ux-T		
LL01RP-BDFxxL06-Mx-T		


*All dimensions are in millimeters.

Packaging Details (SPQ)

DF Series



BDF Series



Accessories




- 7 Different Types of Holder
LL01CRCR10Hx
LL01LUCR10Hx
LL01CRMD25Hx
LL01CRQK25Hx
LL01CROR25Hx
LL01OSRD40Hx
LL01CRRP25Hx
- 3 Different Types of Tape
LL01A00XHNX
LL01A00XHVX
LL01A00XSXM

Mechanical Specification

*All dimensions are in millimeters.


Lens Dimension

LL01CR-DFxxL06



Lens Dimension

LL01OS-BDF25L06 / LL01CR-BDFxxL06 (40°/60°/30°x70°)




Assembly Instruction

Fixing Method

Part No LL01CR-DFxxL06 / LL01xx-BDFxxL06
LED CREE XQE-HD



Luminarie
Accessories




Assembly Instruction

Fixing Method

Part No LL01CR-DFxxL06
LED CREE XD16 / XHP35-HI / XPL-HI / XQD




Luminarie
Accessories



Holder Dimension

LL01CRCR10Hx



Assembly Instruction

Fixing Method


Part No LL01CR-DFxxL06-Mx-T (Lens:DF Series)
LL01CR-CRxxL06-Mx-T (Lens:BDF Series)
Holder LL01CRCR10Hx
Tape LL01A00XHNx



Tape




Luminarie
Accessories




*All dimensions are in millimeters.

LL01LUCR10Hx




Fixing Method

Part No	LL01LU-DFxxL06-Ux-T (Lens:DF Series) LL01LU-BDFxxL06-Ux-T (Lens:BDF Series)
Holder	LL01LUCR10Hx
Tape	LL01A00XHNX




LL01CRMD25H×




Fixing Method

Part No	LL01HS-DFxxL06-Mx-T (Lens:DF Series)
Holder	LL01CRMD25Hx
Tape	LL01A00XHVX




LL01CRQK25Hx



Fixing Method

Part No	LL01CR-QKxxL06-Mx-T (Lens:DF Series)
Holder	LL01CRQK25Hx
Tape	LL01A00XSMX




Mechanical Specification

*All dimensions are in millimeters.

Holder Dimension

LL01CROR25Hx



Assembly Instruction

Part No LL01CR-BDFxL06-Ux-T
Holder LL01CROR25Hx
Tape LL01A00XHNX


Fixing Method



Tape




Luminaire Accessories



Holder Dimension

LL01OSRD40Hx



Assembly Instruction

Part No LL01OS-BDFxL06-Ux-T
Holder LL01OSRD40Hx
Tape LL01A00XHNX


Fixing Method



Tape




Luminaire Accessories



Holder Dimension

LL01CRRP25Hx



Assembly Instruction

Part No LL01RP-BDFxL06-Mx-T
Holder LL01CRRP25Hx
Tape LL01A00XHNX


Fixing Method



Tape




Luminaire Accessories



















Photometric Distribution

DF Series




Photometric Distribution

DF Series

LED	 CREE XP-G2	 CREE XP-G3	 CREE XQD	 CREE XQE-HD	 EDISON 3030	 NICHIA NF2x757D
25°	-		-	-	-	-
40°	-		-	-	-	-
60°	-			-	-	-
80°		-				
100°		-		-		
30°×65°		-			-	-


Photometric Distribution

DF Series




Photometric Distribution

BDF Series




Photometric Distribution

BDF Series



Photometric Distribution

BDF Series




Photometric Distribution

BDF Series


LED




25°



40°



60°



80°

-

100°

-

30°×65°









-

30°×70°

-






Details by LED

DF Series

Part No	Holder	Tape	LED Package Size	LED
LL01CR-DFxxL06	-	-	1616 / 3030 / 3535	 CREE XD16  CREE XHP35-HI  CREE XPL-HI  CREE XQD  CREE XQE-HD  LED  LED
LL01CR-DFxxL06-Mx-T	 LL01CRCR10Hx	 LL01A00XHNX	3030 / 3535	 CREE XPE  CREE XPE2  CREE XPG  CREE XP-G2  CREE XP-G3  CREE XQE-HD  LED  OSRAM SQUARE
LL01LU-DFxxL06-Ux-T	 LL01LUCR10Hx	 LL01A00XHNX	3045	 LUMILEDS LUXEON A  LUMILEDS LUXEON REBEL  LUMILEDS LUXEON REBEL ES
LL01HS-DFxxL06-Mx-T	 LL01CRMD25Hx	 LL01A00XHVX	3535	 CREE XPE  NICHIA NF2x757D  NICHIA NV5xx19A  NICHIA NV5xx19B  SAMSUNG LH351B
LL01CR-QKxxL06-Mx-T	 LL01CRQK25Hx	 LL01A00XSMX	3535	 CREE XPE

Details by LED

BDF Series


Part No	Holder	Tape	LED Package Size	LED
LL01OS-BDF25L06 LL01CR-BDFxxL06 (40°/60°/30°×70°)	-	-	1414 / 1616 / 1620 1818 / 3535	       
LL01CR-BDFxxL06-Ux-T Lens assembled by using BDF 25°/40°/60°/30°×70° DF 80°/100°/30°×65°			2525	
LL01CR-CRxxL06-Mx-T Lens assembled by using BDF 25°/40°/60°/30°×70°			3535	
LL01LU-BDFxxL06-Ux-T Lens assembled by using BDF 25°/40°/60°/30°×70°			3045	
LL01OS-BDFxxL06-Ux-T Lens assembled by using BDF 25°/40°/60°/30°×70° DF 80°/100°/30°×65°			3030	      
LL01RP-BDFxxL06-Mx-T Lens assembled by using BDF 40°/60° DF 80°/100°			3535	

DF Series



LED	Part No	FWHM	cd / lm	IES
	LL01CR-DF25L06	-	-	-
	LL01CR-DF40L06	-	-	-
	LL01CR-DF60L06	32°	1.9	
	LL01CR-DF80L06	31°	2.0	
	LL01CR-DF100L06	44°	1.1	
	LL01CR-DF3065L06	-	-	-
	LL01CR-DF25L06	-	-	-
	LL01CR-DF40L06	-	-	-
	LL01CR-DF60L06	-	-	-
	LL01CR-DF80L06	37°	1.6	
	LL01CR-DF100L06	60°	0.8	
	LL01CR-DF3065L06	25°×36°	2.2	
	LL01CR-DF25L06	-	-	-
	LL01CR-DF40L06	-	-	-
	LL01CR-DF60L06	-	-	-
	LL01CR-DF80L06	35°	1.7	
	LL01CR-DF100L06	51°	1.0	
	LL01CR-DF3065L06	-	-	-
	LL01CR-DF25L06-M2-T	15°	7.8	
	LL01CR-DF40L06-M2-T	26°	3.0	
	LL01CR-DF60L06-M2-T	42°	1.4	
	LL01CR-DF80L06-M2-T	42°	1.2	
	LL01CR-DF100L06-M2-T	57°	0.7	
	LL01CR-DF3065L06-M2-T	20°×33°	3.1	
	LL01CR-QK25L06-M2-T	15°	7.8	
	LL01CR-QK40L06-M2-T	26°	3.0	
	LL01CR-QK60L06-M2-T	42°	1.4	
	LL01CR-QK80L06-M2-T	42°	1.2	
	LL01CR-QK100L06-M2-T	57°	0.7	
	LL01CR-QK3065L06-M2-T	20°×33°	3.1	
	LL01HS-DF25L06-M2-T	15°	7.8	
	LL01HS-DF40L06-M2-T	-	-	-
	LL01HS-DF60L06-M2-T	-	-	-
	LL01HS-DF80L06-M2-T	42°	1.2	
	LL01HS-DF100L06-M2-T	57°	0.7	
	LL01HS-DF3065L06-M2-T	20°×33°	3.1	
	LL01CR-DF25L06-M2-T	-	-	-
	LL01CR-DF40L06-M2-T	-	-	-
	LL01CR-DF60L06-M2-T	-	-	-
	LL01CR-DF80L06-M2-T	34°	1.8	
	LL01CR-DF100L06-M2-T	48°	1.1	
	LL01CR-DF3065L06-M2-T	-	-	-
	LL01CR-DF25L06-M2-T	22°	4.3	
	LL01CR-DF40L06-M2-T	32°	2.4	
	LL01CR-DF60L06-M2-T	44°	1.3	
	LL01CR-DF80L06-M2-T	50°	1.0	
	LL01CR-DF100L06-M2-T	59°	0.7	
	LL01CR-DF3065L06-M2-T	24°×35°	2.2	

LED	Part No	FWHM	cd / lm	IES
	LL01CR-DF25L06-M2-T	-	-	-
	LL01CR-DF40L06-M2-T	-	-	-
	LL01CR-DF60L06-M2-T	-	-	-
	LL01CR-DF80L06-M2-T	41°	1.4	
	LL01CR-DF100L06-M2-T	58°	0.8	
	LL01CR-DF3065L06-M2-T	24°×34°	2.3	
	LL01CR-DF25L06-M2-T	21°	3.3	
	LL01CR-DF40L06-M2-T	38°	1.4	
	LL01CR-DF60L06-M2-T	53°	0.9	
	LL01CR-DF80L06-M2-T	-	-	-
	LL01CR-DF100L06-M2-T	-	-	-
	LL01CR-DF3065L06-M2-T	-	-	-
	LL01CR-DF25L06	-	-	-
	LL01CR-DF40L06	-	-	-
	LL01CR-DF60L06	36°	1.5	
	LL01CR-DF80L06	52°	0.9	
	LL01CR-DF100L06	54°	0.8	
	LL01CR-DF3065L06	24°×34°	2.0	
	LL01CR-DF25L06	-	-	-
	LL01CR-DF40L06	-	-	-
	LL01CR-DF60L06	-	-	-
	LL01CR-DF80L06	35°	1.7	
	LL01CR-DF100L06	-	-	-
	LL01CR-DF3065L06	19°×32°	2.9	
	LL01CR-DF25L06-M2-T	-	-	-
	LL01CR-DF40L06-M2-T	-	-	-
	LL01CR-DF60L06-M2-T	-	-	-
	LL01CR-DF80L06-M2-T	35°	1.7	
	LL01CR-DF100L06-M2-T	-	-	-
	LL01CR-DF3065L06-M2-T	19°×32°	2.9	
	LL01CR-DF25L06	-	-	-
	LL01CR-DF40L06	-	-	-
	LL01CR-DF60L06	-	-	-
	LL01CR-DF80L06	32°	1.9	
	LL01CR-DF100L06	44°	1.2	
	LL01CR-DF3065L06	-	-	-
	LL01CR-DF25L06-M2-T	-	-	-
	LL01CR-DF40L06-M2-T	-	-	-
	LL01CR-DF60L06-M2-T	-	-	-
	LL01CR-DF80L06-M2-T	32°	1.9	
	LL01CR-DF100L06-M2-T	44°	1.2	
	LL01CR-DF3065L06-M2-T	-	-	-
	LL01HS-DF25L06-M2-T	-	-	-
	LL01HS-DF40L06-M2-T	-	-	-
	LL01HS-DF60L06-M2-T	-	-	-
	LL01HS-DF80L06-M2-T	32°	2.0	
	LL01HS-DF100L06-M2-T	43°	1.2	
	LL01HS-DF3065L06-M2-T	-	-	-

DF Series

LED	Part No	FWHM	cd / lm	IES
 NICHIA NVSxx19A	LL01HS-DF25L06-M2-T	-	-	-
	LL01HS-DF40L06-M2-T	-	-	-
	LL01HS-DF60L06-M2-T	-	-	-
	LL01HS-DF80L06-M2-T	51°	0.9	
	LL01HS-DF100L06-M2-T	55°	0.8	
	LL01HS-DF3065L06-M2-T	28°×38°	1.7	
 NICHIA NVSxx19B	LL01HS-DF25L06-M2-T	-	-	-
	LL01HS-DF40L06-M2-T	-	-	-
	LL01HS-DF60L06-M2-T	-	-	-
	LL01HS-DF80L06-M2-T	40°	1.4	
	LL01HS-DF100L06-M2-T	56°	0.8	
	LL01HS-DF3065L06-M2-T	28°×38°	1.7	
 OSRAM SQUARE	LL01CR-DF25L06-M2-T	-	-	-
	LL01CR-DF40L06-M2-T	-	-	-
	LL01CR-DF60L06-M2-T	-	-	-
	LL01CR-DF80L06-M2-T	41°	1.3	
	LL01CR-DF100L06-M2-T	59°	0.8	
 OSRAM SQUARE	LL01CR-DF3065L06-M2-T	-	-	-
	LL01HS-DF25L06-M2-T	22	3.8	
	LL01HS-DF40L06-M2-T	-	-	-
	LL01HS-DF60L06-M2-T	-	-	-
	LL01HS-DF80L06-M2-T	45°	1.2	
 SAMSUNG LH351B	LL01HS-DF100L06-M2-T	54°	0.9	
	LL01HS-DF3065L06-M2-T	-	-	-
	LL01LU-DF25L06-U2-T	21°	3.9	
	LL01LU-DF40L06-U2-T	34°	2.4	
	LL01LU-DF60L06-U2-T	45°	1.3	
 LUMILEDS LUXEON A	LL01LU-DF80L06-U2-T	37°	1.6	
	LL01LU-DF100L06-U2-T	54°	0.9	
	LL01LU-DF3065L06-U2-T	34°×22°	2.5	
	LL01LU-DF25L06-U2-T	-	-	-
	LL01LU-DF40L06-U2-T	-	-	-
 LUMILEDS LUXEON REBEL	LL01LU-DF60L06-U2-T	-	-	-
	LL01LU-DF80L06-U2-T	34°	1.9	
	LL01LU-DF100L06-U2-T	49°	1.0	
	LL01LU-DF3065L06-U2-T	25°×35°	2.3	
	LL01LU-DF25L06-U2-T	-	-	-
 LUMILEDS LUXEON REBEL ES	LL01LU-DF40L06-U2-T	-	-	-
	LL01LU-DF60L06-U2-T	-	-	-
	LL01LU-DF80L06-U2-T	41°	1.2	
	LL01LU-DF100L06-U2-T	54°	0.8	
	LL01LU-DF3065L06-U2-T	27°×35°	1.9	

BDF Series

LED	Part No	FWHM	cd / lm	IES
 CREE XB-D	LL01CR-BDF25L06-U2-T	16°	5.6	
	LL01CR-BDF40L06-U2-T	18°	4.6	
	LL01CR-BDF60L06-U2-T	30°	2.1	
	LL01CR-BDF80L06-U2-T	40°	1.4	
	LL01CR-BDF100L06-U2-T	52°	0.9	
	LL01CR-BDF3065L06-U2-T	24°×35°	2.2	
 CREE XHP35-HI	LL01CR-BDF3070L06-U2-T	18°×37°	3.1	
	LL01OS-BDF25L06	23°	3.4	
	LL01CR-BDF40L06	22°	3.7	
	LL01CR-BDF60L06	33°	1.7	
 CREE XPE	LL01CR-BDF3070L06	23°×36°	2.1	
	LL01CR-CR25L06-M2-T	-	-	-
	LL01CR-CR40L06-M2-T	15°	7.9	
	LL01CR-CR60L06-M2-T	27°	2.5	
 CREE XPL-HI	LL01CR-CR3070L06-M2-T	17°×32°	2.8	
	LL01OS-BDF25L06	20°	4.7	
	LL01CR-BDF40L06	20°	4.0	
	LL01CR-BDF60L06	31°	1.9	
 CREE XQD	LL01CR-BDF3070L06	-	-	-
	LL01OS-BDF25L06	-	-	-
	LL01CR-BDF40L06	21°	3.3	
	LL01CR-BDF60L06	30°	2.0	
 CREE XQE-HD	LL01CR-BDF3070L06	-	-	-
	LL01OS-BDF25L06	-	-	-
	LL01CR-BDF40L06	16°	6.3	
	LL01CR-BDF60L06	27°	2.4	
 CREE XQE-HI	LL01CR-BDF3070L06	-	-	-
	LL01OS-BDF25L06	11°	10.5	
	LL01CR-BDF40L06	15°	6.5	
	LL01CR-BDF60L06	25°	2.8	
 LG Innotek H35C1	LL01CR-BDF3070L06	-	-	-
	LL01RP-BDF40L06-M2-T	21°	3.7	
	LL01RP-BDF60L06-M2-T	33°	1.7	
	LL01RP-BDF80L06-M2-T	37°	1.6	
 LUMILEDS LUXEON 3030 2D	LL01RP-BDF100L06-M2-T	57°	0.9	
	LL01OS-BDF25L06-U2-T	-	-	-
	LL01OS-BDF40L06-U2-T	18°	4.2	
	LL01OS-BDF60L06-U2-T	32°	2.1	
 LUMILEDS LUXEON REBEL ES	LL01OS-BDF80L06-U2-T	-	-	-
	LL01OS-BDF100L06-U2-T	-	-	-
	LL01OS-BDF3065L06-U2-T	-	-	-
	LL01OS-BDF3070L06-U2-T	-	-	-
	LL01LU-BDF25L06-U2-T	21°	4.5	
	LL01LU-BDF40L06-U2-T	21°	3.6	
 LUMILEDS LUXEON REBEL ES	LL01LU-BDF60L06-U2-T	32°	1.9	
	LL01LU-BDF3070L06-U2-T	20°×35°	2.3	

BDF Series

LED	Part No	FWHM	cd / lm	IES
	LL01OS-BDF25L06	-	-	-
	LL01CR-BDF40L06	16°	6.2	
	LL01CR-BDF60L06	27°	2.6	
	LL01CR-BDF3070L06	-	-	-
	LL01OS-BDF25L06-U2-T	-	-	-
	LL01OS-BDF40L06-U2-T	21°	3.7	
	LL01OS-BDF60L06-U2-T	32°	2.1	
	LL01OS-BDF80L06-U2-T	35°	1.6	
	LL01OS-BDF100L06-U2-T	52°	0.9	
	LL01OS-BDF3065L06-U2-T	28°×36°	1.9	
	LL01OS-BDF3070L06-U2-T	-	-	-
	LL01OS-BDF25L06-U2-T	-	-	-
	LL01OS-BDF40L06-U2-T	20°	3.9	
	LL01OS-BDF60L06-U2-T	32°	1.7	
	LL01OS-BDF80L06-U2-T	32°	2.0	
	LL01OS-BDF100L06-U2-T	43°	1.2	
	LL01OS-BDF3065L06-U2-T	-	-	-
	LL01OS-BDF3070L06-U2-T	-	-	-
	LL01OS-BDF25L06-U2-T	18°	4.9	
	LL01OS-BDF40L06-U2-T	20°	4.3	
	LL01OS-BDF60L06-U2-T	30°	2.1	
	LL01OS-BDF80L06-U2-T	40°	1.4	
	LL01OS-BDF100L06-U2-T	51°	1.0	
	LL01OS-BDF3065L06-U2-T	23°×32°	2.5	
	LL01OS-BDF3070L06-U2-T	-	-	-
	LL01OS-BDF25L06-U2-T	13°	8.6	
	LL01OS-BDF40L06-U2-T	17°	5.1	
	LL01OS-BDF60L06-U2-T	31°	2.0	
	LL01OS-BDF80L06-U2-T	-	-	-
	LL01OS-BDF100L06-U2-T	-	-	-
	LL01OS-BDF3065L06-U2-T	-	-	-
	LL01OS-BDF3070L06-U2-T	-	-	-
	LL01OS-BDF25L06-M2-T	12°	10.1	
	LL01OS-BDF40L06-M2-T	17°	6.1	
	LL01OS-BDF60L06-M2-T	25°	3.0	
	LL01OS-BDF80L06-M2-T	41°	1.4	
	LL01OS-BDF100L06-M2-T	44°	1.2	
	LL01OS-BDF3065L06-M2-T	-	-	-
	LL01OS-BDF3070L06-M2-T	-	-	-
	LL01OS-BDF25L06	17°	3.4	
	LL01CR-BDF40L06	21°	3.1	
	LL01CR-BDF60L06	30°	1.7	
	LL01CR-BDF3070L06	21°×38°	2.7	
	LL01OS-BDF25L06	17°	3.6	
	LL01CR-BDF40L06	22°	3.0	
	LL01CR-BDF60L06	33°	1.5	
	LL01CR-BDF3070L06	23°×38°	2.5	

LED	Part No	FWHM	cd / lm	IES
	LL01OS-BDF25L06-U2-T	17°	4.8	
	LL01OS-BDF40L06-U2-T	21°	3.6	
	LL01OS-BDF60L06-U2-T	31°	1.9	
	LL01OS-BDF80L06-U2-T	-	-	-
	LL01OS-BDF100L06-U2-T	-	-	-
	LL01OS-BDF3065L06-U2-T	-	-	-
	LL01OS-BDF3070L06-U2-T	-	-	-

Product Nomenclature

Ledlink Led Type Lens Angle Holder
LL 01 CR -DF 25 L06 -M2 -T
Lens Dot Number Serial Number Type of Material Tape

Ledlink Optics, Inc

Taiwan HQ

15F, No.655,Bannan Rd., Chung-Ho Dist.,
New Taipei City, Taiwan 235

Ledlink Optics (Dongguan) Co., Ltd

Dongguan Factory

No.5, TianKeng Industrial Dist., HengLi Town, DongGuan City,
GuangDong Province, China 523478

Ledlink Optics (Yangzhou) Co., Ltd

Yangzhou Factory

No.180, LinJiang Rd., YangZhou City, Jiangsu Province, China 225009

www.ledlink-optics.com

service@ledlink-optics.com



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

LedLink Optics:

[LL01CR-DF40L](#) [LL01CR-DF25L-M2](#) [LL01CR-DF60L](#) [LL01CR-BDF40L06](#) [LL01CR-BDF60L06](#) [LL01CR-DF60L06-M2](#) [LL01CR-DF25L06-M2](#) [LL01CR-DF40L06](#) [LL01CR-DF60L06](#) [LL01OS-BDF60L06-M2-T](#) [LL01RP-BDF80L06-M2-T](#) [LL01CR-BDF60L06-M2-T](#) [LL01CR-DF40L06-M2-T](#) [LL01LU-DF40L06-U2-T](#) [LL01HS-DF40L06-M2-T](#) [LL01OS-BDF3065L06-M2-T](#) [LL01CR-BDF80L06-M2-T](#) [LL01CR-DF3065L06](#) [LL01HS-DF3065L06-M2-T](#) [LL01OS-BDF3070L06-M2-T](#) [LL01HS-DF80L06-M2-T](#) [LL01RP-BDF40L06-M2-T](#) [LL01CR-BDF25L06-M2-T](#) [LL01CR-QK25L06-M2-T](#) [LL01LU-BDF60L06-M2-T](#) [LL01HS-DF3070L06-M2-T](#) [LL01OS-BDF25L06](#) [LL01CR-DF80L06-M2-T](#) [LL01CR-QK3070L06-M2-T](#) [LL01LU-DF25L06-U2-T](#) [LL01HS-DF60L06-M2-T](#) [LL01OS-BDF40L06-M2-T](#) [LL01OS-BDF80L06-M2-T](#) [LL01CR-DF100L06-M2](#) [LL01CR-DF25L06](#) [LL01RP-BDF60L06-M2-T](#) [LL01CR-BDF3070L06-M2-T](#) [LL01CR-DF3070L06-M2-T](#) [LL01CR-QK100L06-M2-T](#) [LL01LU-DF80L06-U2-T](#) [LL01CR-DF3070L06](#) [LL01HS-DF25L06-M2-T](#) [LL01CR-DF60L06-M2-T](#) [LL01LU-DF3070L06-U2-T](#) [LL01CR-BDF3070L06](#) [LL01CR-DF100L06-M2-T](#) [LL01CR-DF40L06-M2](#) [LL01CR-QK80L06-M2-T](#) [LL01LU-DF60L06-U2-T](#) [LL01CR-QK60L06-M2-T](#) [LL01LU-BDF3070L06-M2-T](#) [LL01OS-BDF100L06-M2-T](#) [LL01CR-BDF3065L06-M2-T](#) [LL01CR-DF100L02-M2](#) [LL01RP-BDF100L06-M2-T](#) [LL01CR-DF25L06-M2-T](#) [LL01OS-BDF25L06-M2-T](#) [LL01LU-BDF40L06-M2-T](#) [LL01CR-BDF100L06-M2-T](#) [LL01LU-DF100L06-U2-T](#) [LL01LU-DF3065L06-U2-T](#) [LL01CR-DF3065L06-M2-T](#) [LL01HS-DF100L06-M2-T](#) [LL01CR-BDF40L06-M2-T](#) [LL01CR-DF100L06](#) [LL01LU-BDF25L06-M2-T](#) [LL01CR-DF80L06](#) [LL01CR-QK3065L06-M2-T](#) [LL01CR-QK40L06-M2-T](#)