


6			
NO OF CKTS	DIM A	DIM B	DIM C
2	$\frac{(5.44)}{.214}$	$\frac{(2.54)}{.100}$	$\frac{(7.59)}{.299}$
3	$\frac{(7.98)}{.314}$	$\frac{(5.08)}{.200}$	$\frac{(10.13)}{.399}$
4	$\frac{(10.52)}{.414}$	$\frac{(7.62)}{.300}$	$\frac{(12.67)}{.499}$
5	$\frac{(13.06)}{.514}$	$\frac{(10.16)}{.400}$	$\frac{(15.21)}{.599}$
6	$\frac{(15.60)}{.614}$	$\frac{(12.70)}{.500}$	$\frac{(17.75)}{.699}$
7	$\frac{(18.14)}{.714}$	$\frac{(15.24)}{.600}$	$\frac{(20.29)}{.799}$
8	$\frac{(20.68)}{.814}$	$\frac{(17.78)}{.700}$	$\frac{(22.23)}{.899}$
9	$\frac{(23.22)}{.914}$	$\frac{(20.30)}{.800}$	$\frac{(25.37)}{.999}$
10	$\frac{(25.76)}{1.014}$	$\frac{(22.86)}{.900}$	$\frac{(27.91)}{1.099}$
11	$\frac{(28.30)}{1.114}$	$\frac{(25.40)}{1.000}$	$\frac{(30.45)}{1.199}$
12	$\frac{(30.84)}{1.214}$	$\frac{(27.94)}{1.100}$	$\frac{(32.99)}{1.299}$
13	$\frac{(33.38)}{1.314}$	$\frac{(30.48)}{1.200}$	$\frac{(35.53)}{1.399}$
14	$\frac{(35.92)}{1.414}$	$\frac{(33.02)}{1.300}$	$\frac{(38.07)}{1.499}$
15	$\frac{(38.46)}{1.514}$	$\frac{(35.56)}{1.400}$	$\frac{(40.61)}{1.599}$
16	$\frac{(41.00)}{1.614}$	$\frac{(38.10)}{1.500}$	$\frac{(43.15)}{1.699}$
17	$\frac{(43.54)}{1.714}$	$\frac{(40.64)}{1.600}$	$\frac{(45.69)}{1.799}$
18	$\frac{(46.08)}{1.814}$	$\frac{(43.18)}{1.700}$	$\frac{(48.23)}{1.899}$
19	$\frac{(48.62)}{1.914}$	$\frac{(45.72)}{1.800}$	$\frac{(50.77)}{1.999}$
20	$\frac{(51.16)}{2.014}$	$\frac{(48.26)}{1.900}$	$\frac{(53.31)}{2.099}$
21	$\frac{(53.70)}{2.114}$	$\frac{(50.80)}{2.000}$	$\frac{(55.85)}{2.199}$
22	$\frac{(56.24)}{2.214}$	$\frac{(53.34)}{2.100}$	$\frac{(58.39)}{2.299}$
23	$\frac{(58.78)}{2.314}$	$\frac{(55.88)}{2.200}$	$\frac{(60.93)}{2.399}$
24	$\frac{(61.32)}{2.414}$	$\frac{(58.42)}{2.300}$	$\frac{(63.47)}{2.499}$
25	$\frac{(63.86)}{2.514}$	$\frac{(60.96)}{2.400}$	$\frac{(66.01)}{2.599}$
26	$\frac{(66.40)}{2.614}$	$\frac{(63.50)}{2.500}$	$\frac{(68.55)}{2.699}$
27	$\frac{(68.94)}{2.714}$	$\frac{(66.04)}{2.600}$	$\frac{(71.09)}{2.799}$
28	$\frac{(71.48)}{2.814}$	$\frac{(68.58)}{2.700}$	$\frac{(73.63)}{2.899}$



- ## NOTES

1. MATERIAL: HOUSING: UNFILLED NYLON, UL94V-2, MOLDED NATURAL (WHITE)
TERMINALS: SEE LEGEND
2. FINISH:
 - (154) OVERALL TIN: (0.00254)/(0.000100 MIN OVER
(0.00127)/(0.000050 MIN NICKEL.
 - (197) OVERALL REFLOWED MATTE TIN: (0.00152)/(0.000060 MIN OVER
(0.00127)/(0.000050 MIN NICKEL.
 - (208) SELECT GOLD: (0.00038)/(0.000015 MIN,
SELECT TIN: (0.00254)/(0.000100 MIN,
OVERALL NICKEL UNDERPLATE: (0.00127)/(0.000050 MIN.
 - (228) SELECT GOLD: (0.00076)/(0.000030 MIN,
SELECT TIN: (0.00254)/(0.000100 MIN,
OVERALL NICKLE UNDERPLATE: (0.00127)/(0.000050 MIN.
 - (501) OVERALL GOLD: (0.00051)/(0.000020 MIN OVER
(0.00076)/(0.000030 MIN NICKEL
 - (502) OVERALL GOLD: (0.00051)/(0.000020 MIN OVER
(0.00127)/(0.000050 MIN NICKEL.
 - (503) OVERALL GOLD: (0.00076)/(0.000030 MIN OVER
(0.00127)/(0.000050 MIN NICKEL.
3. PRODUCT SPECIFICATION: PS-7720-001
4. PACKAGING: BULK PK-7720-001 SEE CHART
5. THESE HOUSINGS ARE FOR USE WITH SINGLE 22 AWG WIRE TERMINATION C
6. COLORED STRIPE TO RUN LENTH OF RIB AS SHOWN (SEE CHART FOR COLO
7. SEE APPLICATION SPEC SMES-7720-0002 FOR ADDITIONAL INFORMATION.
8. WIRE SPECIFICATIONS: SEE SMES-7720-0002
(INSUL. DIA (1.52)/(0.060 MAX)
SLOT SIZE A FOR USE WITH:
26 AWG SOLID, STRANDED TINNED
28 AWG SOLID, STRANDED TINNED, AND STRANDED TOPCOAT
SLOT SIZE H FOR USE WITH:
24 AWG SOLID, STRANDED TINNED, AND STRANDED TOPCOAT
26 AWG STRANDED TOPCOAT
SLOT SIZE F FOR USE WITH:
22 AWG STRANDED TINNED
9. THIS PART CONFORMS TO CLASS B REQUIREMENTS OF
COSMETIC SPECIFICATION PS-45499-002.

3-*	BB
2	BB
1	BB

CHANGE PLATING EC NO: UCP2011-1314 DRAWN:MK IPER 2010/12/29 CHKD: J.BELL APPR: FSWITH 2011/03/09				DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM/IN		SCALE ---	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	
					= 0	4 PLACES	± ---	± ---	DRAWN BY	DATE	TITLE KK 100 IDT CONNECTOR ASSEMBLY			
					= 0	3 PLACES	± ---	± ---	CHECKED BY	DATE				
					= 0	2 PLACES	± ---	± ---	SAMIEC	2004/04/13				
					1 PLACE	± ---	± ---	APPROVED BY	DATE	MOLEX INCORPORATED				
					ANGULAR ±1/2°			MARGULIS	2004/04/13					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS								MATERIAL NO.	DOCUMENT NO.				SHEET NO.	
								SEE CHART		SD-7720-001			1 OF *	
BB					REV	SIZE A	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

D

C

B

A


D

C

B


A

6 HOUSING TYPE A	5 HOUSING TYPE D	4	3 HOUSING TYPE WA	2 HOUSING TYPE WD	1
HOUSING TYPE B	HOUSING TYPE E		HOUSING TYPE WB	HOUSING TYPE WE	
HOUSING TYPE C	HOUSING TYPE F		HOUSING TYPE WC	HOUSING TYPE WF	



CAT EARS

CAT EAR TERMINAL OPTION



COLOR STRIP
SEE NOTE 6
TYP ALL HOUSING TYPES

ADD CAT EAR VIEW EC NO: UCP2011-1314 DRWN:MKIPPER CHKD:JBELL APPR:FSMITH BB		2011/01/05 2011/03/09	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 □=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM/IN		SCALE ---	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	TITLE KK 100 IDT CONNECTOR ASSEMBLY	
						mm	INCH	DRAWN BY SAMIEC	DATE 2004/04/13	MOLEX MOLEX INCORPORATED				
					4 PLACES	± ---	± ---	CHECKED BY SAMIEC	DATE 2004/04/13					
					3 PLACES	± ---	± ---	APPROVED BY MARGULIS	DATE 2004/04/13					
					2 PLACES	± ---	± ---	MATERIAL NO. SEE CHART					DOCUMENT NO. SD-7720-001	SHEET NO. 2 OF *
1 PLACE		± ---	± ---	ANGULAR ±1/2°		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

A-7720-ANA154		A-7720-BNA154		A-7720-CNA154		A-7720-DNA154		A-7720-ENA154		A-7720-FNA154	
HOUSING	7720-AN	HOUSING	7720-BN	HOUSING	7720-CN	HOUSING	7720-DN	HOUSING	7720-EN	HOUSING	7720-FN
TERM. NO	7691-A154	TERM. NO	7691-A154	TERM. NO	7691-A154	TERM. NO	7691-A154	TERM. NO	7691-A154	TERM. NO	7691-A154
PLATING:	154	PLATING:	154	PLATING:	154	PLATING:	154	PLATING:	154	PLATING:	154
COLOR	BROWN	COLOR	BROWN	COLOR	BROWN	COLOR	BROWN	COLOR	BROWN	COLOR	BROWN
MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:
22-26-7021	A-7720-A02A154A	22-26-8021	A-7720-B02A154A	22-26-9021	A-7720-C02A154A	22-41-3021	A-7720-D02A154A	22-41-4021	A-7720-E02A154A	22-41-5021	A-7720-F02A154A
22-26-7031	A-7720-A03A154A	22-26-8031	A-7720-B03A154A	22-26-9031	A-7720-C03A154A	22-41-3031	A-7720-D03A154A	22-41-4031	A-7720-E03A154A	22-41-5031	A-7720-F03A154A
22-26-7041	A-7720-A04A154A	22-26-8041	A-7720-B04A154A	22-26-9041	A-7720-C04A154A	22-41-3041	A-7720-D04A154A	22-41-4041	A-7720-E04A154A	22-41-5041	A-7720-F04A154A
22-26-7051	A-7720-A05A154A	22-26-8051	A-7720-B05A154A	22-26-9051	A-7720-C05A154A	22-41-3051	A-7720-D05A154A	22-41-4051	A-7720-E05A154A	22-41-5051	A-7720-F05A154A
22-26-7061	A-7720-A06A154A	22-26-8061	A-7720-B06A154A	22-26-9061	A-7720-C06A154A	22-41-3061	A-7720-D06A154A	22-41-4061	A-7720-E06A154A	22-41-5061	A-7720-F06A154A
22-26-7071	A-7720-A07A154A	22-26-8071	A-7720-B07A154A	22-26-9071	A-7720-C07A154A	22-41-3071	A-7720-D07A154A	22-41-4071	A-7720-E07A154A	22-41-5071	A-7720-F07A154A
22-26-7081	A-7720-A08A154A	22-26-8081	A-7720-B08A154A	22-26-9081	A-7720-C08A154A	22-41-3081	A-7720-D08A154A	22-41-4081	A-7720-E08A154A	22-41-5081	A-7720-F08A154A
22-26-7091	A-7720-A09A154A	22-26-8091	A-7720-B09A154A	22-26-9091	A-7720-C09A154A	22-41-3091	A-7720-D09A154A	22-41-4091	A-7720-E09A154A	22-41-5091	A-7720-F09A154A
22-26-7101	A-7720-A10A154A	22-26-8101	A-7720-B10A154A	22-26-9101	A-7720-C10A154A	22-41-3101	A-7720-D10A154A	22-41-4101	A-7720-E10A154A	22-41-5101	A-7720-F10A154A
22-26-7111	A-7720-A11A154A	22-26-8111	A-7720-B11A154A	22-26-9111	A-7720-C11A154A	22-41-3111	A-7720-D11A154A	22-41-4111	A-7720-E11A154A	22-41-5111	A-7720-F11A154A
22-26-7121	A-7720-A12A154A	22-26-8121	A-7720-B12A154A	22-26-9121	A-7720-C12A154A	22-41-3121	A-7720-D12A154A	22-41-4121	A-7720-E12A154A	22-41-5121	A-7720-F12A154A
22-26-7131	A-7720-A13A154A	22-26-8131	A-7720-B13A154A	22-26-9131	A-7720-C13A154A	22-41-3131	A-7720-D13A154A	22-41-4131	A-7720-E13A154A	22-41-5131	A-7720-F13A154A
22-26-7141	A-7720-A14A154A	22-26-8141	A-7720-B14A154A	22-26-9141	A-7720-C14A154A	22-41-3141	A-7720-D14A154A	22-41-4141	A-7720-E14A154A	22-41-5141	A-7720-F14A154A
22-26-7151	A-7720-A15A154A	22-26-8151	A-7720-B15A154A	22-26-9151	A-7720-C15A154A	22-41-3151	A-7720-D15A154A	22-41-4151	A-7720-E15A154A	22-41-5151	A-7720-F15A154A
22-26-7161	A-7720-A16A154A	22-26-8161	A-7720-B16A154A	22-26-9161	A-7720-C16A154A	22-41-3161	A-7720-D16A154A	22-41-4161	A-7720-E16A154A	22-41-5161	A-7720-F16A154A
22-26-7171	A-7720-A17A154A	22-26-8171	A-7720-B17A154A	22-26-9171	A-7720-C17A154A	22-41-3171	A-7720-D17A154A	22-41-4171	A-7720-E17A154A	22-41-5171	A-7720-F17A154A
22-26-7181	A-7720-A18A154A	22-26-8181	A-7720-B18A154A	22-26-9181	A-7720-C18A154A	22-41-3181	A-7720-D18A154A	22-41-4181	A-7720-E18A154A	22-41-5181	A-7720-F18A154A
22-26-7191	A-7720-A19A154A	22-26-8191	A-7720-B19A154A	22-26-9191	A-7720-C19A154A	22-41-3191	A-7720-D19A154A	22-41-4191	A-7720-E19A154A	22-41-5191	A-7720-F19A154A
22-26-7201	A-7720-A20A154A	22-26-8201	A-7720-B20A154A	22-26-9201	A-7720-C20A154A	22-41-3201	A-7720-D20A154A	22-41-4201	A-7720-E20A154A	22-41-5201	A-7720-F20A154A
22-26-7211	A-7720-A21A154A	22-26-8211	A-7720-B21A154A	22-26-9211	A-7720-C21A154A	22-41-3211	A-7720-D21A154A	22-41-4211	A-7720-E21A154A	22-41-5211	A-7720-F21A154A
22-26-7221	A-7720-A22A154A	22-26-8221	A-7720-B22A154A	22-26-9221	A-7720-C22A154A	22-41-3221	A-7720-D22A154A	22-41-4221	A-7720-E22A154A	22-41-5221	A-7720-F22A154A
22-26-7231	A-7720-A23A154A	22-26-8231	A-7720-B23A154A	22-26-9231	A-7720-C23A154A	22-41-3231	A-7720-D23A154A	22-41-4231	A-7720-E23A154A	22-41-5231	A-7720-F23A154A
22-26-7241	A-7720-A24A154A	22-26-8241	A-7720-B24A154A	22-26-9241	A-7720-C24A154A	22-41-3241	A-7720-D24A154A	22-41-4241	A-7720-E24A154A	22-41-5241	A-7720-F24A154A
22-26-7251	A-7720-A25A154A	22-26-8251	A-7720-B25A154A	22-26-9251	A-7720-C25A154A	22-41-3251	A-7720-D25A154A	22-41-4251	A-7720-E25A154A	22-41-5251	A-7720-F25A154A
22-26-7261	A-7720-A26A154A	22-26-8261	A-7720-B26A154A	22-26-9261	A-7720-C26A154A	22-41-3261	A-7720-D26A154A	22-41-4261	A-7720-E26A154A	22-41-5261	A-7720-F26A154A
	A-7720-A27A154A	22-26-8271	A-7720-B27A154A		A-7720-C27A154A	22-41-3271	A-7720-D27A154A	22-41-4271	A-7720-E27A154A	22-41-5271	A-7720-F27A154A
22-26-7281	A-7720-A28A154A	22-26-8281	A-7720-B28A154A	22-26-9281	A-7720-C28A154A	22-41-3281	A-7720-D28A154A	22-41-4281	A-7720-E28A154A	22-41-5281	A-7720-F28A154A

REVISION: BB	ECR/ECN INFORMATION:	TITLE: KK 100 IDT CONNECTOR ASSEMBLY	SHEET No. 3
	EC No.: UCP2011-1314		
	DATE: 4/12/2011		
DOCUMENT NUMBER: SD-7720-001		CREATED / REVISED BY: MKIPPER	CHECKED BY: JBELL
		APPROVED BY: FSMITH	

A-7720-ANF154B		A-7720-BNF154B		A-7720-CNF154B		A-7720-DNF154B		A-7720-ENF154B		A-7720-FNF154B	
HOUSING	7720-AN	HOUSING	7720-BN	HOUSING	7720-CN	HOUSING	7720-DN	HOUSING	7720-EN	HOUSING	7720-FN
TERM. NO	41138-F154	TERM. NO	41138-F154	TERM. NO	41138-F154	TERM. NO	41138-F154	TERM. NO	41138-F154	TERM. NO	41138-F154
PLATING:	154	PLATING:	154	PLATING:	154	PLATING:	154	PLATING:	154	PLATING:	154
COLOR	BLACK	COLOR	BLACK	COLOR	BLACK	COLOR	BLACK	COLOR	BLACK	COLOR	BLACK
MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:
22-42-3020	A-7720-A02F154B	22-42-3021	A-7720-B02F154B	22-42-3022	A-7720-C02F154B	22-42-3023	A-7720-D02F154B	22-42-3024	A-7720-E02F154B	22-42-3025	A-7720-F02F154B
22-42-3030	A-7720-A03F154B	22-42-3031	A-7720-B03F154B	22-42-3032	A-7720-C03F154B	22-42-3033	A-7720-D03F154B	22-42-3034	A-7720-E03F154B	22-42-3035	A-7720-F03F154B
22-42-3040	A-7720-A04F154B	22-42-3041	A-7720-B04F154B	22-42-3042	A-7720-C04F154B	22-42-3043	A-7720-D04F154B	22-42-3044	A-7720-E04F154B	22-42-3045	A-7720-F04F154B
22-42-3050	A-7720-A05F154B	22-42-3051	A-7720-B05F154B	22-42-3052	A-7720-C05F154B	22-42-3053	A-7720-D05F154B	22-42-3054	A-7720-E05F154B	22-42-3055	A-7720-F05F154B
22-42-3060	A-7720-A06F154B	22-42-3061	A-7720-B06F154B	22-42-3062	A-7720-C06F154B	22-42-3063	A-7720-D06F154B	22-42-3064	A-7720-E06F154B	22-42-3065	A-7720-F06F154B
22-42-3070	A-7720-A07F154B	22-42-3071	A-7720-B07F154B	22-42-3072	A-7720-C07F154B	22-42-3073	A-7720-D07F154B	22-42-3074	A-7720-E07F154B	22-42-3075	A-7720-F07F154B
22-42-3080	A-7720-A08F154B	22-42-3081	A-7720-B08F154B	22-42-3082	A-7720-C08F154B		A-7720-D08F154B	22-42-3084	A-7720-E08F154B	22-42-3085	A-7720-F08F154B
22-42-3090	A-7720-A09F154B	22-42-3091	A-7720-B09F154B	22-42-3092	A-7720-C09F154B	22-42-3093	A-7720-D09F154B	22-42-3094	A-7720-E09F154B	22-42-3095	A-7720-F09F154B
22-42-3100	A-7720-A10F154B	22-42-3101	A-7720-B10F154B	22-42-3102	A-7720-C10F154B		A-7720-D10F154B	22-42-3104	A-7720-E10F154B	22-42-3105	A-7720-F10F154B
22-42-3110	A-7720-A11F154B	22-42-3111	A-7720-B11F154B	22-42-3112	A-7720-C11F154B		A-7720-D11F154B	22-42-3114	A-7720-E11F154B	22-42-3115	A-7720-F11F154B
	A-7720-A12F154B	22-42-3121	A-7720-B12F154B	22-42-3122	A-7720-C12F154B		A-7720-D12F154B	22-42-3124	A-7720-E12F154B	22-42-3125	A-7720-F12F154B
	A-7720-A13F154B	22-42-3131	A-7720-B13F154B	22-42-3132	A-7720-C13F154B		A-7720-D13F154B	22-42-3134	A-7720-E13F154B	22-42-3135	A-7720-F13F154B
	A-7720-A14F154B	22-42-3141	A-7720-B14F154B	22-42-3142	A-7720-C14F154B		A-7720-D14F154B	22-42-3144	A-7720-E14F154B	22-42-3145	A-7720-F14F154B
	A-7720-A15F154B	22-42-3151	A-7720-B15F154B	22-42-3152	A-7720-C15F154B		A-7720-D15F154B	22-42-3154	A-7720-E15F154B	22-42-3155	A-7720-F15F154B
	A-7720-A16F154B	22-42-3161	A-7720-B16F154B	22-42-3162	A-7720-C16F154B		A-7720-D16F154B	22-42-3164	A-7720-E16F154B	22-42-3165	A-7720-F16F154B
	A-7720-A17F154B	22-42-3171	A-7720-B17F154B	22-42-3172	A-7720-C17F154B		A-7720-D17F154B	22-42-3174	A-7720-E17F154B	22-42-3175	A-7720-F17F154B
	A-7720-A18F154B	22-42-3181	A-7720-B18F154B	22-42-3182	A-7720-C18F154B		A-7720-D18F154B	22-42-3184	A-7720-E18F154B	22-42-3185	A-7720-F18F154B
22-42-3190	A-7720-A19F154B	22-42-3191	A-7720-B19F154B	22-42-3192	A-7720-C19F154B		A-7720-D19F154B	22-42-3194	A-7720-E19F154B	22-42-3195	A-7720-F19F154B
	A-7720-A20F154B	22-42-3201	A-7720-B20F154B	22-42-3202	A-7720-C20F154B		A-7720-D20F154B	22-42-3204	A-7720-E20F154B	22-42-3205	A-7720-F20F154B
22-42-3210	A-7720-A21F154B	22-42-3211	A-7720-B21F154B	22-42-3212	A-7720-C21F154B		A-7720-D21F154B	22-42-3214	A-7720-E21F154B	22-42-3215	A-7720-F21F154B
	A-7720-A22F154B	22-42-3221	A-7720-B22F154B	22-42-3222	A-7720-C22F154B		A-7720-D22F154B	22-42-3224	A-7720-E22F154B	22-42-3225	A-7720-F22F154B
	A-7720-A23F154B	22-42-3231	A-7720-B23F154B	22-42-3232	A-7720-C23F154B		A-7720-D23F154B	22-42-3234	A-7720-E23F154B	22-42-3235	A-7720-F23F154B
	A-7720-A24F154B	22-42-3241	A-7720-B24F154B	22-42-3242	A-7720-C24F154B		A-7720-D24F154B	22-42-3244	A-7720-E24F154B	22-42-3245	A-7720-F24F154B
22-42-3250	A-7720-A25F154B	22-42-3251	A-7720-B25F154B	22-42-3252	A-7720-C25F154B		A-7720-D25F154B	22-42-3254	A-7720-E25F154B	22-42-3255	A-7720-F25F154B
	A-7720-A26F154B	22-42-3261	A-7720-B26F154B	22-42-3262	A-7720-C26F154B		A-7720-D26F154B	22-42-3264	A-7720-E26F154B	22-42-3265	A-7720-F26F154B
	A-7720-A27F154B	22-42-3271	A-7720-B27F154B	22-42-3272	A-7720-C27F154B		A-7720-D27F154B	22-42-3274	A-7720-E27F154B	22-42-3275	A-7720-F27F154B
	A-7720-A28F154B	22-42-3281	A-7720-B28F154B	22-42-3282	A-7720-C28F154B		A-7720-D28F154B	22-42-3284	A-7720-E28F154B	22-42-3285	A-7720-F28F154B

REVISION: BB	ECR/ECN INFORMATION:	TITLE: KK 100 IDT CONNECTOR ASSEMBLY	SHEET No. 5
	EC No.: UCP2011-1314 DATE: 4/12/2011		
DOCUMENT NUMBER: SD-7720-001		CREATED / REVISED BY: MKIPPER	CHECKED BY: JBELL
		APPROVED BY: FSMITH	

A-7720-WANF154B		A-7720-WBNF154B		A-7720-WCNF154B		A-7720-WDNF154B		A-7720-WENF154B		A-7720-WFNF154B	
HOUSING	7720-WAN	HOUSING	7720-WBN	HOUSING	7720-WCN	HOUSING	7720WDN	HOUSING	7720-WEN	HOUSING	7720-WFN
TERM. NO	41138-F154	TERM. NO	41138-F154	TERM. NO	41138-F154	TERM. NO	41138-F154	TERM. NO	41138-F154	TERM. NO	41138-F154
PLATING:	154	PLATING:	154	PLATING:	154	PLATING:	154	PLATING:	154	PLATING:	154
COLOR	BLACK	COLOR	BLACK	COLOR	BLACK	COLOR	BLACK	COLOR	BLACK	COLOR	BLACK
MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:
22-42-6020	A-7720-WA02F154B	22-42-6021	A-7720-WB02F154B	22-42-6022	A-7720-WC02F154B	22-42-6023	A-7720-WD02F154B	22-42-6024	A-7720-WE02F154B	22-42-6025	A-7720-WF02F154B
22-42-6030	A-7720-WA03F154B	22-42-6031	A-7720-WB03F154B	22-42-6032	A-7720-WC03F154B	22-42-6033	A-7720-WD03F154B	22-42-6034	A-7720-WE03F154B	22-42-6035	A-7720-WF03F154B
22-42-6040	A-7720-WA04F154B	22-42-6041	A-7720-WB04F154B	22-42-6042	A-7720-WC04F154B	22-42-6043	A-7720-WD04F154B	22-42-6044	A-7720-WE04F154B	22-42-6045	A-7720-WF04F154B
22-42-6050	A-7720-WA05F154B	22-42-6051	A-7720-WB05F154B	22-42-6052	A-7720-WC05F154B	22-42-6053	A-7720-WD05F154B	22-42-6054	A-7720-WE05F154B	22-42-6055	A-7720-WF05F154B
22-42-6060	A-7720-WA06F154B	22-42-6061	A-7720-WB06F154B	22-42-6062	A-7720-WC06F154B	22-42-6063	A-7720-WD06F154B	22-42-6064	A-7720-WE06F154B	22-42-6065	A-7720-WF06F154B
22-42-6070	A-7720-WA07F154B	22-42-6071	A-7720-WB07F154B	22-42-6072	A-7720-WC07F154B	22-42-6073	A-7720-WD07F154B	22-42-6074	A-7720-WE07F154B	22-42-6075	A-7720-WF07F154B
22-42-6080	A-7720-WA08F154B	22-42-6081	A-7720-WB08F154B	22-42-6082	A-7720-WC08F154B	22-42-6083	A-7720-WD08F154B	22-42-6084	A-7720-WE08F154B	22-42-6085	A-7720-WF08F154B
22-42-6090	A-7720-WA09F154B	22-42-6091	A-7720-WB09F154B	22-42-6092	A-7720-WC09F154B	22-42-6093	A-7720-WD09F154B	22-42-6094	A-7720-WE09F154B	22-42-6095	A-7720-WF09F154B
22-42-6100	A-7720-WA10F154B	22-42-6101	A-7720-WB10F154B	22-42-6102	A-7720-WC10F154B	22-42-6103	A-7720-WD10F154B	22-42-6104	A-7720-WE10F154B	22-42-6105	A-7720-WF10F154B
22-42-6110	A-7720-WA11F154B	22-42-6111	A-7720-WB11F154B	22-42-6112	A-7720-WC11F154B	22-42-6113	A-7720-WD11F154B	22-42-6114	A-7720-WE11F154B	22-42-6115	A-7720-WF11F154B
22-42-6120	A-7720-WA12F154B	22-42-6121	A-7720-WB12F154B	22-42-6122	A-7720-WC12F154B	22-42-6123	A-7720-WD12F154B	22-42-6124	A-7720-WE12F154B	22-42-6125	A-7720-WF12F154B
22-42-6130	A-7720-WA13F154B	22-42-6131	A-7720-WB13F154B	22-42-6132	A-7720-WC13F154B	22-42-6133	A-7720-WD13F154B	22-42-6134	A-7720-WE13F154B	22-42-6135	A-7720-WF13F154B
22-42-6140	A-7720-WA14F154B	22-42-6141	A-7720-WB14F154B	22-42-6142	A-7720-WC14F154B	22-42-6143	A-7720-WD14F154B	22-42-6144	A-7720-WE14F154B	22-42-6145	A-7720-WF14F154B
22-42-6150	A-7720-WA15F154B	22-42-6151	A-7720-WB15F154B	22-42-6152	A-7720-WC15F154B	22-42-6153	A-7720-WD15F154B	22-42-6154	A-7720-WE15F154B	22-42-6155	A-7720-WF15F154B
22-42-6160	A-7720-WA16F154B	22-42-6161	A-7720-WB16F154B	22-42-6162	A-7720-WC16F154B	22-42-6163	A-7720-WD16F154B	22-42-6164	A-7720-WE16F154B	22-42-6165	A-7720-WF16F154B
22-42-6170	A-7720-WA17F154B	22-42-6171	A-7720-WB17F154B	22-42-6172	A-7720-WC17F154B	22-42-6173	A-7720-WD17F154B	22-42-6174	A-7720-WE17F154B	22-42-6175	A-7720-WF17F154B
22-42-6180	A-7720-WA18F154B	22-42-6181	A-7720-WB18F154B	22-42-6182	A-7720-WC18F154B	22-42-6183	A-7720-WD18F154B	22-42-6184	A-7720-WE18F154B	22-42-6185	A-7720-WF18F154B
22-42-6190	A-7720-WA19F154B	22-42-6191	A-7720-WB19F154B	22-42-6192	A-7720-WC19F154B	22-42-6193	A-7720-WD19F154B	22-42-6194	A-7720-WE19F154B	22-42-6195	A-7720-WF19F154B
22-42-6200	A-7720-WA20F154B	22-42-6201	A-7720-WB20F154B	22-42-6202	A-7720-WC20F154B	22-42-6203	A-7720-WD20F154B	22-42-6204	A-7720-WE20F154B	22-42-6205	A-7720-WF20F154B
22-42-6210	A-7720-WA21F154B	22-42-6211	A-7720-WB21F154B	22-42-6212	A-7720-WC21F154B	22-42-6213	A-7720-WD21F154B	22-42-6214	A-7720-WE21F154B	22-42-6215	A-7720-WF21F154B
22-42-6220	A-7720-WA22F154B	22-42-6221	A-7720-WB22F154B	22-42-6222	A-7720-WC22F154B	22-42-6223	A-7720-WD22F154B	22-42-6224	A-7720-WE22F154B	22-42-6225	A-7720-WF22F154B
22-42-6230	A-7720-WA23F154B	22-42-6231	A-7720-WB23F154B	22-42-6232	A-7720-WC23F154B	22-42-6233	A-7720-WD23F154B	22-42-6234	A-7720-WE23F154B	22-42-6235	A-7720-WF23F154B
22-42-6240	A-7720-WA24F154B	22-42-6241	A-7720-WB24F154B	22-42-6242	A-7720-WC24F154B	22-42-6243	A-7720-WD24F154B	22-42-6244	A-7720-WE24F154B	22-42-6245	A-7720-WF24F154B
22-42-6250	A-7720-WA25F154B	22-42-6251	A-7720-WB25F154B	22-42-6252	A-7720-WC25F154B	22-42-6253	A-7720-WD25F154B	22-42-6254	A-7720-WE25F154B	22-42-6255	A-7720-WF25F154B
22-42-6260	A-7720-WA26F154B	22-42-6261	A-7720-WB26F154B	22-42-6262	A-7720-WC26F154B	22-42-6263	A-7720-WD26F154B	22-42-6264	A-7720-WE26F154B	22-42-6265	A-7720-WF26F154B
22-42-6270	A-7720-WA27F154B	22-42-6271	A-7720-WB27F154B	22-42-6272	A-7720-WC27F154B	22-42-6273	A-7720-WD27F154B	22-42-6274	A-7720-WE27F154B	22-42-6275	A-7720-WF27F154B
22-42-6280	A-7720-WA28F154B	22-42-6281	A-7720-WB28F154B	22-42-6282	A-7720-WC28F154B	22-42-6283	A-7720-WD28F154B	22-42-6284	A-7720-WE28F154B	22-42-6285	A-7720-WF28F154B

<u>REVISION:</u> BB	<u>ECR/ECN INFORMATION:</u> <u>EC No.:</u> UCP2011-1314 <u>DATE:</u> 4/12/2011	<u>TITLE:</u> KK 100 IDT CONNECTOR ASSEMBLY		<u>SHEET No.</u> 6
<u>DOCUMENT NUMBER:</u> SD-7720-001		<u>CREATED / REVISED BY:</u> MKIPPER	<u>CHECKED BY:</u> JBELL	<u>APPROVED BY:</u> FSMITH
TEMPLATE FILENAME: PRODUCT_SPEC[SIZE_A](V.1).DOC				

A-7720-ANA501A		A-7720-BNA501A		A-7720-CNA501A		A-7720-DNA501A		A-7720-ENA501A		A-7720-FNA501A	
HOUSING	7720-AN	HOUSING	7720-BN	HOUSING	7720-CN	HOUSING	7720-DN	HOUSING	7720-EN	HOUSING	7720-FN
TERM. NO	7691-A501	TERM. NO	7691-A501	TERM. NO	7691-A501	TERM. NO	7691-A501	TERM. NO	7691-A501	TERM. NO	7691-A501
PLATING:	501	PLATING:	501	PLATING:	501	PLATING:	501	PLATING:	501	PLATING:	501
COLOR	BROWN	COLOR	BROWN	COLOR	BROWN	COLOR	BROWN	COLOR	BROWN	COLOR	BROWN
MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:
	A-7720-A02A501A		A-7720-B02A501A		A-7720-C02A501A		A-7720-D02A501A	22-45-7024	A-7720-E02A501A		A-7720-F02A501A
	A-7720-A03A501A		A-7720-B03A501A		A-7720-C03A501A		A-7720-D03A501A	22-45-7034	A-7720-E03A501A		A-7720-F03A501A
	A-7720-A04A501A		A-7720-B04A501A		A-7720-C04A501A		A-7720-D04A501A	22-45-7044	A-7720-E04A501A		A-7720-F04A501A
22-45-7053	A-7720-A05A501A	22-45-8051	A-7720-B05A501A		A-7720-C05A501A		A-7720-D05A501A	22-45-7054	A-7720-E05A501A		A-7720-F05A501A
	A-7720-A06A501A		A-7720-B06A501A		A-7720-C06A501A		A-7720-D06A501A	22-45-7064	A-7720-E06A501A		A-7720-F06A501A
22-45-7073	A-7720-A07A501A		A-7720-B07A501A		A-7720-C07A501A		A-7720-D07A501A	22-45-7074	A-7720-E07A501A		A-7720-F07A501A
	A-7720-A08A501A		A-7720-B08A501A		A-7720-C08A501A	22-45-7089	A-7720-D08A501A	22-45-7084	A-7720-E08A501A		A-7720-F08A501A
	A-7720-A09A501A		A-7720-B09A501A		A-7720-C09A501A		A-7720-D09A501A		A-7720-E09A501A		A-7720-F09A501A
	A-7720-A10A501A		A-7720-B10A501A		A-7720-C10A501A		A-7720-D10A501A	22-45-7104	A-7720-E10A501A		A-7720-F10A501A
	A-7720-A11A501A		A-7720-B11A501A		A-7720-C11A501A		A-7720-D11A501A		A-7720-E11A501A		A-7720-F11A501A
	A-7720-A12A501A	22-45-8121	A-7720-B12A501A		A-7720-C12A501A		A-7720-D12A501A		A-7720-E12A501A		A-7720-F12A501A
	A-7720-A13A501A		A-7720-B13A501A		A-7720-C13A501A		A-7720-D13A501A		A-7720-E13A501A		A-7720-F13A501A
	A-7720-A14A501A		A-7720-B14A501A		A-7720-C14A501A		A-7720-D14A501A		A-7720-E14A501A		A-7720-F14A501A
	A-7720-A15A501A		A-7720-B15A501A		A-7720-C15A501A		A-7720-D15A501A		A-7720-E15A501A		A-7720-F15A501A
	A-7720-A16A501A	22-45-8161	A-7720-B16A501A		A-7720-C16A501A		A-7720-D16A501A		A-7720-E16A501A		A-7720-F16A501A
	A-7720-A17A501A		A-7720-B17A501A		A-7720-C17A501A		A-7720-D17A501A		A-7720-E17A501A		A-7720-F17A501A
	A-7720-A18A501A		A-7720-B18A501A		A-7720-C18A501A		A-7720-D18A501A		A-7720-E18A501A		A-7720-F18A501A
	A-7720-A19A501A		A-7720-B19A501A		A-7720-C19A501A		A-7720-D19A501A		A-7720-E19A501A		A-7720-F19A501A
	A-7720-A20A501A		A-7720-B20A501A		A-7720-C20A501A		A-7720-D20A501A		A-7720-E20A501A		A-7720-F20A501A
	A-7720-A21A501A		A-7720-B21A501A		A-7720-C21A501A		A-7720-D21A501A		A-7720-E21A501A		A-7720-F21A501A
	A-7720-A22A501A		A-7720-B22A501A		A-7720-C22A501A		A-7720-D22A501A		A-7720-E22A501A		A-7720-F22A501A
	A-7720-A23A501A		A-7720-B23A501A		A-7720-C23A501A		A-7720-D23A501A		A-7720-E23A501A		A-7720-F23A501A
	A-7720-A24A501A		A-7720-B24A501A		A-7720-C24A501A		A-7720-D24A501A		A-7720-E24A501A		A-7720-F24A501A
	A-7720-A25A501A		A-7720-B25A501A		A-7720-C25A501A		A-7720-D25A501A		A-7720-E25A501A		A-7720-F25A501A
	A-7720-A26A501A		A-7720-B26A501A		A-7720-C26A501A		A-7720-D26A501A		A-7720-E26A501A		A-7720-F26A501A
	A-7720-A27A501A		A-7720-B27A501A		A-7720-C27A501A		A-7720-D27A501A		A-7720-E27A501A		A-7720-F27A501A
	A-7720-A28A501A		A-7720-B28A501A		A-7720-C28A501A		A-7720-D28A501A		A-7720-E28A501A		A-7720-F28A501A

REVISION: BB		ECR/ECN INFORMATION: EC No.: UCP2011-1314 DATE: 4/12/2011		TITLE: KK 100 IDT CONNECTOR ASSEMBLY				SHEET No. 7	
DOCUMENT NUMBER: SD-7720-001				CREATED / REVISED BY: MKIPPER		CHECKED BY: JBELL		APPROVED BY: FSMITH	

A-7720-ANH501B		A-7720-BNH501B		A-7720-CNH501B		A-7720-DNH501B		A-7720-ENH501B		A-7720-FNH501B	
HOUSING	7720-AN	HOUSING	7720-BN	HOUSING	7720-CN	HOUSING	7720-DN	HOUSING	7720-EN	HOUSING	7720-FN
TERM. NO	41138-H501	TERM. NO	41138-H501	TERM. NO	41138-H501	TERM. NO	41138-H501	TERM. NO	41138-H501	TERM. NO	41138-H501
PLATING:	501	PLATING:	501	PLATING:	501	PLATING:	501	PLATING:	501	PLATING:	501
COLOR	GREEN	COLOR	GREEN	COLOR	GREEN	COLOR	GREEN	COLOR	GREEN	COLOR	GREEN
MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:
	A-7720-A02H501B	22-45-8022	A-7720-B02H501B	22-45-7022	A-7720-C02H501B		A-7720-D02H501B	22-45-7026	A-7720-E02H501B	22-45-7028	A-7720-F02H501B
22-45-7035	A-7720-A03H501B	22-45-8032	A-7720-B03H501B		A-7720-C03H501B		A-7720-D03H501B	22-45-7036	A-7720-E03H501B	22-45-7038	A-7720-F03H501B
	A-7720-A04H501B	22-45-8042	A-7720-B04H501B		A-7720-C04H501B		A-7720-D04H501B	22-45-7046	A-7720-E04H501B	22-45-7048	A-7720-F04H501B
22-45-7055	A-7720-A05H501B	22-45-8052	A-7720-B05H501B		A-7720-C05H501B		A-7720-D05H501B	22-45-7056	A-7720-E05H501B	22-45-7058	A-7720-F05H501B
	A-7720-A06H501B		A-7720-B06H501B		A-7720-C06H501B		A-7720-D06H501B		A-7720-E06H501B	22-45-7068	A-7720-F06H501B
	A-7720-A07H501B		A-7720-B07H501B		A-7720-C07H501B		A-7720-D07H501B	22-45-7076	A-7720-E07H501B	22-45-7078	A-7720-F07H501B
	A-7720-A08H501B		A-7720-B08H501B	22-45-7082	A-7720-C08H501B	22-45-8087	A-7720-D08H501B	22-45-7086	A-7720-E08H501B	22-45-7088	A-7720-F08H501B
	A-7720-A09H501B		A-7720-B09H501B		A-7720-C09H501B		A-7720-D09H501B	22-45-7096	A-7720-E09H501B	22-45-7098	A-7720-F09H501B
	A-7720-A10H501B	22-45-8102	A-7720-B10H501B		A-7720-C10H501B		A-7720-D10H501B		A-7720-E10H501B	22-45-7108	A-7720-F10H501B
	A-7720-A11H501B		A-7720-B11H501B		A-7720-C11H501B		A-7720-D11H501B		A-7720-E11H501B	22-45-7118	A-7720-F11H501B
	A-7720-A12H501B		A-7720-B12H501B		A-7720-C12H501B		A-7720-D12H501B	22-45-7126	A-7720-E12H501B	22-45-7128	A-7720-F12H501B
	A-7720-A13H501B		A-7720-B13H501B		A-7720-C13H501B	22-45-8137	A-7720-D13H501B	22-45-7136	A-7720-E13H501B	22-45-7138	A-7720-F13H501B
	A-7720-A14H501B		A-7720-B14H501B		A-7720-C14H501B		A-7720-D14H501B		A-7720-E14H501B	22-45-7148	A-7720-F14H501B
	A-7720-A15H501B		A-7720-B15H501B		A-7720-C15H501B		A-7720-D15H501B		A-7720-E15H501B	22-45-7158	A-7720-F15H501B
	A-7720-A16H501B		A-7720-B16H501B		A-7720-C16H501B		A-7720-D16H501B		A-7720-E16H501B		A-7720-F16H501B
	A-7720-A17H501B		A-7720-B17H501B		A-7720-C17H501B		A-7720-D17H501B		A-7720-E17H501B		A-7720-F17H501B
	A-7720-A18H501B		A-7720-B18H501B		A-7720-C18H501B		A-7720-D18H501B		A-7720-E18H501B		A-7720-F18H501B
	A-7720-A19H501B		A-7720-B19H501B		A-7720-C19H501B		A-7720-D19H501B		A-7720-E19H501B		A-7720-F19H501B
	A-7720-A20H501B		A-7720-B20H501B		A-7720-C20H501B		A-7720-D20H501B		A-7720-E20H501B		A-7720-F20H501B
	A-7720-A21H501B		A-7720-B21H501B		A-7720-C21H501B		A-7720-D21H501B		A-7720-E21H501B		A-7720-F21H501B
	A-7720-A22H501B		A-7720-B22H501B		A-7720-C22H501B		A-7720-D22H501B		A-7720-E22H501B		A-7720-F22H501B
	A-7720-A23H501B		A-7720-B23H501B		A-7720-C23H501B		A-7720-D23H501B		A-7720-E23H501B		A-7720-F23H501B
	A-7720-A24H501B		A-7720-B24H501B		A-7720-C24H501B		A-7720-D24H501B		A-7720-E24H501B		A-7720-F24H501B
	A-7720-A25H501B		A-7720-B25H501B		A-7720-C25H501B		A-7720-D25H501B		A-7720-E25H501B		A-7720-F25H501B
	A-7720-A26H501B		A-7720-B26H501B		A-7720-C26H501B		A-7720-D26H501B		A-7720-E26H501B		A-7720-F26H501B
	A-7720-A27H501B		A-7720-B27H501B		A-7720-C27H501B		A-7720-D27H501B		A-7720-E27H501B		A-7720-F27H501B
22-45-7285	A-7720-A28H501B		A-7720-B28H501B		A-7720-C28H501B	22-45-8287	A-7720-D28H501B		A-7720-E28H501B		A-7720-F28H501B

<u>REVISION:</u> BB	<u>ECR/ECN INFORMATION:</u> <u>EC No.:</u> UCP2011-1314 <u>DATE:</u> 4/12/2011	<u>TITLE:</u> KK 100 IDT CONNECTOR ASSEMBLY		<u>SHEET No.</u> 8
<u>DOCUMENT NUMBER:</u> SD-7720-001		<u>CREATED / REVISED BY:</u> MKIPPER	<u>CHECKED BY:</u> JBELL	<u>APPROVED BY:</u> FSMITH
TEMPLATE FILENAME: PRODUCT_SPEC[SIZE_A](V.1).DOC				

A-7720-WANF501B		A-7720-WBNF501B		A-7720-WCNF501B		A-7720-WDNF501B		A-7720-WENF501B		A-7720-WFNF501B	
HOUSING	7720-WAN	HOUSING	7720-WBN	HOUSING	7720-WCN	HOUSING	7720-WDN	HOUSING	7720-WEN	HOUSING	7720-WFN
TERM. NO	41138-F501	TERM. NO	41138-F501	TERM. NO	41138-F501	TERM. NO	41138-F501	TERM. NO	41138-F501	TERM. NO	41138-F501
PLATING:	501	PLATING:	501	PLATING:	501	PLATING:	501	PLATING:	501	PLATING:	501
COLOR	BLACK	COLOR	BLACK	COLOR	BLACK	COLOR	BLACK	COLOR	BLACK	COLOR	BLACK
MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:
22-45-6021	A-7720-WA02F501B	22-45-6025	A-7720-WB02F501B	22-45-6026	A-7720-WC02F501B	22-45-6027	A-7720-WD02F501B	22-45-6028	A-7720-WE02F501B	22-45-6029	A-7720-WF02F501B
22-45-6031	A-7720-WA03F501B	22-45-6035	A-7720-WB03F501B	22-45-6036	A-7720-WC03F501B	22-45-6037	A-7720-WD03F501B	22-45-6038	A-7720-WE03F501B	22-45-6039	A-7720-WF03F501B
22-45-6041	A-7720-WA04F501B	22-45-6045	A-7720-WB04F501B	22-45-6046	A-7720-WC04F501B	22-45-6047	A-7720-WD04F501B	22-45-6048	A-7720-WE04F501B	22-45-6049	A-7720-WF04F501B
22-45-6051	A-7720-WA05F501B	22-45-6055	A-7720-WB05F501B	22-45-6056	A-7720-WC05F501B	22-45-6057	A-7720-WD05F501B	22-45-6058	A-7720-WE05F501B	22-45-6059	A-7720-WF05F501B
22-45-6061	A-7720-WA06F501B	22-45-6065	A-7720-WB06F501B	22-45-6066	A-7720-WC06F501B	22-45-6067	A-7720-WD06F501B	22-45-6068	A-7720-WE06F501B	22-45-6069	A-7720-WF06F501B
22-45-6071	A-7720-WA07F501B	22-45-6075	A-7720-WB07F501B	22-45-6076	A-7720-WC07F501B	22-45-6077	A-7720-WD07F501B	22-45-6078	A-7720-WE07F501B	22-45-6079	A-7720-WF07F501B
22-45-6081	A-7720-WA08F501B	22-45-6085	A-7720-WB08F501B	22-45-6086	A-7720-WC08F501B	22-45-6087	A-7720-WD08F501B	22-45-6088	A-7720-WE08F501B	22-45-6089	A-7720-WF08F501B
22-45-6091	A-7720-WA09F501B	22-45-6095	A-7720-WB09F501B	22-45-6096	A-7720-WC09F501B	22-45-6097	A-7720-WD09F501B	22-45-6098	A-7720-WE09F501B	22-45-6099	A-7720-WF09F501B
22-45-6101	A-7720-WA10F501B	22-45-6105	A-7720-WB10F501B	22-45-6106	A-7720-WC10F501B	22-45-6107	A-7720-WD10F501B	22-45-6108	A-7720-WE10F501B	22-45-6109	A-7720-WF10F501B
22-45-6111	A-7720-WA11F501B	22-45-6115	A-7720-WB11F501B	22-45-6116	A-7720-WC11F501B	22-45-6117	A-7720-WD11F501B	22-45-6118	A-7720-WE11F501B	22-45-6119	A-7720-WF11F501B
22-45-6121	A-7720-WA12F501B	22-45-6125	A-7720-WB12F501B	22-45-6126	A-7720-WC12F501B	22-45-6127	A-7720-WD12F501B	22-45-6128	A-7720-WE12F501B	22-45-6129	A-7720-WF12F501B
22-45-6131	A-7720-WA13F501B	22-45-6135	A-7720-WB13F501B	22-45-6136	A-7720-WC13F501B	22-45-6137	A-7720-WD13F501B	22-45-6138	A-7720-WE13F501B	22-45-6139	A-7720-WF13F501B
22-45-6141	A-7720-WA14F501B	22-45-6145	A-7720-WB14F501B	22-45-6146	A-7720-WC14F501B	22-45-6147	A-7720-WD14F501B	22-45-6148	A-7720-WE14F501B	22-45-6149	A-7720-WF14F501B
22-45-6151	A-7720-WA15F501B	22-45-6155	A-7720-WB15F501B	22-45-6156	A-7720-WC15F501B	22-45-6157	A-7720-WD15F501B	22-45-6158	A-7720-WE15F501B	22-45-6159	A-7720-WF15F501B
22-45-6161	A-7720-WA16F501B	22-45-6165	A-7720-WB16F501B	22-45-6166	A-7720-WC16F501B	22-45-6167	A-7720-WD16F501B	22-45-6168	A-7720-WE16F501B	22-45-6169	A-7720-WF16F501B
22-45-6171	A-7720-WA17F501B	22-45-6175	A-7720-WB17F501B	22-45-6176	A-7720-WC17F501B	22-45-6177	A-7720-WD17F501B	22-45-6178	A-7720-WE17F501B	22-45-6179	A-7720-WF17F501B
22-45-6181	A-7720-WA18F501B	22-45-6185	A-7720-WB18F501B	22-45-6186	A-7720-WC18F501B	22-45-6187	A-7720-WD18F501B	22-45-6188	A-7720-WE18F501B	22-45-6189	A-7720-WF18F501B
22-45-6191	A-7720-WA19F501B	22-45-6195	A-7720-WB19F501B	22-45-6196	A-7720-WC19F501B	22-45-6197	A-7720-WD19F501B	22-45-6198	A-7720-WE19F501B	22-45-6199	A-7720-WF19F501B
22-45-6201	A-7720-WA20F501B	22-45-6205	A-7720-WB20F501B	22-45-6206	A-7720-WC20F501B	22-45-6207	A-7720-WD20F501B	22-45-6208	A-7720-WE20F501B	22-45-6209	A-7720-WF20F501B
22-45-6211	A-7720-WA21F501B	22-45-6215	A-7720-WB21F501B	22-45-6216	A-7720-WC21F501B	22-45-6217	A-7720-WD21F501B	22-45-6218	A-7720-WE21F501B	22-45-6219	A-7720-WF21F501B
22-45-6221	A-7720-WA22F501B	22-45-6225	A-7720-WB22F501B	22-45-6226	A-7720-WC22F501B	22-45-6227	A-7720-WD22F501B	22-45-6228	A-7720-WE22F501B	22-45-6229	A-7720-WF22F501B
22-45-6231	A-7720-WA23F501B	22-45-6235	A-7720-WB23F501B	22-45-6236	A-7720-WC23F501B	22-45-6237	A-7720-WD23F501B	22-45-6238	A-7720-WE23F501B	22-45-6239	A-7720-WF23F501B
22-45-6241	A-7720-WA24F501B	22-45-6245	A-7720-WB24F501B	22-45-6246	A-7720-WC24F501B	22-45-6247	A-7720-WD24F501B	22-45-6248	A-7720-WE24F501B	22-45-6249	A-7720-WF24F501B
22-45-6251	A-7720-WA25F501B	22-45-6255	A-7720-WB25F501B	22-45-6256	A-7720-WC25F501B	22-45-6257	A-7720-WD25F501B	22-45-6258	A-7720-WE25F501B	22-45-6259	A-7720-WF25F501B
22-45-6261	A-7720-WA26F501B	22-45-6265	A-7720-WB26F501B	22-45-6266	A-7720-WC26F501B	22-45-6267	A-7720-WD26F501B	22-45-6268	A-7720-WE26F501B	22-45-6269	A-7720-WF26F501B
22-45-6271	A-7720-WA27F501B	22-45-6275	A-7720-WB27F501B	22-45-6276	A-7720-WC27F501B	22-45-6277	A-7720-WD27F501B	22-45-6278	A-7720-WE27F501B	22-45-6279	A-7720-WF27F501B
22-45-6281	A-7720-WA28F501B	22-45-6285	A-7720-WB28F501B	22-45-6286	A-7720-WC28F501B	22-45-6287	A-7720-WD28F501B	22-45-6288	A-7720-WE28F501B	22-45-6289	A-7720-WF28F501B

REVISION:		TITLE:		SHEET No.	
BB		KK 100 IDT CONNECTOR ASSEMBLY		9	
ECR/ECN INFORMATION:					
EC No.: UCP2011-1314					
DATE: 4/12/2011					
DOCUMENT NUMBER:		CREATED / REVISED BY:		CHECKED BY:	
SD-7720-001		MKIPPER		JBELL	
				APPROVED BY:	
				FSMITH	

A-7720-ANH503B		A-7720-BNH503B		A-7720-CNH503B		A-7720-DNH503B		A-7720-ENH503B		A-7720-FNH503B	
HOUSING	7720-AN	HOUSING	7720-BN	HOUSING	7720-CN	HOUSING	7720-DN	HOUSING	7720-EN	HOUSING	7720-FN
TERM. NO	41138-H503	TERM. NO	41138-H503	TERM. NO	41138-H503	TERM. NO	41138-H503	TERM. NO	41138-H503	TERM. NO	41138-H503
PLATING:	503	PLATING:	503	PLATING:	503	PLATING:	503	PLATING:	503	PLATING:	503
COLOR	GREEN	COLOR	GREEN	COLOR	GREEN	COLOR	GREEN	COLOR	GREEN	COLOR	GREEN
MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:
	A-7720-A02H503B		A-7720-B02H503B		A-7720-C02H503B		A-7720-D02H503B		A-7720-E02H503B		A-7720-F02H503B
	A-7720-A03H503B		A-7720-B03H503B	22-45-9032	A-7720-C03H503B		A-7720-D03H503B		A-7720-E03H503B		A-7720-F03H503B
	A-7720-A04H503B		A-7720-B04H503B	22-45-9042	A-7720-C04H503B		A-7720-D04H503B	22-45-9045	A-7720-E04H503B	22-45-9047	A-7720-F04H503B
	A-7720-A05H503B		A-7720-B05H503B		A-7720-C05H503B		A-7720-D05H503B	22-45-9055	A-7720-E05H503B	22-45-9057	A-7720-F05H503B
	A-7720-A06H503B		A-7720-B06H503B	22-45-9062	A-7720-C06H503B		A-7720-D06H503B	22-45-9065	A-7720-E06H503B	22-45-9067	A-7720-F06H503B
	A-7720-A07H503B		A-7720-B07H503B	22-45-9072	A-7720-C07H503B		A-7720-D07H503B		A-7720-E07H503B	22-45-9077	A-7720-F07H503B
	A-7720-A08H503B		A-7720-B08H503B	22-45-9082	A-7720-C08H503B		A-7720-D08H503B		A-7720-E08H503B	22-45-9087	A-7720-F08H503B
	A-7720-A09H503B		A-7720-B09H503B		A-7720-C09H503B		A-7720-D09H503B		A-7720-E09H503B		A-7720-F09H503B
	A-7720-A10H503B		A-7720-B10H503B	22-45-9102	A-7720-C10H503B		A-7720-D10H503B		A-7720-E10H503B		A-7720-F10H503B
	A-7720-A11H503B		A-7720-B11H503B		A-7720-C11H503B		A-7720-D11H503B		A-7720-E11H503B	22-45-9117	A-7720-F11H503B
	A-7720-A12H503B		A-7720-B12H503B		A-7720-C12H503B		A-7720-D12H503B		A-7720-E12H503B		A-7720-F12H503B
	A-7720-A13H503B		A-7720-B13H503B		A-7720-C13H503B		A-7720-D13H503B		A-7720-E13H503B		A-7720-F13H503B
	A-7720-A14H503B		A-7720-B14H503B		A-7720-C14H503B		A-7720-D14H503B		A-7720-E14H503B		A-7720-F14H503B
	A-7720-A15H503B		A-7720-B15H503B		A-7720-C15H503B		A-7720-D15H503B		A-7720-E15H503B		A-7720-F15H503B
	A-7720-A16H503B		A-7720-B16H503B		A-7720-C16H503B		A-7720-D16H503B		A-7720-E16H503B		A-7720-F16H503B
	A-7720-A17H503B		A-7720-B17H503B		A-7720-C17H503B		A-7720-D17H503B		A-7720-E17H503B		A-7720-F17H503B
	A-7720-A18H503B		A-7720-B18H503B		A-7720-C18H503B		A-7720-D18H503B		A-7720-E18H503B		A-7720-F18H503B
	A-7720-A19H503B		A-7720-B19H503B		A-7720-C19H503B		A-7720-D19H503B		A-7720-E19H503B		A-7720-F19H503B
	A-7720-A20H503B		A-7720-B20H503B		A-7720-C20H503B		A-7720-D20H503B		A-7720-E20H503B		A-7720-F20H503B
	A-7720-A21H503B		A-7720-B21H503B		A-7720-C21H503B		A-7720-D21H503B		A-7720-E21H503B		A-7720-F21H503B
	A-7720-A22H503B		A-7720-B22H503B		A-7720-C22H503B		A-7720-D22H503B		A-7720-E22H503B		A-7720-F22H503B
	A-7720-A23H503B		A-7720-B23H503B		A-7720-C23H503B		A-7720-D23H503B		A-7720-E23H503B		A-7720-F23H503B
	A-7720-A24H503B		A-7720-B24H503B		A-7720-C24H503B		A-7720-D24H503B		A-7720-E24H503B		A-7720-F24H503B
	A-7720-A25H503B		A-7720-B25H503B		A-7720-C25H503B		A-7720-D25H503B		A-7720-E25H503B		A-7720-F25H503B
	A-7720-A26H503B		A-7720-B26H503B		A-7720-C26H503B		A-7720-D26H503B		A-7720-E26H503B		A-7720-F26H503B
	A-7720-A27H503B		A-7720-B27H503B		A-7720-C27H503B		A-7720-D27H503B		A-7720-E27H503B		A-7720-F27H503B
	A-7720-A28H503B		A-7720-B28H503B		A-7720-C28H503B		A-7720-D28H503B		A-7720-E28H503B		A-7720-F28H503B

REVISION: BB	ECR/ECN INFORMATION:	TITLE: KK 100 IDT CONNECTOR ASSEMBLY	SHEET No. 10
	EC No.: UCP2011-1314 DATE: 4/12/2011		
DOCUMENT NUMBER: SD-7720-001		CREATED / REVISED BY: MKIPPER	CHECKED BY: JBELL
		APPROVED BY: FSMITH	

A-7720-ANH154C		A-7720-BNH154C		A-7720-CNH154C		A-7720-DNH154C		A-7720-ENH154C		A-7720-FNH154C	
HOUSING	7720-AN	HOUSING	7720-BN	HOUSING	7720-CN	HOUSING	7720-DN	HOUSING	7720-EN	HOUSING	7720-FN
TERM. NO	41512-H154	TERM. NO	41512-H154	TERM. NO	41512-H154	TERM. NO	41512-H154	TERM. NO	41512-H154	TERM. NO	41512-H154
PLATING:	154	PLATING:	154	PLATING:	154	PLATING:	154	PLATING:	154	PLATING:	154
COLOR	GREEN	COLOR	GREEN	COLOR	GREEN	COLOR	GREEN	COLOR	GREEN	COLOR	GREEN
MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:
	A-7720-A02H154C		A-7720-B02H154C	22-42-4022	A-7720-C02H154C		A-7720-D02H154C	22-42-4024	A-7720-E02H154C		A-7720-F02H154C
	A-7720-A03H154C		A-7720-B03H154C		A-7720-C03H154C		A-7720-D03H154C		A-7720-E03H154C		A-7720-F03H154C
	A-7720-A04H154C		A-7720-B04H154C		A-7720-C04H154C	22-42-4043	A-7720-D04H154C	22-42-4044	A-7720-E04H154C		A-7720-F04H154C
	A-7720-A05H154C		A-7720-B05H154C		A-7720-C05H154C		A-7720-D05H154C		A-7720-E05H154C		A-7720-F05H154C
	A-7720-A06H154C		A-7720-B06H154C		A-7720-C06H154C		A-7720-D06H154C	22-42-4064	A-7720-E06H154C		A-7720-F06H154C
	A-7720-A07H154C		A-7720-B07H154C		A-7720-C07H154C	22-42-4073	A-7720-D07H154C	22-42-4074	A-7720-E07H154C		A-7720-F07H154C
	A-7720-A08H154C		A-7720-B08H154C		A-7720-C08H154C		A-7720-D08H154C	22-42-4084	A-7720-E08H154C		A-7720-F08H154C
	A-7720-A09H154C		A-7720-B09H154C		A-7720-C09H154C		A-7720-D09H154C		A-7720-E09H154C		A-7720-F09H154C
	A-7720-A10H154C		A-7720-B10H154C		A-7720-C10H154C	22-42-4103	A-7720-D10H154C	22-42-4104	A-7720-E10H154C		A-7720-F10H154C
	A-7720-A11H154C		A-7720-B11H154C		A-7720-C11H154C	22-42-4113	A-7720-D11H154C	22-42-4114	A-7720-E11H154C		A-7720-F11H154C
	A-7720-A12H154C		A-7720-B12H154C		A-7720-C12H154C	22-42-4123	A-7720-D12H154C	22-42-4124	A-7720-E12H154C		A-7720-F12H154C
	A-7720-A13H154C		A-7720-B13H154C		A-7720-C13H154C	22-42-4133	A-7720-D13H154C	22-42-4134	A-7720-E13H154C		A-7720-F13H154C
	A-7720-A14H154C		A-7720-B14H154C		A-7720-C14H154C	22-42-4143	A-7720-D14H154C	22-42-4144	A-7720-E14H154C		A-7720-F14H154C
	A-7720-A15H154C		A-7720-B15H154C		A-7720-C15H154C	22-42-4153	A-7720-D15H154C		A-7720-E15H154C		A-7720-F15H154C
	A-7720-A16H154C		A-7720-B16H154C		A-7720-C16H154C		A-7720-D16H154C	22-42-4164	A-7720-E16H154C		A-7720-F16H154C
	A-7720-A17H154C		A-7720-B17H154C		A-7720-C17H154C		A-7720-D17H154C		A-7720-E17H154C		A-7720-F17H154C
	A-7720-A18H154C		A-7720-B18H154C		A-7720-C18H154C		A-7720-D18H154C	22-42-4184	A-7720-E18H154C		A-7720-F18H154C
	A-7720-A19H154C		A-7720-B19H154C		A-7720-C19H154C		A-7720-D19H154C		A-7720-E19H154C		A-7720-F19H154C
	A-7720-A20H154C		A-7720-B20H154C		A-7720-C20H154C		A-7720-D20H154C	22-42-4204	A-7720-E20H154C		A-7720-F20H154C
	A-7720-A21H154C		A-7720-B21H154C		A-7720-C21H154C		A-7720-D21H154C	22-42-4214	A-7720-E21H154C		A-7720-F21H154C
	A-7720-A22H154C		A-7720-B22H154C		A-7720-C22H154C		A-7720-D22H154C		A-7720-E22H154C		A-7720-F22H154C
	A-7720-A23H154C		A-7720-B23H154C		A-7720-C23H154C		A-7720-D23H154C		A-7720-E23H154C		A-7720-F23H154C
	A-7720-A24H154C		A-7720-B24H154C		A-7720-C24H154C	22-42-4243	A-7720-D24H154C		A-7720-E24H154C		A-7720-F24H154C
	A-7720-A25H154C		A-7720-B25H154C		A-7720-C25H154C		A-7720-D25H154C		A-7720-E25H154C		A-7720-F25H154C
	A-7720-A26H154C		A-7720-B26H154C		A-7720-C26H154C	22-42-4263	A-7720-D26H154C		A-7720-E26H154C		A-7720-F26H154C
	A-7720-A27H154C		A-7720-B27H154C		A-7720-C27H154C		A-7720-D27H154C		A-7720-E27H154C		A-7720-F27H154C
	A-7720-A28H154C		A-7720-B28H154C		A-7720-C28H154C		A-7720-D28H154C		A-7720-E28H154C		A-7720-F28H154C

REVISION: BB		ECR/ECN INFORMATION: EC No.: UCP2011-1314 DATE: 4/12/2011		TITLE: KK 100 IDT CONNECTOR ASSEMBLY				SHEET No. 11	
DOCUMENT NUMBER: SD-7720-001				CREATED / REVISED BY: MKIPPER		CHECKED BY: JBELL		APPROVED BY: FSMITH	

A-7720-ANF154C		A-7720-BNF154C		A-7720-CNF154C		A-7720-DNF154C		A-7720-ENF154C		A-7720-FNF154C	
HOUSING	7720-AN	HOUSING	7720-BN	HOUSING	7720-CN	HOUSING	7720-DN	HOUSING	7720-EN	HOUSING	7720-FN
TERM. NO	41512-F154	TERM. NO	41512-F154	TERM. NO	41512-F154	TERM. NO	41512-F154	TERM. NO	41512-F154	TERM. NO	41512-F154
PLATING:	154	PLATING:	154	PLATING:	154	PLATING:	154	PLATING:	154	PLATING:	154
COLOR	BLACK	COLOR	BLACK	COLOR	BLACK	COLOR	BLACK	COLOR	BLACK	COLOR	BLACK
MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:
	A-7720-A02F154C		A-7720-B02F154C		A-7720-C02F154C		A-7720-D02F154C	22-42-5024	A-7720-E02F154C		A-7720-F02F154C
	A-7720-A03F154C		A-7720-B03F154C		A-7720-C03F154C		A-7720-D03F154C	22-42-5034	A-7720-E03F154C		A-7720-F03F154C
	A-7720-A04F154C		A-7720-B04F154C		A-7720-C04F154C		A-7720-D04F154C	22-42-5044	A-7720-E04F154C		A-7720-F04F154C
	A-7720-A05F154C		A-7720-B05F154C		A-7720-C05F154C		A-7720-D05F154C	22-42-5054	A-7720-E05F154C		A-7720-F05F154C
	A-7720-A06F154C		A-7720-B06F154C		A-7720-C06F154C		A-7720-D06F154C	22-42-5064	A-7720-E06F154C		A-7720-F06F154C
	A-7720-A07F154C		A-7720-B07F154C		A-7720-C07F154C		A-7720-D07F154C	22-42-5074	A-7720-E07F154C		A-7720-F07F154C
	A-7720-A08F154C		A-7720-B08F154C		A-7720-C08F154C		A-7720-D08F154C	22-42-5084	A-7720-E08F154C		A-7720-F08F154C
	A-7720-A09F154C		A-7720-B09F154C		A-7720-C09F154C		A-7720-D09F154C	22-42-5094	A-7720-E09F154C		A-7720-F09F154C
	A-7720-A10F154C		A-7720-B10F154C		A-7720-C10F154C		A-7720-D10F154C	22-42-5104	A-7720-E10F154C		A-7720-F10F154C
	A-7720-A11F154C		A-7720-B11F154C		A-7720-C11F154C		A-7720-D11F154C	22-42-5114	A-7720-E11F154C		A-7720-F11F154C
	A-7720-A12F154C		A-7720-B12F154C		A-7720-C12F154C		A-7720-D12F154C	22-42-5124	A-7720-E12F154C		A-7720-F12F154C
	A-7720-A13F154C		A-7720-B13F154C		A-7720-C13F154C		A-7720-D13F154C	22-42-5134	A-7720-E13F154C		A-7720-F13F154C
	A-7720-A14F154C		A-7720-B14F154C		A-7720-C14F154C		A-7720-D14F154C	22-42-5144	A-7720-E14F154C		A-7720-F14F154C
	A-7720-A15F154C		A-7720-B15F154C		A-7720-C15F154C		A-7720-D15F154C	22-42-5154	A-7720-E15F154C		A-7720-F15F154C
	A-7720-A16F154C		A-7720-B16F154C		A-7720-C16F154C		A-7720-D16F154C	22-42-5164	A-7720-E16F154C		A-7720-F16F154C
	A-7720-A17F154C		A-7720-B17F154C		A-7720-C17F154C		A-7720-D17F154C	22-42-5174	A-7720-E17F154C		A-7720-F17F154C
	A-7720-A18F154C		A-7720-B18F154C		A-7720-C18F154C		A-7720-D18F154C	22-42-5184	A-7720-E18F154C		A-7720-F18F154C
	A-7720-A19F154C		A-7720-B19F154C		A-7720-C19F154C		A-7720-D19F154C	22-42-5194	A-7720-E19F154C		A-7720-F19F154C
	A-7720-A20F154C		A-7720-B20F154C		A-7720-C20F154C		A-7720-D20F154C	22-42-5204	A-7720-E20F154C		A-7720-F20F154C
	A-7720-A21F154C		A-7720-B21F154C		A-7720-C21F154C		A-7720-D21F154C	22-42-5214	A-7720-E21F154C		A-7720-F21F154C
	A-7720-A22F154C		A-7720-B22F154C		A-7720-C22F154C		A-7720-D22F154C		A-7720-E22F154C		A-7720-F22F154C
	A-7720-A23F154C		A-7720-B23F154C		A-7720-C23F154C		A-7720-D23F154C		A-7720-E23F154C		A-7720-F23F154C
	A-7720-A24F154C		A-7720-B24F154C		A-7720-C24F154C		A-7720-D24F154C	22-42-5244	A-7720-E24F154C		A-7720-F24F154C
	A-7720-A25F154C		A-7720-B25F154C		A-7720-C25F154C		A-7720-D25F154C		A-7720-E25F154C		A-7720-F25F154C
	A-7720-A26F154C		A-7720-B26F154C		A-7720-C26F154C		A-7720-D26F154C		A-7720-E26F154C		A-7720-F26F154C
	A-7720-A27F154C		A-7720-B27F154C		A-7720-C27F154C		A-7720-D27F154C	22-42-5274	A-7720-E27F154C		A-7720-F27F154C
	A-7720-A28F154C		A-7720-B28F154C		A-7720-C28F154C		A-7720-D28F154C		A-7720-E28F154C		A-7720-F28F154C

<u>REVISION:</u> BB	<u>ECR/ECN INFORMATION:</u> <u>EC No.:</u> UCP2011-1314 <u>DATE:</u> 4/12/2011	<u>TITLE:</u> KK 100 IDT CONNECTOR ASSEMBLY		<u>SHEET No.</u> 12
<u>DOCUMENT NUMBER:</u> SD-7720-001		<u>CREATED / REVISED BY:</u> MKIPPER	<u>CHECKED BY:</u> JBELL	<u>APPROVED BY:</u> FSMITH
TEMPLATE FILENAME: PRODUCT_SPEC[SIZE_A](V.1).DOC				

A-7720-WANF154C		A-7720-WBNF154C		A-7720-WCNF154C		A-7720-WDNF154C		A-7720-WENF154C		A-7720-WFNF154C	
HOUSING	7720-WAN	HOUSING	7720-WBN	HOUSING	7720-WCN	HOUSING	7720-WDN	HOUSING	7720-WEN	HOUSING	7720-WFN
TERM. NO	41512-F154	TERM. NO	41512-F154	TERM. NO	41512-F154	TERM. NO	41512-F154	TERM. NO	41512-F154	TERM. NO	41512-F154
PLATING:	154	PLATING:	154	PLATING:	154	PLATING:	154	PLATING:	154	PLATING:	154
COLOR	BLACK	COLOR	BLACK	COLOR	BLACK	COLOR	BLACK	COLOR	BLACK	COLOR	BLACK
MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:
22-42-7020	A-7720-WA02F154C	22-42-7021	A-7720-WB02F154C	22-42-7022	A-7720-WC02F154C	22-42-7023	A-7720-WD02F154C	22-42-7024	A-7720-WE02F154C	22-42-7025	A-7720-WF02F154C
22-42-7030	A-7720-WA03F154C	22-42-7031	A-7720-WB03F154C	22-42-7032	A-7720-WC03F154C	22-42-7033	A-7720-WD03F154C	22-42-7034	A-7720-WE03F154C	22-42-7035	A-7720-WF03F154C
22-42-7040	A-7720-WA04F154C	22-42-7041	A-7720-WB04F154C	22-42-7042	A-7720-WC04F154C	22-42-7043	A-7720-WD04F154C	22-42-7044	A-7720-WE04F154C	22-42-7045	A-7720-WF04F154C
22-42-7050	A-7720-WA05F154C	22-42-7051	A-7720-WB05F154C	22-42-7052	A-7720-WC05F154C	22-42-7053	A-7720-WD05F154C	22-42-7054	A-7720-WE05F154C	22-42-7055	A-7720-WF05F154C
22-42-7060	A-7720-WA06F154C	22-42-7061	A-7720-WB06F154C	22-42-7062	A-7720-WC06F154C	22-42-7063	A-7720-WD06F154C	22-42-7064	A-7720-WE06F154C	22-42-7065	A-7720-WF06F154C
22-42-7070	A-7720-WA07F154C	22-42-7071	A-7720-WB07F154C	22-42-7072	A-7720-WC07F154C	22-42-7073	A-7720-WD07F154C	22-42-7074	A-7720-WE07F154C		A-7720-WF07F154C
22-42-7080	A-7720-WA08F154C	22-42-7081	A-7720-WB08F154C	22-42-7082	A-7720-WC08F154C	22-42-7083	A-7720-WD08F154C	22-42-7084	A-7720-WE08F154C	22-42-7085	A-7720-WF08F154C
22-42-7090	A-7720-WA09F154C	22-42-7091	A-7720-WB09F154C	22-42-7092	A-7720-WC09F154C	22-42-7093	A-7720-WD09F154C	22-42-7094	A-7720-WE09F154C	22-42-7095	A-7720-WF09F154C
22-42-7100	A-7720-WA10F154C	22-42-7101	A-7720-WB10F154C	22-42-7102	A-7720-WC10F154C	22-42-7103	A-7720-WD10F154C	22-42-7104	A-7720-WE10F154C	22-42-7105	A-7720-WF10F154C
22-42-7110	A-7720-WA11F154C	22-42-7111	A-7720-WB11F154C	22-42-7112	A-7720-WC11F154C	22-42-7113	A-7720-WD11F154C	22-42-7114	A-7720-WE11F154C	22-42-7115	A-7720-WF11F154C
22-42-7120	A-7720-WA12F154C	22-42-7121	A-7720-WB12F154C	22-42-7122	A-7720-WC12F154C	22-42-7123	A-7720-WD12F154C	22-42-7124	A-7720-WE12F154C	22-42-7125	A-7720-WF12F154C
22-42-7130	A-7720-WA13F154C	22-42-7131	A-7720-WB13F154C	22-42-7132	A-7720-WC13F154C	22-42-7133	A-7720-WD13F154C	22-42-7134	A-7720-WE13F154C	22-42-7135	A-7720-WF13F154C
22-42-7140	A-7720-WA14F154C	22-42-7141	A-7720-WB14F154C	22-42-7142	A-7720-WC14F154C	22-42-7143	A-7720-WD14F154C	22-42-7144	A-7720-WE14F154C	22-42-7145	A-7720-WF14F154C
22-42-7150	A-7720-WA15F154C	22-42-7151	A-7720-WB15F154C	22-42-7152	A-7720-WC15F154C	22-42-7153	A-7720-WD15F154C	22-42-7154	A-7720-WE15F154C	22-42-7155	A-7720-WF15F154C
22-42-7160	A-7720-WA16F154C	22-42-7161	A-7720-WB16F154C	22-42-7162	A-7720-WC16F154C	22-42-7163	A-7720-WD16F154C	22-42-7164	A-7720-WE16F154C		A-7720-WF16F154C
22-42-7170	A-7720-WA17F154C	22-42-7171	A-7720-WB17F154C	22-42-7172	A-7720-WC17F154C	22-42-7173	A-7720-WD17F154C	22-42-7174	A-7720-WE17F154C	22-42-7175	A-7720-WF17F154C
22-42-7180	A-7720-WA18F154C	22-42-7181	A-7720-WB18F154C	22-42-7182	A-7720-WC18F154C	22-42-7183	A-7720-WD18F154C	22-42-7184	A-7720-WE18F154C	22-42-7185	A-7720-WF18F154C
22-42-7190	A-7720-WA19F154C	22-42-7191	A-7720-WB19F154C	22-42-7192	A-7720-WC19F154C	22-42-7193	A-7720-WD19F154C	22-42-7194	A-7720-WE19F154C	22-42-7195	A-7720-WF19F154C
22-42-7200	A-7720-WA20F154C	22-42-7201	A-7720-WB20F154C	22-42-7202	A-7720-WC20F154C	22-42-7203	A-7720-WD20F154C	22-42-7204	A-7720-WE20F154C	22-42-7205	A-7720-WF20F154C
22-42-7210	A-7720-WA21F154C	22-42-7211	A-7720-WB21F154C	22-42-7212	A-7720-WC21F154C	22-42-7213	A-7720-WD21F154C	22-42-7214	A-7720-WE21F154C	22-42-7215	A-7720-WF21F154C
22-42-7220	A-7720-WA22F154C	22-42-7221	A-7720-WB22F154C	22-42-7222	A-7720-WC22F154C	22-42-7223	A-7720-WD22F154C	22-42-7224	A-7720-WE22F154C	22-42-7225	A-7720-WF22F154C
22-42-7230	A-7720-WA23F154C	22-42-7231	A-7720-WB23F154C	22-42-7232	A-7720-WC23F154C	22-42-7233	A-7720-WD23F154C	22-42-7234	A-7720-WE23F154C	22-42-7235	A-7720-WF23F154C
22-42-7240	A-7720-WA24F154C	22-42-7241	A-7720-WB24F154C	22-42-7242	A-7720-WC24F154C	22-42-7243	A-7720-WD24F154C	22-42-7244	A-7720-WE24F154C	22-42-7245	A-7720-WF24F154C
22-42-7250	A-7720-WA25F154C	22-42-7251	A-7720-WB25F154C	22-42-7252	A-7720-WC25F154C	22-42-7253	A-7720-WD25F154C	22-42-7254	A-7720-WE25F154C	22-42-7255	A-7720-WF25F154C
22-42-7260	A-7720-WA26F154C	22-42-7261	A-7720-WB26F154C	22-42-7262	A-7720-WC26F154C	22-42-7263	A-7720-WD26F154C	22-42-7264	A-7720-WE26F154C	22-42-7265	A-7720-WF26F154C
22-42-7270	A-7720-WA27F154C	22-42-7271	A-7720-WB27F154C	22-42-7272	A-7720-WC27F154C	22-42-7273	A-7720-WD27F154C	22-42-7274	A-7720-WE27F154C	22-42-7275	A-7720-WF27F154C
22-42-7280	A-7720-WA28F154C	22-42-7281	A-7720-WB28F154C	22-42-7282	A-7720-WC28F154C	22-42-7283	A-7720-WD28F154C	22-42-7284	A-7720-WE28F154C	22-42-7285	A-7720-WF28F154C

<u>REVISION:</u> BB	<u>ECR/ECN INFORMATION:</u> <u>EC No.:</u> UCP2011-1314 <u>DATE:</u> 4/12/2011	<u>TITLE:</u> KK 100 IDT CONNECTOR ASSEMBLY		<u>SHEET No.</u> 13
<u>DOCUMENT NUMBER:</u> SD-7720-001		<u>CREATED / REVISED BY:</u> MKIPPER	<u>CHECKED BY:</u> JBELL	<u>APPROVED BY:</u> FSMITH
TEMPLATE FILENAME: PRODUCT_SPEC[SIZE_A](V.1).DOC				

A-7720-ANA228A		A-7720-BNA228A		A-7720-CNA228A		A-7720-DNA228A		A-7720-ENA228A		A-7720-FNA228A	
HOUSING	7720-AN	HOUSING	7720-BN	HOUSING	7720-CN	HOUSING	7720-DN	HOUSING	7720-EN	HOUSING	7720-FN
TERM. NO	7691-A228	TERM. NO	7691-A228	TERM. NO	7691-A228	TERM. NO	7691-A228	TERM. NO	7691-A228	TERM. NO	7691-A228
PLATING:	228	PLATING:	228	PLATING:	228	PLATING:	228	PLATING:	228	PLATING:	228
COLOR	BROWN	COLOR	BROWN	COLOR	BROWN	COLOR	BROWN	COLOR	BROWN	COLOR	BROWN
MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:
	A-7720-A02A228A		A-7720-B02A228A		A-7720-C02A228A		A-7720-D02A228A		A-7720-E02A228A	22-45-9029	A-7720-F02A228A
	A-7720-A03A228A		A-7720-B03A228A		A-7720-C03A228A	22-45-9030	A-7720-D03A228A		A-7720-E03A228A	22-45-9039	A-7720-F03A228A
	A-7720-A04A228A		A-7720-B04A228A	22-45-9041	A-7720-C04A228A	22-45-9040	A-7720-D04A228A		A-7720-E04A228A	22-45-9049	A-7720-F04A228A
	A-7720-A05A228A		A-7720-B05A228A		A-7720-C05A228A	22-45-9050	A-7720-D05A228A		A-7720-E05A228A	22-45-9059	A-7720-F05A228A
	A-7720-A06A228A		A-7720-B06A228A		A-7720-C06A228A		A-7720-D06A228A		A-7720-E06A228A	22-45-9069	A-7720-F06A228A
	A-7720-A07A228A		A-7720-B07A228A		A-7720-C07A228A		A-7720-D07A228A		A-7720-E07A228A	22-45-9079	A-7720-F07A228A
	A-7720-A08A228A		A-7720-B08A228A		A-7720-C08A228A	22-45-9080	A-7720-D08A228A		A-7720-E08A228A	22-45-9089	A-7720-F08A228A
	A-7720-A09A228A		A-7720-B09A228A		A-7720-C09A228A		A-7720-D09A228A		A-7720-E09A228A	22-45-9099	A-7720-F09A228A
	A-7720-A10A228A		A-7720-B10A228A		A-7720-C10A228A		A-7720-D10A228A		A-7720-E10A228A	22-45-9109	A-7720-F10A228A
	A-7720-A11A228A		A-7720-B11A228A		A-7720-C11A228A		A-7720-D11A228A		A-7720-E11A228A	22-45-9119	A-7720-F11A228A
	A-7720-A12A228A		A-7720-B12A228A		A-7720-C12A228A		A-7720-D12A228A		A-7720-E12A228A	22-45-9129	A-7720-F12A228A
	A-7720-A13A228A		A-7720-B13A228A		A-7720-C13A228A		A-7720-D13A228A		A-7720-E13A228A	22-45-9139	A-7720-F13A228A
	A-7720-A14A228A		A-7720-B14A228A		A-7720-C14A228A		A-7720-D14A228A		A-7720-E14A228A	22-45-9149	A-7720-F14A228A
	A-7720-A15A228A		A-7720-B15A228A		A-7720-C15A228A		A-7720-D15A228A		A-7720-E15A228A	22-45-9159	A-7720-F15A228A
	A-7720-A16A228A		A-7720-B16A228A		A-7720-C16A228A		A-7720-D16A228A		A-7720-E16A228A	22-45-9169	A-7720-F16A228A
	A-7720-A17A228A		A-7720-B17A228A		A-7720-C17A228A		A-7720-D17A228A		A-7720-E17A228A		A-7720-F17A228A
	A-7720-A18A228A		A-7720-B18A228A		A-7720-C18A228A		A-7720-D18A228A		A-7720-E18A228A		A-7720-F18A228A
	A-7720-A19A228A		A-7720-B19A228A		A-7720-C19A228A		A-7720-D19A228A		A-7720-E19A228A		A-7720-F19A228A
	A-7720-A20A228A		A-7720-B20A228A		A-7720-C20A228A		A-7720-D20A228A		A-7720-E20A228A		A-7720-F20A228A
	A-7720-A21A228A		A-7720-B21A228A		A-7720-C21A228A		A-7720-D21A228A		A-7720-E21A228A		A-7720-F21A228A
	A-7720-A22A228A		A-7720-B22A228A		A-7720-C22A228A		A-7720-D22A228A		A-7720-E22A228A		A-7720-F22A228A
	A-7720-A23A228A		A-7720-B23A228A		A-7720-C23A228A		A-7720-D23A228A		A-7720-E23A228A		A-7720-F23A228A
	A-7720-A24A228A		A-7720-B24A228A		A-7720-C24A228A		A-7720-D24A228A		A-7720-E24A228A		A-7720-F24A228A
	A-7720-A25A228A		A-7720-B25A228A		A-7720-C25A228A		A-7720-D25A228A		A-7720-E25A228A		A-7720-F25A228A
	A-7720-A26A228A		A-7720-B26A228A		A-7720-C26A228A		A-7720-D26A228A		A-7720-E26A228A		A-7720-F26A228A
	A-7720-A27A228A		A-7720-B27A228A		A-7720-C27A228A		A-7720-D27A228A		A-7720-E27A228A		A-7720-F27A228A
	A-7720-A28A228A		A-7720-B28A228A		A-7720-C28A228A		A-7720-D28A228A		A-7720-E28A228A		A-7720-F28A228A

REVISION: BB		ECR/ECN INFORMATION: EC No.: UCP2011-1314 DATE: 4/12/2011		TITLE: KK 100 IDT CONNECTOR ASSEMBLY				SHEET No. 14	
DOCUMENT NUMBER: SD-7720-001				CREATED / REVISED BY: MKIPPER		CHECKED BY: JBELL		APPROVED BY: FSMITH	

A-7720-ANH208B		A-7720-BNH208B		A-7720-CNH208B		A-7720-DNH208B		A-7720-ENH208B		A-7720-FNH208B	
HOUSING	7720-AN	HOUSING	7720-BN	HOUSING	7720-CN	HOUSING	7720-DN	HOUSING	7720-EN	HOUSING	7720-FN
TERM. NO	41138-H208	TERM. NO	41138-H208	TERM. NO	41138-H208	TERM. NO	41138-H208	TERM. NO	41138-H208	TERM. NO	41138-H208
PLATING:	208	PLATING:	208	PLATING:	208	PLATING:	208	PLATING:	208	PLATING:	208
COLOR	GREEN	COLOR	GREEN	COLOR	GREEN	COLOR	GREEN	COLOR	GREEN	COLOR	GREEN
MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:	MATL NO	ENG NO:
	A-7720-A02H208B		A-7720-B02H208B		A-7720-C02H208B		A-7720-D02H208B		A-7720-E02H208B		A-7720-F02H208B
	A-7720-A03H208B		A-7720-B03H208B		A-7720-C03H208B		A-7720-D03H208B		A-7720-E03H208B		A-7720-F03H208B
	A-7720-A04H208B		A-7720-B04H208B		A-7720-C04H208B		A-7720-D04H208B		A-7720-E04H208B	22-45-9048	A-7720-F04H208B
	A-7720-A05H208B		A-7720-B05H208B	22-45-5053	A-7720-C05H208B		A-7720-D05H208B		A-7720-E05H208B		A-7720-F05H208B
	A-7720-A06H208B		A-7720-B06H208B		A-7720-C06H208B		A-7720-D06H208B		A-7720-E06H208B	22-45-9068	A-7720-F06H208B
	A-7720-A07H208B		A-7720-B07H208B		A-7720-C07H208B		A-7720-D07H208B		A-7720-E07H208B		A-7720-F07H208B
	A-7720-A08H208B		A-7720-B08H208B		A-7720-C08H208B		A-7720-D08H208B		A-7720-E08H208B		A-7720-F08H208B
	A-7720-A09H208B		A-7720-B09H208B		A-7720-C09H208B		A-7720-D09H208B		A-7720-E09H208B		A-7720-F09H208B
	A-7720-A10H208B		A-7720-B10H208B		A-7720-C10H208B		A-7720-D10H208B		A-7720-E10H208B		A-7720-F10H208B
	A-7720-A11H208B		A-7720-B11H208B		A-7720-C11H208B		A-7720-D11H208B		A-7720-E11H208B		A-7720-F11H208B
	A-7720-A12H208B		A-7720-B12H208B		A-7720-C12H208B		A-7720-D12H208B		A-7720-E12H208B		A-7720-F12H208B
	A-7720-A13H208B		A-7720-B13H208B		A-7720-C13H208B		A-7720-D13H208B		A-7720-E13H208B		A-7720-F13H208B
	A-7720-A14H208B		A-7720-B14H208B		A-7720-C14H208B		A-7720-D14H208B		A-7720-E14H208B		A-7720-F14H208B
	A-7720-A15H208B		A-7720-B15H208B		A-7720-C15H208B		A-7720-D15H208B		A-7720-E15H208B		A-7720-F15H208B
	A-7720-A16H208B		A-7720-B16H208B		A-7720-C16H208B		A-7720-D16H208B		A-7720-E16H208B	22-45-9168	A-7720-F16H208B
	A-7720-A17H208B		A-7720-B17H208B		A-7720-C17H208B		A-7720-D17H208B		A-7720-E17H208B		A-7720-F17H208B
	A-7720-A18H208B		A-7720-B18H208B		A-7720-C18H208B		A-7720-D18H208B		A-7720-E18H208B		A-7720-F18H208B
	A-7720-A19H208B		A-7720-B19H208B		A-7720-C19H208B		A-7720-D19H208B		A-7720-E19H208B		A-7720-F19H208B
	A-7720-A20H208B		A-7720-B20H208B		A-7720-C20H208B		A-7720-D20H208B		A-7720-E20H208B		A-7720-F20H208B
	A-7720-A21H208B		A-7720-B21H208B		A-7720-C21H208B		A-7720-D21H208B		A-7720-E21H208B		A-7720-F21H208B
	A-7720-A22H208B		A-7720-B22H208B		A-7720-C22H208B		A-7720-D22H208B		A-7720-E22H208B		A-7720-F22H208B
	A-7720-A23H208B		A-7720-B23H208B		A-7720-C23H208B		A-7720-D23H208B		A-7720-E23H208B		A-7720-F23H208B
	A-7720-A24H208B		A-7720-B24H208B		A-7720-C24H208B		A-7720-D24H208B		A-7720-E24H208B		A-7720-F24H208B
	A-7720-A25H208B		A-7720-B25H208B		A-7720-C25H208B		A-7720-D25H208B		A-7720-E25H208B		A-7720-F25H208B
	A-7720-A26H208B		A-7720-B26H208B		A-7720-C26H208B		A-7720-D26H208B		A-7720-E26H208B		A-7720-F26H208B
	A-7720-A27H208B		A-7720-B27H208B		A-7720-C27H208B		A-7720-D27H208B		A-7720-E27H208B		A-7720-F27H208B
	A-7720-A28H208B		A-7720-B28H208B		A-7720-C28H208B		A-7720-D28H208B		A-7720-E28H208B		A-7720-F28H208B

REVISION:	ECR/ECN INFORMATION:	TITLE:	SHEET No.
BB	EC No.: UCP2011-1314 DATE: 4/12/2011	KK 100 IDT CONNECTOR ASSEMBLY	15
DOCUMENT NUMBER:	CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:
SD-7720-001	MKIPPER	JBELL	FSMITH

[illegible]

<u>REVISION:</u> BB	<u>ECR/ECN INFORMATION:</u> <u>EC No.:</u> UCP2011-1314 <u>DATE:</u> 4/12/2011	<u>TITLE:</u> KK 100 IDT CONNECTOR ASSEMBLY			<u>SHEET No.</u> 16
<u>DOCUMENT NUMBER:</u> SD-7720-001		<u>CREATED / REVISED BY:</u> MKIPPER	<u>CHECKED BY:</u> JBELL	<u>APPROVED BY:</u> FSMITH	

[illegible]

<u>REVISION:</u> BB	<u>ECR/ECN INFORMATION:</u> <u>EC No.:</u> UCP2011-1314 <u>DATE:</u> 4/12/2011	<u>TITLE:</u> KK 100 IDT CONNECTOR ASSEMBLY			<u>SHEET No.</u> 17
<u>DOCUMENT NUMBER:</u> SD-7720-001		<u>CREATED / REVISED BY:</u> MKIPPER	<u>CHECKED BY:</u> JBELL	<u>APPROVED BY:</u> FSMITH	

MATL NO	ENG NO:	HOUSING	TERM. NO	COLOR	PLATING:	MOLDED VOID	TERMINAL VOID	
022421175	A-7720-F17H154B-51A	7720-F17-51	41138-H(154)	GREEN	154	1,17	1,17	
050290032	A-7720-E17H154B-51A	7720-E17-51	41138-H(154)	GREEN	154	1,17	1,17	
050291615	A-7720-E19H154B-51A	7720-E19-51	41138-H(154)	GREEN	154	1, 19	1, 19	
050348528	A-7720-F03A154A-2A	7720-F03-2	7691-A(154)	BROWN	154	2	2	
050348532	A-7720-F04A154A-51A	7720-F04-51	7691-A(154)	BROWN	154	2,3	2,3	
050362456	A-7720-WC05F154B-51A	7720-WC05-51	41188-F(154)	BLACK	154	2,4	2,4	

REVISION: BB	ECR/ECN INFORMATION: EC No.: UCP2011-1314 DATE: 4/12/2011	TITLE: KK 100 IDT CONNECTOR ASSEMBLY	SHEET No. 18
DOCUMENT NUMBER: SD-7720-001	CREATED / REVISED BY: MKIPPER	CHECKED BY: JBELL	APPROVED BY: FSMITH

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

22-42-3064