







NOTES:

1. MATERIAL AND FINISH:
  - A. RJ45 PLUG : CLEAR POLYCARBONATE (PC).
  - B. BOOT : CLEAR POLYCARBONATE (PC),
  - C. CONTACTS: COPPER ALLOY, FINISH: SELECTIVE GOLD PLATING.
  - D. CABLE JACKET: LS0H OR PVC.
2. PACKAGING:
 



PATCH CORD IS INDIVIDUALLY COILED, SECURED WITH A CABLE TIE AND IS PACKED IN A SEALED BAG.

THE QUANTITY OF PATCH CORDS IN THE CARTON BOX WILL DEPEND UPON THE LENGTH OF THE CORDS.
3. IMPERIAL LENGTH PATCH CORDS (PVC SHEATH ONLY) MPN NUMBERS SHOULD BE GENERATED FROM THE LENGTH OF 1FT TO 65FT, 0.5FT INCREMENT FOR ANY OF THESE LENGTHS (FOR EXAMPLE: 2.5FT, 3.5FT ETC) ARE NOT AVAILABLE TO ORDER.
4. TESTING PROCEDURE FOR 1 FEET PATCH CORD
 

1 FT (FEET) PATCH CORD SHOULD BE TESTED ONLY FOR WIRE MAP AND PERFORMANCE IS NOT CERTIFIED
5. REFER SHEET 2 AND 3 FOR STANDARD PATCH CORD LENGTHS IN METER AND COLORS REFER SHEET 4 FOR THE IMPERIAL LENGTH PART NUMBER MATRIX.
6. PATCH CORD ARE SUITABLE FOR EIA 568A OR 568B APPLICATIONS.
7. CONTACT MOLEX FOR LENGTHS OR COLORS NOT SPECIFIED ON SHEET 2 AND 3.



L +150.0  
0.0



WIRING SEQUENCE:

PIN NO.	WIRE COLOR
1	WHITE/ORANGE
2	ORANGE
3	WHITE/GREEN
4	BLUE
5	WHITE/BLUE
6	GREEN
7	WHITE/BROWN
8	BROWN

<b>SYMBOLS</b> ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	DIMENSION UNITS: <b>mm</b> SCALE: <b>NTS</b>	CURRENT REV DESC: EC NO: 629245 DRWN: NBP 2019/12/16 CHK'D: RCG 2020/01/31 APPR: RCG 2020/01/31	 PATCH CORD CAT 5E U/UTP PATCH CORD		
	GENERAL TOLERANCES (UNLESS SPECIFIED) ANGULAR TOL ± ° 4 PLACES ± 3 PLACES ± 2 PLACES ± 1 PLACE ± 0.5 0 PLACES ±	INITIAL REVISION: DRWN: PS03 2010/11/19 APPR: RGOPALAKRISH 2010/12/28	PRODUCT CUSTOMER DRAWING			
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	THIRD ANGLE PROJECTION	DRAWING: <b>A1-SIZE</b> SERIES: <b>18191</b>	DOCUMENT NUMBER: <b>SD-18191-001</b> DOC TYPE: <b>PSD</b> DOC PART: <b>001</b> REVISION: <b>C2</b>	MATERIAL NUMBER: <b>SEE CHART</b> CUSTOMER: <b>GENERAL MARKET</b>	SHEET NUMBER: <b>1 OF 4</b>

SL NO.	MPN NO.	SAP NO.	DESCRIPTION	LENGTH IN METER 'L'
1	PCD-01000-OC	181910585	PCORD C5E U/UTP LSOH RED 0.5M	0.5
2	PCD-01000-OE	181910586	PCORD C5E U/UTP LSOH GRAY 0.5M	
3	PCD-01000-OH	181910587	PCORD C5E U/UTP LSOH BLUE 0.5M	
4	PCD-01000-OJ	181910588	PCORD C5E U/UTP LSOH GREEN 0.5M	
5	PCD-01000-OK	181910589	PCORD C5E U/UTP LSOH YELLOW 0.5M	
6	PCD-01000-BK	181910593	PCORD C5E U/UTP LSOH BLACK 0.5M	
7	PCD-01001-OC	181910594	PCORD C5E U/UTP LSOH RED 1.0M	1.0
8	PCD-01001-OE	181910595	PCORD C5E U/UTP LSOH GRAY 1.0M	
9	PCD-01001-OH	181910596	PCORD C5E U/UTP LSOH BLUE 1.0M	
10	PCD-01001-OJ	181910597	PCORD C5E U/UTP LSOH GREEN 1.0M	
11	PCD-01001-OK	181910598	PCORD C5E U/UTP LSOH YELLOW 1.0M	
12	PCD-01001-BK	181910602	PCORD C5E U/UTP LSOH BLACK 1.0M	
13	PCD-01002-OC	181910603	PCORD C5E U/UTP LSOH RED 1.5M	1.5
14	PCD-01002-OE	181910604	PCORD C5E U/UTP LSOH GRAY 1.5M	
15	PCD-01002-OH	181910605	PCORD C5E U/UTP LSOH BLUE 1.5M	
16	PCD-01002-OJ	181910606	PCORD C5E U/UTP LSOH GREEN 1.5M	
17	PCD-01002-OK	181910607	PCORD C5E U/UTP LSOH YELLOW 1.5M	
18	PCD-01002-BK	181910611	PCORD C5E U/UTP LSOH BLACK 1.5M	
19	PCD-01003-OC	181910612	PCORD C5E U/UTP LSOH RED 2.0M	2.0
20	PCD-01003-OE	181910613	PCORD C5E U/UTP LSOH GRAY 2.0M	
21	PCD-01003-OH	181910614	PCORD C5E U/UTP LSOH BLUE 2.0M	
22	PCD-01003-OJ	181910615	PCORD C5E U/UTP LSOH GREEN 2.0M	
23	PCD-01003-OK	181910616	PCORD C5E U/UTP LSOH YELLOW 2.0M	
24	PCD-01003-BK	181910620	PCORD C5E U/UTP LSOH BLACK 2.0M	
25	PCD-01005-OC	181910630	PCORD C5E U/UTP LSOH RED 3.0M	3.0
26	PCD-01005-OE	181910631	PCORD C5E U/UTP LSOH GRAY 3.0M	
27	PCD-01005-OH	181910632	PCORD C5E U/UTP LSOH BLUE 3.0M	
28	PCD-01005-OJ	181910633	PCORD C5E U/UTP LSOH GREEN 3.0M	
29	PCD-01005-OK	181910634	PCORD C5E U/UTP LSOH YELLOW 3.0M	
30	PCD-01005-BK	181910638	PCORD C5E U/UTP LSOH BLACK 3.0M	
31	PCD-01009-OC	181910666	PCORD C5E U/UTP LSOH RED 5.0M	5.0
32	PCD-01009-OE	181910667	PCORD C5E U/UTP LSOH GRAY 5.0M	
33	PCD-01009-OH	181910668	PCORD C5E U/UTP LSOH BLUE 5.0M	
34	PCD-01009-OJ	181910669	PCORD C5E U/UTP LSOH GREEN 5.0M	
35	PCD-01009-OK	181910670	PCORD C5E U/UTP LSOH YELLOW 5.0M	
36	PCD-01009-BK	181910674	PCORD C5E U/UTP LSOH BLACK 5.0M	
37	PCD-01013-OC	181910702	PCORD C5E U/UTP LSOH RED 7.0M	7.0
38	PCD-01013-OE	181910703	PCORD C5E U/UTP LSOH GRAY 7.0M	
39	PCD-01013-OH	181910704	PCORD C5E U/UTP LSOH BLUE 7.0M	
40	PCD-01013-OJ	181910705	PCORD C5E U/UTP LSOH GREEN 7.0M	
41	PCD-01013-OK	181910706	PCORD C5E U/UTP LSOH YELLOW 7.0M	
42	PCD-01013-BK	181910710	PCORD C5E U/UTP LSOH BLACK 7.0M	
43	PCD-01019-OC	181910756	PCORD C5E U/UTP LSOH RED 10.0M	10.0
44	PCD-01019-OE	181910757	PCORD C5E U/UTP LSOH GRAY 10.0M	
45	PCD-01019-OH	181910758	PCORD C5E U/UTP LSOH BLUE 10.0M	
46	PCD-01019-OJ	181910759	PCORD C5E U/UTP LSOH GREEN 10.0M	
47	PCD-01019-OK	181910760	PCORD C5E U/UTP LSOH YELLOW 10.0M	
48	PCD-01019-BK	181910764	PCORD C5E U/UTP LSOH BLACK 10.0M	

SL NO.	MPN NO.	SAP NO.	DESCRIPTION	LENGTH IN METER 'L'
49	PCD-01040-OC	181910945	PCORD C5E U/UTP PVC RED 0.5M	0.5
50	PCD-01040-OE	181910946	PCORD C5E U/UTP PVC GRAY 0.5M	
51	PCD-01040-OH	181910947	PCORD C5E U/UTP PVC BLUE 0.5M	
52	PCD-01040-OJ	181910948	PCORD C5E U/UTP PVC GREEN 0.5M	
53	PCD-01040-OK	181910949	PCORD C5E U/UTP PVC YELLOW 0.5M	
54	PCD-01040-BK	181910953	PCORD C5E U/UTP PVC BLACK 0.5M	
55	PCD-01041-OC	181910954	PCORD C5E U/UTP PVC RED 1.0M	1.0
56	PCD-01041-OE	181910955	PCORD C5E U/UTP PVC GRAY 1.0M	
57	PCD-01041-OH	181910956	PCORD C5E U/UTP PVC BLUE 1.0M	
58	PCD-01041-OJ	181910957	PCORD C5E U/UTP PVC GREEN 1.0M	
59	PCD-01041-OK	181910958	PCORD C5E U/UTP PVC YELLOW 1.0M	
60	PCD-01041-BK	181910962	PCORD C5E U/UTP PVC BLACK 1.0M	
61	PCD-01047-OC	181911008	PCORD C5E U/UTP PVC RED 1.5M	1.5
62	PCD-01047-OE	181911009	PCORD C5E U/UTP PVC GRAY 1.5M	
63	PCD-01047-OH	181911010	PCORD C5E U/UTP PVC BLUE 1.5M	
64	PCD-01047-OJ	181911011	PCORD C5E U/UTP PVC GREEN 1.5M	
65	PCD-01047-OK	181911012	PCORD C5E U/UTP PVC YELLOW 1.5M	
66	PCD-01047-BK	181911016	PCORD C5E U/UTP PVC BLACK 1.5M	
67	PCD-01042-OC	181910963	PCORD C5E U/UTP PVC RED 2.0M	2.0
68	PCD-01042-OE	181910964	PCORD C5E U/UTP PVC GRAY 2.0M	
69	PCD-01042-OH	181910965	PCORD C5E U/UTP PVC BLUE 2.0M	
70	PCD-01042-OJ	181910966	PCORD C5E U/UTP PVC GREEN 2.0M	
71	PCD-01042-OK	181910967	PCORD C5E U/UTP PVC YELLOW 2.0M	
72	PCD-01042-BK	181910971	PCORD C5E U/UTP PVC BLACK 2.0M	
73	PCD-01043-OC	181910972	PCORD C5E U/UTP PVC RED 3.0M	3.0
74	PCD-01043-OE	181910973	PCORD C5E U/UTP PVC GRAY 3.0M	
75	PCD-01043-OH	181910974	PCORD C5E U/UTP PVC BLUE 3.0M	
76	PCD-01043-OJ	181910975	PCORD C5E U/UTP PVC GREEN 3.0M	
77	PCD-01043-OK	181910976	PCORD C5E U/UTP PVC YELLOW 3.0M	
78	PCD-01043-BK	181910980	PCORD C5E U/UTP PVC BLACK 3.0M	
79	PCD-01044-OC	181910981	PCORD C5E U/UTP PVC RED 5.0M	5.0
80	PCD-01044-OE	181910982	PCORD C5E U/UTP PVC GRAY 5.0M	
81	PCD-01044-OH	181910983	PCORD C5E U/UTP PVC BLUE 5.0M	
82	PCD-01044-OJ	181910984	PCORD C5E U/UTP PVC GREEN 5.0M	
83	PCD-01044-OK	181910985	PCORD C5E U/UTP PVC YELLOW 5.0M	
84	PCD-01044-BK	181910989	PCORD C5E U/UTP PVC BLACK 5.0M	
85	PCD-01045-OC	181910990	PCORD C5E U/UTP PVC RED 7.0M	7.0
86	PCD-01045-OE	181910991	PCORD C5E U/UTP PVC GRAY 7.0M	
87	PCD-01045-OH	181910992	PCORD C5E U/UTP PVC BLUE 7.0M	
88	PCD-01045-OJ	181910993	PCORD C5E U/UTP PVC GREEN 7.0M	
89	PCD-01045-OK	181910994	PCORD C5E U/UTP PVC YELLOW 7.0M	
90	PCD-01045-BK	181910998	PCORD C5E U/UTP PVC BLACK 7.0M	
91	PCD-01046-OC	181910999	PCORD C5E U/UTP PVC RED 10.0M	10.0
92	PCD-01046-OE	181911000	PCORD C5E U/UTP PVC GRAY 10.0M	
93	PCD-01046-OH	181911001	PCORD C5E U/UTP PVC BLUE 10.0M	
94	PCD-01046-OJ	181911002	PCORD C5E U/UTP PVC GREEN 10.0M	
95	PCD-01046-OK	181911003	PCORD C5E U/UTP PVC YELLOW 10.0M	
96	PCD-01046-BK	181911007	PCORD C5E U/UTP PVC BLACK 10.0M	

<b>SYMBOLS</b> = 0 = 0 = 0 = 0 = 0 = 0 = 0 = 0 = 0	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC:		 <b>PATCH CORD CAT 5E U/UTP PATCH CORD</b> <b>PRODUCT CUSTOMER DRAWING</b>	
	DIMENSION UNITS	SCALE	EC NO: 629245			
	mm	NTS	DRWN: NBP	2019/12/16		
	GENERAL TOLERANCES (UNLESS SPECIFIED)		CHK'D: RCG	2020/01/31		
	ANGULAR TOL ± °		APPR: RCG	2020/01/31		
4 PLACES ±		INITIAL REVISION:				
3 PLACES ±		DRWN: PS03	2010/11/19			
2 PLACES ±		APPR: RGOPALAKRISH	2010/12/28			
1 PLACE ± 0.5		DOCUMENT NUMBER				
0 PLACES ±		SD-18191-001				
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
			A1-SIZE 18191	SEE CHART	GENERAL MARKET	2 OF 4


SL NO.	MPN NO.	SAP NO.	DESCRIPTION	LENGTH IN METER 'L'
1	PCD-01000-OC-I	181911305	PCORD C5E U/UTP LS0H RED 0.5M-INDIA	0.5
2	PCD-01000-OE-I	181911306	PCORD C5E U/UTP LS0H GRAY 0.5M-INDIA	
3	PCD-01000-OH-I	181911307	PCORD C5E U/UTP LS0H BLUE 0.5M-INDIA	
4	PCD-01000-OJ-I	181911308	PCORD C5E U/UTP LS0H GREEN 0.5M-INDIA	
5	PCD-01000-OK-I	181911309	PCORD C5E U/UTP LS0H YELLOW 0.5M-INDIA	
6	PCD-01000-BK-I	181911313	PCORD C5E U/UTP LS0H BLACK 0.5M-INDIA	
7	PCD-01001-OC-I	181911314	PCORD C5E U/UTP LS0H RED 1.0M-INDIA	1.0
8	PCD-01001-OE-I	181911315	PCORD C5E U/UTP LS0H GRAY 1.0M-INDIA	
9	PCD-01001-OH-I	181911316	PCORD C5E U/UTP LS0H BLUE 1.0M-INDIA	
10	PCD-01001-OJ-I	181911317	PCORD C5E U/UTP LS0H GREEN 1.0M-INDIA	
11	PCD-01001-OK-I	181911318	PCORD C5E U/UTP LS0H YELLOW 1.0M-INDIA	
12	PCD-01001-BK-I	181911322	PCORD C5E U/UTP LS0H BLACK 1.0M-INDIA	
13	PCD-01002-OC-I	181911323	PCORD C5E U/UTP LS0H RED 1.5M-INDIA	1.5
14	PCD-01002-OE-I	181911324	PCORD C5E U/UTP LS0H GRAY 1.5M-INDIA	
15	PCD-01002-OH-I	181911325	PCORD C5E U/UTP LS0H BLUE 1.5M-INDIA	
16	PCD-01002-OJ-I	181911326	PCORD C5E U/UTP LS0H YELLOW 1.5M-INDIA	
17	PCD-01002-OK-I	181911327	PCORD C5E U/UTP LS0H YELLOW 1.5M-INDIA	
18	PCD-01002-BK-I	181911331	PCORD C5E U/UTP LS0H BLACK 1.5M-INDIA	
19	PCD-01003-OC-I	181911332	PCORD C5E U/UTP LS0H RED 2.0M-INDIA	2.0
20	PCD-01003-OE-I	181911333	PCORD C5E U/UTP LS0H GRAY 2.0M-INDIA	
21	PCD-01003-OH-I	181911334	PCORD C5E U/UTP LS0H BLUE 2.0M-INDIA	
22	PCD-01003-OJ-I	181911335	PCORD C5E U/UTP LS0H GREEN 2.0M-INDIA	
23	PCD-01003-OK-I	181911336	PCORD C5E U/UTP LS0H YELLOW 2.0M-INDIA	
24	PCD-01003-BK-I	181911340	PCORD C5E U/UTP LS0H BLACK 2.0M-INDIA	
25	PCD-01005-OC-I	181911350	PCORD C5E U/UTP LS0H RED 3.0M-INDIA	3.0
26	PCD-01005-OE-I	181911351	PCORD C5E U/UTP LS0H GRAY 3.0M-INDIA	
27	PCD-01005-OH-I	181911352	PCORD C5E U/UTP LS0H BLUE 3.0M-INDIA	
28	PCD-01005-OJ-I	181911353	PCORD C5E U/UTP LS0H GREEN 3.0M-INDIA	
29	PCD-01005-OK-I	181911354	PCORD C5E U/UTP LS0H YELLOW 3.0M-INDIA	
30	PCD-01005-BK-I	181911358	PCORD C5E U/UTP LS0H BLACK 3.0M-INDIA	
31	PCD-01009-OC-I	181911386	PCORD C5E U/UTP LS0H RED 5.0M-INDIA	5.0
32	PCD-01009-OE-I	181911387	PCORD C5E U/UTP LS0H GRAY 5.0M-INDIA	
33	PCD-01009-OH-I	181911388	PCORD C5E U/UTP LS0H BLUE 5.0M-INDIA	
34	PCD-01009-OJ-I	181911389	PCORD C5E U/UTP LS0H GREEN 5.0M-INDIA	
35	PCD-01009-OK-I	181911390	PCORD C5E U/UTP LS0H YELLOW 5.0M-INDIA	
36	PCD-01009-BK-I	181911394	PCORD C5E U/UTP LS0H BLACK 5.0M-INDIA	
37	PCD-01013-OC-I	181911422	PCORD C5E U/UTP LS0H RED 7.0M-INDIA	7.0
38	PCD-01013-OE-I	181911423	PCORD C5E U/UTP LS0H GRAY 7.0M-INDIA	
39	PCD-01013-OH-I	181911424	PCORD C5E U/UTP LS0H BLUE 7.0M-INDIA	
40	PCD-01013-OJ-I	181911425	PCORD C5E U/UTP LS0H GREEN 7.0M-INDIA	
41	PCD-01013-OK-I	181911426	PCORD C5E U/UTP LS0H YELLOW 7.0M-INDIA	
42	PCD-01013-BK-I	181911430	PCORD C5E U/UTP LS0H BLACK 7.0M-INDIA	
43	PCD-01019-OC-I	181911476	PCORD C5E U/UTP LS0H RED 10.0M-INDIA	10.0
44	PCD-01019-OE-I	181911477	PCORD C5E U/UTP LS0H GRAY 10.0M-INDIA	
45	PCD-01019-OH-I	181911478	PCORD C5E U/UTP LS0H BLUE 10.0M-INDIA	
46	PCD-01019-OJ-I	181911479	PCORD C5E U/UTP LS0H GREEN 10.0M-INDIA	
47	PCD-01019-OK-I	181911480	PCORD C5E U/UTP LS0H YELLOW 10.0M-INDIA	
48	PCD-01019-BK-I	181911484	PCORD C5E U/UTP LS0H BLACK 10.0M-INDIA	

SL NO.	MPN NO.	SAP NO.	DESCRIPTION	LENGTH IN METER 'L'
49	PCD-01040-OC-I	181911665	PCORD C5E U/UTP PVC RED 0.5M-INDIA	0.5
50	PCD-01040-OE-I	181911666	PCORD C5E U/UTP PVC GRAY 0.5M-INDIA	
51	PCD-01040-OH-I	181911667	PCORD C5E U/UTP PVC BLUE 0.5M-INDIA	
52	PCD-01040-OJ-I	181911668	PCORD C5E U/UTP PVC GREEN 0.5M-INDIA	
53	PCD-01040-OK-I	181911669	PCORD C5E U/UTP PVC YELLOW 0.5M-INDIA	
54	PCD-01040-BK-I	181911673	PCORD C5E U/UTP PVC BLACK 0.5M-INDIA	
55	PCD-01041-OC-I	181911674	PCORD C5E U/UTP PVC RED 1.0M-INDIA	1.0
56	PCD-01041-OE-I	181911675	PCORD C5E U/UTP PVC GRAY 1.0M-INDIA	
57	PCD-01041-OH-I	181911676	PCORD C5E U/UTP PVC BLUE 1.0M-INDIA	
58	PCD-01041-OJ-I	181911677	PCORD C5E U/UTP PVC GREEN 1.0M-INDIA	
59	PCD-01041-OK-I	181911678	PCORD C5E U/UTP PVC YELLOW 1.0M-INDIA	
60	PCD-01041-BK-I	181911682	PCORD C5E U/UTP PVC BLACK 1.0M-INDIA	
61	PCD-01047-OC-I	181911683	PCORD C5E U/UTP PVC RED 1.5M-INDIA	1.5
62	PCD-01047-OE-I	181911684	PCORD C5E U/UTP PVC GRAY 1.5M-INDIA	
63	PCD-01047-OH-I	181911685	PCORD C5E U/UTP PVC BLUE 1.5M-INDIA	
64	PCD-01047-OJ-I	181911686	PCORD C5E U/UTP PVC GREEN 1.5M-INDIA	
65	PCD-01047-OK-I	181911687	PCORD C5E U/UTP PVC YELLOW 1.5M-INDIA	
66	PCD-01047-BK-I	181911691	PCORD C5E U/UTP PVC BLACK 1.5M-INDIA	
67	PCD-01042-OC-I	181911692	PCORD C5E U/UTP PVC RED 2.0M-INDIA	2.0
68	PCD-01042-OE-I	181911693	PCORD C5E U/UTP PVC GRAY 2.0M-INDIA	
69	PCD-01042-OH-I	181911694	PCORD C5E U/UTP PVC BLUE 2.0M-INDIA	
70	PCD-01042-OJ-I	181911695	PCORD C5E U/UTP PVC GREEN 2.0M-INDIA	
71	PCD-01042-OK-I	181911696	PCORD C5E U/UTP PVC YELLOW 2.0M-INDIA	
72	PCD-01042-BK-I	181911700	PCORD C5E U/UTP PVC BLACK 2.0M-INDIA	
73	PCD-01043-OC-I	181911710	PCORD C5E U/UTP PVC RED 3.0M-INDIA	3.0
74	PCD-01043-OE-I	181911711	PCORD C5E U/UTP PVC GRAY 3.0M-INDIA	
75	PCD-01043-OH-I	181911712	PCORD C5E U/UTP PVC BLUE 3.0M-INDIA	
76	PCD-01043-OJ-I	181911713	PCORD C5E U/UTP PVC GREEN 3.0M-INDIA	
77	PCD-01043-OK-I	181911714	PCORD C5E U/UTP PVC YELLOW 3.0M-INDIA	
78	PCD-01043-BK-I	181911718	PCORD C5E U/UTP PVC BLACK 3.0M-INDIA	
79	PCD-01044-OC-I	181911746	PCORD C5E U/UTP PVC RED 5.0M-INDIA	5.0
80	PCD-01044-OE-I	181911747	PCORD C5E U/UTP PVC GRAY 5.0M-INDIA	
81	PCD-01044-OH-I	181911748	PCORD C5E U/UTP PVC BLUE 5.0M-INDIA	
82	PCD-01044-OJ-I	181911749	PCORD C5E U/UTP PVC GREEN 5.0M-INDIA	
83	PCD-01044-OK-I	181911750	PCORD C5E U/UTP PVC YELLOW 5.0M-INDIA	
84	PCD-01044-BK-I	181911754	PCORD C5E U/UTP PVC BLACK 5.0M-INDIA	
85	PCD-01045-OC-I	181911782	PCORD C5E U/UTP PVC RED 7.0M-INDIA	7.0
86	PCD-01045-OE-I	181911783	PCORD C5E U/UTP PVC GRAY 7.0M-INDIA	
87	PCD-01045-OH-I	181911784	PCORD C5E U/UTP PVC BLUE 7.0M-INDIA	
88	PCD-01045-OJ-I	181911785	PCORD C5E U/UTP PVC GREEN 7.0M-INDIA	
89	PCD-01045-OK-I	181911786	PCORD C5E U/UTP PVC YELLOW 7.0M-INDIA	
90	PCD-01045-BK-I	181911790	PCORD C5E U/UTP PVC BLACK 7.0M-INDIA	
91	PCD-01046-OC-I	181911836	PCORD C5E U/UTP PVC RED 10.0M-INDIA	10.0
92	PCD-01046-OE-I	181911837	PCORD C5E U/UTP PVC GRAY 10.0M-INDIA	
93	PCD-01046-OH-I	181911838	PCORD C5E U/UTP PVC BLUE 10.0M-INDIA	
94	PCD-01046-OJ-I	181911839	PCORD C5E U/UTP PVC GREEN 10.0M-INDIA	
95	PCD-01046-OK-I	181911840	PCORD C5E U/UTP PVC YELLOW 10.0M-INDIA	
96	PCD-01046-BK-I	181911844	PCORD C5E U/UTP PVC BLACK 10.0M-INDIA	

<b>SYMBOLS</b> = 0 = 0 = 0 = 0 = 0 = 0 = 0 = 0 = 0	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION DIMENSION UNITS: <b>mm</b> SCALE: <b>NTS</b> GENERAL TOLERANCES (UNLESS SPECIFIED) ANGULAR TOL ± °	CURRENT REV DESC:  EC NO: 629245 DRWN: NBP 2019/12/16 CHK'D: RCG 2020/01/31 APPR: RCG 2020/01/31  INITIAL REVISION: DRWN: PS03 2010/11/19 APPR: RGOPALAKRISH 2010/12/28	  PATCH CORD CAT 5E U/UTP PATCH CORD  PRODUCT CUSTOMER DRAWING					
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	THIRD ANGLE PROJECTION 		DRAWING SERIES <b>A1-SIZE 18191</b>	DOCUMENT NUMBER <b>SD-18191-001</b>	DOC TYPE <b>PSD</b>	DOC PART <b>001</b>	REVISION <b>C2</b>
	MATERIAL NUMBER <b>SEE CHART</b>	CUSTOMER <b>GENERAL MARKET</b>		SHEET NUMBER <b>3 OF 4</b>				

NOTE:  
IMPERIAL LENGTH PART NUMBER MATRIX CAN BE GENERATED BASED  
ON THE BELOW PROVIDED PART MATRIX

MPN NO.	SAP NO.	DESCRIPTION	REMARKS
PCD-01FXX-XX	18191XXXX	PCORD CAT 5E UTP XXX XXX "XX"FT	REFER NOTE 3 & 4



- COLOR CODE**
- OW-WHITE
  - BK-BLACK
  - OH-BLUE
  - OE-GRAY
  - OJ-GREEN
  - OK-YELLOW
  - ON-ORANGE
  - OP-PURPLE
  - OC-RED
  - PK-PINK

PRE-RELEASE  
REFERENCE  
USE ONLY

SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC:			molex			
	DIMENSION UNITS	SCALE	REV	DATE	DESC	DOC NUMBER	DOC TYPE	DOC PART	REVISION
$\nabla = 0$	mm	NTS				SD-18191-001	PSD	001	C2
$\nabla = 0$	GENERAL TOLERANCES (UNLESS SPECIFIED)			EC NO: 629245		PRODUCT CUSTOMER DRAWING			
$\nabla = 0$	ANGULAR TOL $\pm$ °			DRWN: NBP	2019/12/16				
$\nabla = 0$	4 PLACES $\pm$			CHK'D: RCG	2020/01/31				
$\nabla = 0$	3 PLACES $\pm$			APPR: RCG	2020/01/31				
$\nabla = 0$	2 PLACES $\pm$			INITIAL REVISION:					
$\nabla = 0$	1 PLACE $\pm$ 0.5			DRWN: PS03	2010/11/19				
$\nabla = 0$	0 PLACES $\pm$			APPR: RGOPALAKRISH	2010/12/28				
$\square = 0$	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER	
$\nabla = 0$				A1-SIZE	18191	SEE CHART	GENERAL MARKET	4 OF 4	

DOCUMENT STATUS	RELEASE DATE

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[18191-0596](#) [181910614](#) [18191-0614](#) [18191-0631](#)