



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	7/14/2022	DGUITADAURO



PART NUMBER	LENGTH	
	FEET	METERS
USBCA2-MF-1FT	1.0	0.30 ±.02
USBCA2-MF-3FT	3.0	0.91 ±.02
USBCA2-MF-6FT	6.0	1.83 ±.03
USBCA2-MF-10FT	10.0	3.05 ±.03

- NOTES:
- CABLE ASSEMBLY SHALL MEET USB 2.0 REQUIREMENTS.
  - CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
  - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**  
EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5]   FRACTIONS ± 1/32 .XX = ±.02 [5]   ANGLES ± 1° .XXX = ±.005 [13]	APPROVALS DRAWN BY DMAY CHECKED BY HBAKKE APPROVED BY DGUITADAURO	DATE 6/21/2022 7/13/2022 7/14/2022	 an INFINITO brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY USB
	COLOR VARIATIONS MAY OCCUR		PRODUCT DESCRIPTION USB3.0 A MALE TO A FEMALE CABLE ALUMINUM SHELL WITH COTTON BRAID
	THIRD-ANGLE PROJECTION 	SIZE <b>A</b>	CAGE CODE <b>43321</b>

SCALE: NONE | CAD FILE: USBCA2-MF.SLDDRW | SHEET 1 OF 1