


# CARLING TECHNOLOGIES Rocker Switches



## T SERIES: MINI-TIPPETTE SNAP-IN ROCKER SWITCHES

- Contact Rating: 10A 250VAC; 15A 125VAC; 3/4HP 125-250VAC
- Termination: .250 QC Tab
- Actuator/Bezel color: Black/Black

For quantities of 250 and up, call for quote.

MOUSER STOCK NO.	Carling Technologies Part No.	Fig.	Contact Form	Circuit	Price Each			
					1	25	50	100
691-TA201-TB-B	TA201-TB-B	A	SPST	On-None-Off	1.72	1.38	.86	.68
691-TB201-TB-B	TB201-TB-B	A	SPDT	On-None-On	2.31	1.84	1.17	.90
691-TC201-TB-B	TC201-TB-B	A	SPDT	On-Off-On	2.38	1.90	1.19	.95

## LTA SERIES: MINI-TIPPETTE ILLUMINATED SNAP-IN ROCKER SWITCHES

- Circuit: SPST OFF-ON
- Contact Rating: 10A 250VAC; 15A 125VAC; 3/4HP 125-250VAC

- Actuator: Translucent
- Termination: .250 QC Tab
- Bezel color: Black



For quantities of 250 and up, call for quote.

MOUSER STOCK NO.	Carling Technologies Part No.	Fig.	Lens Color	Lamp Type and Voltage	Price Each			
					1	25	50	100
691-LTA201TAB/12V	LTA201-TA-B/12V	B	Amber	12 V Incandes. lamp	4.05	3.14	2.75	2.46
691-LTA201TRB/12V	LTA201-TR-B/12V	B	Red	12 V Incandes. lamp	4.05	3.14	2.75	2.46
691-LTA201TAB/125N	LTA201-TA-B/125N	B	Amber	125 V Neon lamp	3.80	2.96	2.59	2.22
691-LTA201TRB/125N	LTA201-TR-B/125N	B	Red	125 V Neon lamp	3.80	2.96	2.59	2.22
691-LTA201TAB/250N	LTA201-TA-B/250N	B	Amber	250 V Neon lamp	3.80	2.96	2.59	2.22
691-LTA201TRB/250N	LTA201-TR-B/250N	B	Red	250 V Neon lamp	3.80	2.96	2.59	2.22

## TIG SERIES: FULL SIZE TIPPETTE ROCKER SWITCHES

- Rating: 10A @250VAC/15A@125VAC/3/4HP 125-250VAC
- Termination: .250 QC Tab

- Actuator: Black, glossy finish, smooth curved
- Bracket: Black glossy finish

( ) Momentary

For quantities of 250 and up, call for quote.

MOUSER STOCK NO.	Carling Technologies Part No.	Fig.	Contact Form	Circuit	Price Each			
					1	25	50	100
691-TIGK516SBLNBL	TIGK51-6S-BL-NBL	C	DPST	ON-OFF	6.32	4.72	4.10	3.82
691-TIGK5B6SBLNBL	TIGK5B-6S-BL-NBL	C	DPST	(ON)-OFF	6.32	4.72	4.10	3.82
691-TIGK5M6SBLNBL	TIGK5M-6S-BL-NBL	C	DPST	ON-(OFF)	6.32	4.72	4.10	3.82
691-TIGL516SBLNBL	TIGL51-6S-BL-NBL	C	DPST	ON-ON	5.83	4.43	3.73	3.50
691-TIGL5B6SBLNBL	TIGL5B-6S-BL-NBL	C	DPST	ON-(ON)	6.32	4.72	4.10	3.84
691-TIGM516SBLNBL	TIGM51-6S-BL-NBL	C	DPDT	ON-OFF-ON	5.83	4.43	3.73	3.50
691-TIGM5B6SBLNBL	TIGM5B-6S-BL-NBL	C	DPDT	ON-OFF-(ON)	7.13	5.41	4.56	4.28
691-TIGM5M6SBLNBL	TIGM5M-6S-BL-NBL	C	DPDT	(ON)-OFF-(ON)	7.13	5.41	4.56	4.28

## LTIG SERIES: ILLUMINATED FULL SIZE TIPPETTE ROCKER SWITCHES

- Rating: 10A @250VAC/15A@125VAC/3/4HP 125-250VAC
- Termination: .250 QC Tab
- Illumination: 12VDC incandescent lamp

- Actuator: Red, glossy finish, smooth curved with red lens
- Bracket: Black glossy finish



( ) Momentary

For quantities of 250 and up, call for quote.

MOUSER STOCK NO.	Carling Technologies Part No.	Fig.	Contact Form	Circuit	Price Each			
					1	25	50	100
691-LTIGK516SBLNBL	LTIGK51-6S-BL-RC-NBL-12V	D	DPST	ON-OFF	7.77	6.06	5.30	4.55
691-LTIGL516SBLNBL	LTIGL51-6S-BL-RC-NBL-12V	D	DPST	ON-ON	10.83	8.44	7.39	6.66
691-LTIGL5B6SBLNBL	LTIGL5B-6S-BL-RC-NBL-12V	D	DPST	ON-(ON)	11.66	9.10	7.96	6.83
691-LTIGM516SBLNBL	LTIGM51-6S-BL-RC-NBL-12V	D	DPDT	ON-OFF-ON	10.83	8.44	7.39	6.66
691-LTIGM5B6SBLNBL	LTIGM5B-6S-BL-RC-NBL-12V	D	DPDT	ON-OFF-(ON)	11.66	9.10	7.96	6.83
691-LTIGM5M6SBLNBL	LTIGM5M-6S-BL-RC-NBL-12V	D	DPDT	(ON)-OFF-(ON)	11.66	9.10	7.96	6.83

## R SERIES: CURVETTE SNAP-IN ROCKER SWITCHES

- Circuit: SPST OFF-ON
- Rating: 10A @250VAC/16A@125VAC/3/4HP 125-250VAC
- Termination: .250 QC Tab

- Actuator: Matte finish
- Visi-rocker actuator shows red to indicate "ON" position



( ) Momentary

For quantities of 250 and up, call for quote.

MOUSER STOCK NO.	Carling Technologies Part No.	Fig.	Legend	Actuator/ Bezel Color	Price Each			
					1	25	50	100
<b>Standard actuator</b>								
691-RA901RBB0N	RA901-RB-B-0-N	E	None	Black/Black	1.07	.82	.57	.45
691-RA901RWB0N	RA901-RW-B-0-N	E	None	White/Black	1.07	.82	.57	.45
691-RA901RWW0N	RA901-RW-W-0-N	E	None	White/White	1.07	.82	.57	.45
691-RA901RBBAN	RA901-RB-B-A-N	E	OFF-ON Vert.	Black/Black	1.17	.89	.62	.49
691-RA901RBBFN	RA901-RB-B-F-N	E	O-I Vert.	Black/Black	1.17	.89	.62	.49
<b>Visi-rocker actuator</b>								
691-RA901VBB0V	RA901-VB-B-0-V	E	None	Black/Black	1.17	.89	.62	.49
691-RA901VBB1V	RA901-VB-B-1-V	E	OFF-ON Vert.	Black/Black	1.17	.89	.62	.49
691-RA901VBB2V	RA901-VB-B-2-V	E	OFF-ON Hor.	Black/Black	1.17	.89	.62	.49
691-RA901VBB9V	RA901-VB-B-9-V	E	O-I Vert.	Black/Black	1.17	.89	.62	.49
691-RA901VWW1V	RA901-VW-W-1-V	E	OFF-ON Vert.	White/White	1.17	.89	.62	.49

Catalog #619, August - October 2004  
© Copyright 2004 Mouser Electronics

