

← BACK

NEXT →

# EAGLE PLASTIC DEVICES Battery Holders and Clips

NEW AT MOUSER

## “C” AND “D” BATTERY HOLDERS

**“C” Size** For quantities 2000 and up, call for quote.

MOUSER STOCK NO.	Fig.	No. of Cells	Color	Description	Price Each			
					1	10	100	1000
12BH211	A	1	Black	6" leads-tinned 3/16"	.66	.44	.39	.36
12BH220	B	2	Black	6" leads-tinned 3/16"	.95	.87	.74	.46
12BH221D	B	2	Black	Solder tabs	.95	.87	.74	.46
12BH231	C	3	Black	6" leads-tinned 3/16"	1.11	.85	.77	.70
12BH242	D	4	Black	6" leads-tinned 3/16"	.99	.77	.69	.64
12BH242A	D	4	Black	8" 22AWG leads	1.29	.99	.90	.76
12BH243	E	4	Black	6" leads-tinned 3/16"	1.08	.83	.76	.69
12BH262	F	6	Black	6" leads-tinned 3/16"	1.96	1.63	1.48	1.35
12BH261	G	6	Black	Mini snaps spaced .50"	1.59	1.32	1.20	1.09
12BH261A	G	6	Black	8" 22AWG leads	1.44	1.20	1.09	.91
12BH263	G	6	Black	6" leads-tinned 3/16"	1.44	1.20	1.09	.91
12BH281	H	8	Black	6" leads-tinned 3/16"	2.12	1.77	1.61	1.47

**“D” Size** For quantities 2000 and up, call for quote.

MOUSER STOCK NO.	Fig.	No. of Cells	Color	Description	Price Each			
					1	10	100	1000
12BH111A	A	1	Black	6" leads-tinned 3/16"	.66	.44	.39	.36
12BH111D	A	1	Black	Solder tabs	.66	.44	.39	.36
12BH121	I	2	Black	Solder tabs	1.09	.90	.79	.73
12BH121A	I	2	Black	8" 24AWG leads	1.29	.99	.90	.76
12BH125	J	2	Black	6" leads-tinned 3/16"	.65	.50	.45	.41
12BH131	K	3	Black	6" leads-tinned 3/16"	1.31	.99	.92	.83
12BH146	L	4	Black	6" leads-tinned 3/16"	1.29	.99	.90	.82
12BH142A	L	4	Black	8" 22AWG leads	1.29	.99	.90	.76
12BH144A	M	4	Black	6" leads-tinned 3/16"	1.74	1.45	1.32	1.20
12BH160	N	6	Black	6" leads-tinned 3/16"	2.49	2.07	1.89	1.72
12BH162A	G	6	Black	6" leads-tinned 3/16"	1.43	1.19	1.08	.98
12BH162B	G	6	Black	Mini snaps spaced .50"	1.56	1.29	1.18	1.08
12BH163	O	6	Black	Mini snaps spaced .50"	2.49	2.07	1.89	1.72
12BH181	P	8	Black	6" leads-tinned 3/16"	2.68	2.23	1.99	1.85

## METAL BATTERY HOLDERS/CLIPS

**Steel, Nickel Plated** For quantities of 2000 and up, call for quote.

MOUSER STOCK NO.	Fig.	Description	Price Each			
			1	100	500	1000
12BH071	A	9V battery holder horizontal	.22	.18	.15	.12
12BH079	A	9V battery holder horizontal	.25	.21	.16	.13
12BH080	B	9V battery holder vertical	.29	.22	.19	.17
12BH095	B	9V battery holder vertical	.24	.19	.15	.13
12BH980	B	9V battery holder vertical	.22	.17	.15	.14
12BH092	C	AA battery clip	.14	.10	.09	.08
12BH082	C	AAA battery clip PC mount	.15	.11	.09	.08
12BH209	D	AA battery clip negative	.14	.09	.06	.04
12BH228	E	AA battery clip positive	.14	.09	.06	.04
12BH204	D	AAA battery clip negative	.16	.11	.08	.06
12BH238	F	AAA battery clip positive	.17	.085	.065	.053
12BH210	G	AA dual snap-on clip	.24	.16	.13	.09
12BH202	G	AAA dual snap-on clip	.24	.16	.13	.09
12BH629	H	AA,AAA PC spring contact	.27	.18	.16	.14
12BH002	I	20MM coin cell holder SM	.27	.18	.16	.14
12BH003	J	20MM coin cell holder PC	.27	.18	.16	.14

## COIN CELL BATTERY HOLDERS

For quantities of 25,000 and up, call for quote.

MOUSER STOCK NO.	Fig.	Size	Description	Price Each			
				1	100	1,000	10,000
122-2520	K	20mm	Thru-hole black single cell	.80	.65	.50	.40
122-2523	K	23mm	Thru-hole black single cell	.80	.65	.50	.40
122-2620	L	20mm	Thru-hole black single cell	.80	.65	.50	.40
122-2620	M	20mm	Surface mount beige	.66	.55	.45	.40
122-2312	N	12mm	Thru-hole black single cell	.90	.75	.65	.50
122-2313	N	12mm	Thru-hole black dual cell	.90	.75	.65	.50

## BATTERY HOLDERS W/ COVERS AND SWITCH

• Color: Black • Nickel plated hardware For quantities of 2000 and up, call for quote.

MOUSER STOCK NO.	Fig.	No. of Cells	Size	Description	Price Each			
					1	10	100	1000
12BH9V/CS	O	1	9V	6" leads tinned 3/16" w/cover & switch	.87	.67	.61	.55
12BH325/C	O	2	AA	6" leads tinned 3/16" w/cover	.61	.55	.39	.36
12BH325/CS	O	2	AA	6" leads tinned 3/16" w/cover & switch	.76	.63	.57	.52
12BH331/C	P	3	AA	6" leads tinned 3/16" w/cover	.79	.72	.51	.47
12BH331/CS	P	3	AA	6" leads tinned 3/16" w/cover & switch	.91	.76	.69	.63
12BH348/C	Q	4	AA	6" leads tinned 3/16" w/cover	.93	.85	.61	.55
12BH348/CS	Q	4	AA	6" leads tinned 3/16" w/cover & switch	1.04	.87	.79	.72
12BH421/C	O	2	AAA	6" leads tinned 3/16" w/cover	.56	.51	.36	.33
12BH421/CS	O	2	AAA	6" leads tinned 3/16" w/cover & switch	.69	.58	.53	.48
12BH431/C	P	3	AAA	6" leads tinned 3/16" w/cover	.75	.68	.48	.44
12BH431/CS	P	3	AAA	6" leads tinned 3/16" w/cover & switch	.89	.74	.67	.61
12BH441/C	Q	4	AAA	6" leads tinned 3/16" w/cover	.91	.83	.59	.54
12BH441/CS	Q	4	AAA	6" leads tinned 3/16" w/cover & switch	1.02	.85	.78	.71

Catalog #621, February - April 2005  
© Copyright 2005 Mouser Electronics

Catalog #621, February - April 2005  
© Copyright 2005 Mouser Electronics

1390 [www.mouser.com/eagleplasticdevices](http://www.mouser.com/eagleplasticdevices)

(800) 346-6873

← BACK

NEXT →