

JACKNACK TELECOMMUNICATIONS CABLE PREPERATION TOOL

- Cable Jack Stripper
- Cable Filler Sheer
- Jacknack Clamp
- Wire Placement Tool

MOUSER STOCK NO.	Fig.	Description	Price Each
571-2119000-1	A	Cable Preparation Tool for Unshielded Twisted Pair Cable (Cat. 3-6)	32.00

TOOLS FOR PCB CONNECTORS AND PIN AND SOCKET CONNECTORS

Pro Crimper III Hand Tool

- Field repair/prototyping
- Ratchet control
- Brush/bellmouth control
- Precision crimp height control

571-908711	B	.093" Pin and Socket cont. 20-14 AWG	267.45
571-908701	B	.062" Pin and Socket cont. 30-24 AWG	267.45
571-908691	B	.062" Pin and Socket cont. 24-18 AWG	267.45
571-585141	B	Miniature rectangular connectors	267.45
571-905741	B	Commercial Mate-N-Lok® 24-18 AWG	370.29
571-905481	B	Universal Mate-N-Lok® 24-18 AWG	197.80
571-905461	B	Universal Mate-N-Lok® 20-14 AWG	169.94
571-584951	B	"Series 1" CPC size 16 contacts	158.93
571-584482	B	"Series 2" CPC size 20 contacts	267.45
571-3549401	B	Pro-Crimper III frame	60.50
571-584231	B	Die set for solderless terminals	64.07

TOOLS FOR MTA SERIES

Pistol Grip Hand Tool

MOUSER STOCK NO.	Fig.	Description	Price Each
571-580741	C	Pistol Grip Hand Tool for MTA Series	82.54

Interchangeable Head for Pistol Grip Hand Tool

571-58246-1	D	MTA .100 Series	158.60
571-582471	D	MTA .156 Series	169.94

"T" Handle Maintenance Tool

571-598031	E	For MTA .100 Series	22.21
571-598041	E	For MTA .156 Series	22.31

CONTACT INSERTION/EXTRACTION TOOLS

MOUSER STOCK NO.	Fig.	Description	Price Each
571-910672	F	Insertion/extraction, size 20, 22 contacts	7.06
571-3188311	G	Extraction, .062 Pin and Socket	172.71
571-1804030-1	G	Extraction, Universal Mate-N-Lok®	38.71
571-4558301	H	Insertion, Universal Mate-N-Lok® and MR	20.77
571-4656441	I	Extraction, Commercial Mate-N-Lok®	16.14
571-305183	J	Extraction, size 16 CPC contacts	12.26
571-912851	K	Insertion/extraction, size 20, 22 contacts	20.43
571-910193	L	Extraction, type XII series 3 CPC contacts	224.01
571-911241	M	Extraction, type XII series 4 CPC contacts	52.26

TOOLS FOR MODULAR PLUGS

"Category 5" High Performance Crimp Tool

- For use with modular plugs
- Cuts, strips, and terminates cable
- All plug sizes, except 10-position are accommodated using interchangeable die sets

MOUSER STOCK NO.	Fig.	Description	Price Each
571-32316520	N	8-position modular crimp tool with die	144.37

Professional Hand Tools with Die Sets

- For use with modular plugs
- Cuts, strips, and terminates cable
- All plug sizes, except 10-position are accommodated using interchangeable die sets

571-22316521	N	8-position line	155.30
571-22316523	N	4-position handset	146.25
571-2-231652-6	N	6-position offset-latch	160.35
571-22316527	N	6-position long body	160.35
571-22316528	N	4, 6-position line	165.95

Die Set Only for Professional Hand Tool

571-8534001	-	8-position line	59.18
571-8534003	-	4-position handset	59.18
571-853400-6	-	6-position offset-latch	59.18
571-8534007	-	6-position long body	59.18
571-853400-8	-	4,6-position line	59.18

Professional Hand Tool Kits

571-12316661	-	4-position handset, 4, 6, and 8-position die sets, set of replacement strip blades and small screwdriver	331.54
571-2316625	-	(1) set of strip blades	5.07

