

MOLEX Tools

molex
one company • a world of innovation

TOOL MATRIX

Crimping Tool	Insertion Tool	Extraction Tool	Use With Connector Series
63811-0200	- - -	57072-6000	1.25mm Crimp Terminal
63811-0300	- - -	- - -	1.27mm Micro-D
63811-4800	- - -	- - -	1.27mm Micro-D
11-01-0185	11-02-0001	11-03-0002	.062" Pin and Socket
63811-3300	- - -	- - -	.062" Pin and Socket
63811-1000	- - -	- - -	.062" Pin and Socket
63811-6800	- - -	11-01-0168	.084" Pin and Socket
63811-1000	11-02-0003	11-03-0006	.093" Pin and Socket
63811-3200	- - -	- - -	.093" Pin and Socket
11-01-0204	- - -	- - -	2mm Milli-Grid™ Crimp Terminal
63811-8700	11-02-0022	11-03-0036	2.54mm SL™
11-01-0209	- - -	- - -	2.54mm SL™
11-01-0206	- - -	11-03-0037	Disk Drive
11-01-0185	63812-0000	11-03-0022	KK-100
11-01-0185	- - -	- - -	KK-100
63811-7500	- - -	11-03-0016	KK-156
11-01-0203	- - -	- - -	KK-156
63811-2800	- - -	11-03-0043	Micro-Fit 3.0™
6381-5000	- - -	- - -	Micro-Fit 3.0™
11-01-0197	- - -	11-03-0044	Mini-Fit™ Jr.
11-01-0198	- - -	- - -	Mini-Fit™ Jr.
63811-1500	- - -	63813-0400	Mini-Fit™ Sr.
63811-1600	- - -	- - -	Mini-Fit™ Sr.
63811-4400	- - -	63813-1500	MX150L™
63811-7200	- - -	63813-0500	Sabre™ 7.5mm (Female)
63811-0600	- - -	63813-0800	Sabre™ 7.5mm (Male)

INSERTION AND EXTRACTION TOOLS

MOUSER STOCK NO.	Fig.	Description	Price Each
538-11-02-0001	A	.062" Pin and Socket Insertion Tool	31.68
538-11-03-0002	B	.062" Pin and Socket Extraction Tool	16.92
538-11-01-0168	C	.084" Pin and Socket Extraction Tool	62.35
538-11-02-0003	A	.093" Pin and Socket Insertion Tool	21.12
538-11-03-0006	B	.093" Pin and Socket Extraction Tool	19.45
538-11-02-0022	D	2.54mm SL™ Insertion Tool	18.52
538-11-03-0036	B	2.54mm SL™ Extraction Tool	16.40
538-11-03-0037	B	Disk Drive Extraction Tool	76.04
538-63812-0000	B	KK-100 Insertion Tool	40.21
538-11-03-0022	E	KK-100 Extraction Tool	6.77
538-11-03-0016	F	KK-156 Extraction Tool	16.60
538-11-03-0043	G	Micro-Fit 3.0™ Extraction Tool	16.92
538-11-03-0044	G	Mini-Fit™ Jr. Extraction Tool	19.32
538-63813-0400	H	Mini-Fit™ Sr. Extraction Tool	82.12
538-63813-1500	I	MX150L™ Extraction Tool	22.31
538-63813-2700	F	Sabre™ 7.5mm (Female) Extraction Tool	48.00
538-63813-0800	J	Sabre™ 7.5mm (Male) Extraction Tool	83.53

TOOLS FOR PCB AND PIN AND SOCKET CONNECTORS

MOUSER STOCK NO.	Fig.	Description	Price Each
538-63819-0300	K	1.25mm Crimp Terminal 32-26 AWG	255.00
538-63811-4800	K	1.27mm Micro-D 28-26 AWG	295.00
538-63819-0800	K	.062" Pin and Socket 30-22 AWG	311.00
538-63819-1300	L	.062" Pin and Socket 24-18 AWG	241.72
538-63811-1000	M	.062" and .093" Pin and Socket 24-14 AWG	49.00
538-63811-6800	N	.084" Pin and Socket 20-14 AWG	243.27
538-63819-1200	L	.093" Pin and Socket 22-14 AWG	295.00
538-63819-0100	K	2mm Crimp Terminal	289.28
538-63819-0500	K	2mm Crimp Terminal	268.99
538-63819-0100	K	2mm Milli-Grid™ Crimp Terminal 30-24 AWG	289.28
538-63811-5200	K	2.50 Spox Crimp Terminal	246.40
538-63811-8700	K	2.54mm SL™ 24-22 AWG	321.98
538-638118800	K	2.54mm SL™ 30-24 AWG	269.33
538-63811-7000	K	Disk Drive 22-14 AWG	247.50
538-63811-7500	K	KK-156 24-18 AWG	243.27
538-63811-6600	K	KK-156 30-18 AWG	224.57
538-63819-0000	K	Micro-Fit 3.0™ 30-20 AWG	295.00
538-63811-2875	-	Crimp Tool Locator for 538-63811-2800	35.07
538-63819-0900	K	Mini-Fit™ Jr. 24-18 AWG	241.72
538-63819-1000	K	Mini-Fit™ Jr. 28-22 AWG	235.00
538-63811-1500	O	Mini-Fit™ Sr. 8 AWG	343.44
538-63811-1600	O	Mini-Fit™ Sr. 12-10 AWG	343.44
538-63811-4400	O	MX150L™ 22-14 AWG	343.44
538-63811-7200	N	Sabre™ 7.5mm (Female) 18-14 AWG	321.98

