


MEDER Reed Relays

RoHS Compliant This product is RoHS compliant.



DIMENSIONS: in. (mm)



MEDER CRF SERIES-7GHz HIGH FREQUENCY

- Features:**
- Available with BGA
 - Very low profile
 - Minimum path length for RF

- Applications:**
- High frequency applications
 - High speed applications



RoHS Compliant

For quantities of 50 and up, call for quote.

MOUSER STOCK NO.	Meder Part No.	Fig.	Description	Price Each	
				1	25
876-CRF05-1A	CRF05-1A	A	Reed Relay 1 Form A, 5V Surface Mount High Frequency	6.93	6.58

MEDER CRR SERIES-SURFACE MOUNT

- Features:**
- Ceramic / Thermoset molded package
 - Gold plated leads
 - Very low profile

- Applications:**
- Telecommunications
 - Test and measurement systems
 - Medical applications



RoHS Compliant

For quantities of 50 and up, call for quote.

MOUSER STOCK NO.	Meder Part No.	Fig.	Description	Price Each	
				1	25
876-CRR05-1A	CRR05-1A	A	Reed Relay 1 Form A, 5V Surface Mount Ultra Small Low Profile	5.04	4.79

MEDER DIP SERIES-MOLDED DIP

- Features:**
- Low & high profile package
 - Standard pin configurations
 - Versions with diode available
 - IC - pin compatible

- Applications:**
- Test & Measurements
 - Telecommunications
 - Security



RoHS Compliant

For quantities of 50 and up, call for quote.

MOUSER STOCK NO.	Meder Part No.	Fig.	Description	Price Each	
				1	25
876-DIP05-1A72-11L	DIP05-1A72-11L	B	Reed Relay, 1 Form A, 5V Molded Dip	2.90	2.76
876-DIP05-1A72-11D	DIP05-1A72-11D	B	Reed Relay, 1 Form A, 5V Molded Dip w/Diode	2.93	2.78
876-DIP05-1A72-12L	DIP05-1A72-12L	B	Reed Relay 1 Form A, 5V Molded Dip	2.55	2.42
876-DIP05-2A72-21L	DIP05-2A72-21L	B	Reed Relay 2 Form A 5V Molded Dip	4.69	4.45
876-DIP05-1C90-51L	DIP05-1C90-51L	B	Reed Relay 1 Form C, 5V Molded Dip	6.43	6.11

MEDER LI SERIES-MINIATURE HIGH VOLTAGE PCB MOUNTING

- Features:**
- Smallest possible housing
 - Spacing saving package
 - High resistance available
 - Breakdown voltage 4.5 kVDC

- Applications:**
- High voltage test systems
 - Cable and in-circuit test equipment
 - Battery operated high voltage test equipment



RoHS Compliant

For quantities of 50 and up, call for quote.

MOUSER STOCK NO.	Meder Part No.	Fig.	Description	Price Each	
				1	25
876-LI12-1A85	LI12-1A85	C	Reed Relay 1 Form A, 12V High Voltage PCB Mounting (Small Package)	11.74	11.15

MEDER SIL SERIES-SINGLE IN LINE

- Features:**
- High resistance coils of up to 2000 Ω at 12V
 - Magnetic shield available
 - Breakdown voltage coil-contact up to 4.25 kVDC

- Applications:**
- ATE
 - Measurement equipment
 - Telecommunications



RoHS Compliant

For quantities of 50 and up, call for quote.

MOUSER STOCK NO.	Meder Part No.	Fig.	Description	Price Each	
				1	25
876-SIL05-1A72-71D	SIL05-1A72-71D	D	Reed Relay 1 Form A, 5V SIL (Single In-Line) w/Diode	3.10	2.95
876-SIL05-1A72-71L	SIL05-1A72-71L	D	Reed Relay 1 Form A, 5V SIL (Single In-Line)	2.98	2.83

MEDER RM SERIES HIGH FREQUENCY REED RELAY MODULE

- Features:**
- FR-4/thermoset molded package
 - Minimum path length for RF
 - Leadless SMT design eliminates skewing and coplanarity issues

- Applications:**
- Test and Measurement
 - Telecommunications
 - High frequency applications



RoHS Compliant

For quantities of 25 and up, call for quote.

MOUSER STOCK NO.	Meder Part No.	Fig.	Description	Price Each	
				1	10
876-RM05-4AS-4/4	RM05-4AS-4/4	E	Low Profile, 4 Input/4 Output Surface Mount, BGA, Relay Module, >3GHz	30.22	28.71