


# APC UPS Systems



## APC BACK-UPS

Back up power solutions from desktop to datacenter to custom-built industrial UPS system

For quantities of 2 and up, call for quote.



MOUSER STOCK NO.	APC Part No.	Fig.	No. of Outlets	Model	Input/Output Volts	Output Power Capacity	Backup Time Half/Full Load	Price Each
679-BE350G	BE350G	A	6	Back-UPS ES	120V / 120V	350VA / 200W	9.7 min. / 2.3 min.	53.20
679-BE450G	BE450G	A	8	Back-UPS ES	120V / 120V	450VA / 257W	11.6 min. / 2.5 min.	64.40
679-BE550G	BE550G	A	8	Back-UPS ES	120V / 120V	550VA / 330W	13.5 min. / 3.3 min.	70.70
679-BE750G	BE750G	A	10	Back-UPS ES	120V / 120V	725VA / 450W	11.3 min. / 2.3 min.	105.00
679-BK350	BK350	B	6	Back-UPS CS	120V / 120V	350VA / 210W	18.1 min. / 4.7 min.	88.20
679-BK500	BK500	B	6	Back-UPS CS	120V / 120V	500VA / 300W	13.9 min. / 3.4 min.	131.18
679-BR1200	BR1200	C	8	Back-UPS RS	120V / 120V	1200VA / 780W	17.4 min. / 6.2 min.	209.44
679-BR1500	BR1500	C	8	Back-UPS RS	120V / 120V	1500VA / 865W	15.4 min. / 5.1 min.	255.08
679-BR1300LCD	BR1300LCD	D	8	Back-UPS RS	120V / 120V	1300VA / 780W	16.4 min. / 5.4 min.	216.16
679-BR1500LCD	BR1500LCD	D	8	Back-UPS RS	120V / 120V	1500VA / 865W	13.4 min. / 3.3 min.	238.14
679-SC420	SC420	E	4	Smart-UPS SC	120V / 120V	420VA / 260W	13.5 min. / 5.5 min.	133.00
679-SC620	SC620	E	4	Smart-UPS SC	120V / 120V	620VA / 390W	15.7 min. / 5.5 min.	201.60
679-SUA750	SUA750	F	6	Smart-UPS	120V / 120V	750VA / 500W	15.9 min. / 4.6 min.	328.46
679-SUA1000	SUA1000	F	8	Smart-UPS	120V / 120V	1000VA / 670W	20.6 min. / 6.1 min.	481.21
679-SUA1500	SUA1500	F	8	Smart-UPS	120V / 120V	1440VA / 980W	23.9 min. / 6.7 min.	582.94
679-SUA750RM2U	SUA750RM2U	G	6	Smart-UPS-RM	120V / 120V	750VA / 480W	16.6 min. / 5.5 min.	462.72

## APC UPS REPLACEMENT BATTERY CARTRIDGES

For quantities of 2 and up, call for quote.

\* Other options available, contact a Mouser Representative

MOUSER STOCK NO.	APC Part No.	Replaces Batteries in Models	Price Each
679-RBC2	RBC2	BK200, BK250B, BK280B, BK280, BP280, BP280PNP, BP280C, BP280S, BK300, BK350, BK400, BK400B, BP420S, SU420NET, BK500, BE500U, BK500M, BK650MC, BP650C, BP650PNP, BP650S, SU620NET	41.10
679-RBC4	RBC4	BP1000, SUVS1000, SU1000, SUA1000, SU1000NET	65.76
679-RBC6	RBC6	SU700XL, SU1000XL, BP1400, SU1400, SUA1500	157.55
679-RBC7	RBC7		183.58



## APC SURGE PROTECTION AND CONDITIONING

Secure your equipment from everyday power surges, lightning strikes and other power anomalies

For quantities of 2 and up, call for quote.

MOUSER STOCK NO.	APC Part No.	Fig.	No. of Outlets	Category	Description	Price Each
679-P7T	P7T	A	7	Basic Surge Protectors - A	420 joules, data line protection, 6' cord, black	14.00
679-P7GT	P7GT	B	7	SurgeArrest Personal	420 joules, power-saving, with data line protection, black	25.20
679-P7T10	P7T10	A	7	Basic Surge Protectors - A	420 joules, data line protection, 10' cord, beige	17.50
679-PER7	PER7	B	7	SurgeArrest Personal	420 joules, beige	11.90
679-PER7T	PER7T	B	7	SurgeArrest Personal	240 joules, data line protection, beige	18.37
679-PRO7	PRO7	B	7	SurgeArrest Professional	320 joules, beige	22.79
679-PRO7T	PRO7T	B	7	SurgeArrest Professional	320 joules, data line protection, beige	27.93
679-PRO8	PRO8	C	8	SurgeArrest Professional	320 joules, beige	24.99
679-PRO8T2	PRO8T2	C	8	SurgeArrest Professional	320 joules, 2-line data line protection, beige	29.76
679-NET7	NET7	B	7	SurgeArrest Network	480 joules, beige	24.99
679-NET7T	NET7T	B	7	SurgeArrest Network	480 joules, data line protection beige	32.70
679-NET8	NET8	C	8	SurgeArrest Network	480 joules, beige	29.76
679-NET8N	NET8N	C	8	SurgeArrest Network	480 joules, 10base-T token ring protection, beige	39.69
679-NET9RMBLK	NET9RMBLK	D	9	SurgeArrest Rack Mountable	480 joules, horizontal or vertical mount, beige	98.00

## APC PROTECTNET DATA LINE PROTECTORS

For quantities of 2 and up, call for quote.

MOUSER STOCK NO.	APC Part No.	Fig.	Description	Price Each
679-PNET1GB	PNET1GB	G	RJ45 10/100/1000 Base-T ethernet prot.	23.52
679-PTEL2	PTEL2	G	RJ45 modem/fax/DSL protection	22.05
679-PS9-DTE	PS9-DTE	G	RS232 9 pin F to M serial data line prot.	19.11
679-PS9-DCE	PS9-DCE	G	RS232 9 PIN M to F serial data line prot.	19.11
679-PV	PV	G	Cable modem/DSS cont. box/cable/VCR	22.40

## APC LINE-R-HIGH PERFORMANCE POWER CONDITIONING

For quantities of 2 and up, call for quote.

MOUSER STOCK NO.	APC Part No.	Fig.	Description	Price Each
679-LE600	LE600	F	600VA, 4NEMA 5-15R	43.37
679-LE1200	LE1200	F	1200VA, 4 NEMA 5-15R	54.03

© Copyright 2009 Mouser Electronics

© Copyright 2009 Mouser Electronics

Power Protection