


DESCO Static Control and Lead Free Products



DESCO JEWEL® WORKSTATION CONTINUOUS MINI MONITOR

- Features:**
- Small size - 2.77" x 2.07"
 - Stand-by parking snap
 - Provides true 100% continuous monitoring of operator and work surface
 - Two 10mm push and clinch sockets included



MOUSER STOCK NO.	Desco Part No.	Description	Price Each	
			1	5
809-19212	19212	Sapphire, 120 Volt, NIST Calibrated	129.69	123.21

DESCO COMBO TESTER


- Features:**
- Tests wrist straps and foot grounders
 - Positive rocker switch actuation
 - LED's display test results
 - Battery powered with low-battery indicator



MOUSER STOCK NO.	Desco Part No.	Description	Price Each		
			1	10	25
809-19250	19250	Combo Wrist and Footground NIST	252.30	239.69	
809-19252	19252	Combo WS and FG with Stand NIST	410.35	389.83	

DESCO STATFREE T2™ - DISSIPATIVE DUAL LAYER RUBBER

- Features:**
- Durable rubber material, dissipative (10⁶ - 10⁸ Ω) on one side and conductive on the other
 - Versatile and long-lasting product; use as a dissipative work surface table mat.
 - Bottom conductive layer provides reliable path to ground, compatible for use with continuous monitors
 - Superior heat, chemical, and wear resistance




* Drop Ship Only † Includes groundcord

† 809-66050	66050	Dark Gray, 0.060" x 24" x 36"	88.51	84.09
† 809-66055	66055	Dark Gray, 0.060" x 24" x 48"	94.72	89.98
* 809-66085	66085	Roll, Dark Gray, 0.060" x 36" x 40'	1104.55	Call

DESCO STATFREE B™ - DISSIPATIVE HOMOGENEOUS VINYL


- Features:**
- 10⁷ - 10⁹ Ω resistance
 - Meets the minimum recommended work surface requirement of ANSI/ESD S20.20
 - Reversible extruded homogenous vinyl



809-16213	16213	Mat Kit, Blue, 0.100" x 24" x 36", Common Point Ground Kit Included	66.69	63.36
809-16214	16214	Mat Kit, Blue, 0.100" x 24" x 48", Common Point Ground Kit Included	80.54	76.51

PROTEKTIVE PAK TEK-MATE™ BOARD HANDLERS


- Features:**
- Portable ESD work surface that can also be used to transport populated but unsoldered circuit boards
 - Static dissipative foam (RTT 10⁶ - 10⁷ ohms) laminated to Protektive Pak® corrugate
 - Includes 10mm (3/8") male grounding snap
 - Fits most transportation carts
 - Buried shielding layer minimizes sloughing and rub-off contamination.



MOUSER STOCK NO.	Desco Part No.	Description	Price Each	
			1	10
809-37800	37800	12" x 18" with 10mm male snap	15.44	14.67
809-39852	39852	12" x 18" with 10mm female snap	14.92	14.17
809-39854	39854	18" x 24" with 10mm female snap	29.23	27.89

PROTEKTIVE PAK ESD STACKING BOARD HANDLER TRAYS

- Features:**
- Trays that can stack and nest together for improved use of space
 - Great container for Kanban



MOUSER STOCK NO.	Desco Part No.	Description	Price Each	
			1	10
809-37750	37750	18" x 11-3/8" x 1-3/4"	14.45	13.72
809-37751	37751	22 7/8" x 17 1/4" x 2 3/4"	29.97	28.47

© Copyright 2009 Mouser Electronics

DESCO LEAD-FREE AREA HEEL GRINDER


- Features:**
- With 2 Ω Resistor
 - Premium tear-resistant rubber
 - Interior green rubber layer
 - Green hook and loop fastening system
 - UL Listed
 - Made in America



MOUSER STOCK NO.	Desco Part No.	Description	Price Each		
			1	10	25
809-17260	17260	Heel Grinder, w/2 Meg Resistor	13.91	13.21	12.52

DESCO STATSHIELD® METAL-IN GREEN ESD SHIELDING BAGS

- Features:**
- ESD Shielding
 - Integral antistatic, low tribocharging properties
 - Appropriate ESD packaging for Lead-Free RoHS products
 - Meets ANSI/ESD S20.20 and MIL-PRF-81705D Type III
 - Provides easy identification of Lead-Free assemblies and components in the manufacturing process.




MOUSER STOCK NO.	Desco Part No.	Description	Price Each		
			1	10	25
809-12780	12780	4" X 6", 100 Pack	10.28	9.97	9.75
809-12781	12781	5" X 8", 100 Pack	17.47	16.60	15.72
809-12782	12782	6" X 10", 100 Pack	19.73	18.42	17.77
809-12783	12783	8" X 10", 100 Pack	24.07	22.87	21.66
809-12786	12786	10" X 14", 100 Pack	38.00	35.26	34.15
809-12787	12787	10" X 24", 100 Pack	64.00	61.94	59.83
809-12788	12788	12" X 18", 100 Pack	58.20	54.19	52.98
809-12789	12789	15" X 18", 100 Pack	71.00	68.29	66.04
809-12790	12790	18" X 18", 100 Pack	82.56	78.53	76.22
809-12791	12791	18" X 24", 100 Pack	107.00	102.20	100.21

DESCO STATFREE T2™ LEAD-FREE AREA DISSIPATIVE DUAL LAYER RUBBER MATS

These green mats are laser engraved "Lead-Free Workstation" to identify the workstation as a Lead-Free work area.

- Features:**
- Superior heat, chemical and wear resistance
 - Dissipative worksurface
 - Lightly embossed surface
 - Durable rubber material, dissipative on one side and conductive on the other
 - Non-humidity dependence
 - Dimensionally stable and lays flat
 - Lifetime warranty (limited to Electricals)




MOUSER STOCK NO.	Desco Part No.	Description	Price Each	
			1	5
809-66057	66057	.060" X 24" X 36", Green	91.27	86.70
809-66058	66058	.060" X 24" X 48", Green	109.07	103.62

DESCO STATFREE Z2™ LEAD-FREE DISSIPATIVE 3 LAYER VINYL MAT

This green mat is laser engraved "Lead-Free Workstation" to identify the workstation as a Lead-Free work area.


- Features:**
- Heat fused vinyl composite with top and bottom dissipative vinyl layers
 - Conductive grid mesh inner layer
 - Abrasion resistant top layer
 - Non-humidity dependence
 - Dimensionally stable



809-42480	42480	0.125" X 24" x 48", Green	85.86	81.57
-----------	-------	---------------------------	-------	-------

DESCO MICASTAT® LEAD-FREE AREA DISSIPATIVE LAMINATE MAT

- Features:**
- High Pressure Laminate
 - Low Tribocharging
 - Patented Conductive layer
 - Mat top kits
 - >10E5 and <10E10 RTG
 - Lead-free RoHS compliant



809-10393	10393	0.040, 24" X 36", ESD Green	121.94	115.84
809-10394	10394	0.040, 24" X 48", ESD Green	151.61	144.03

© Copyright 2009 Mouser Electronics