


EAGLE PLASTIC DEVICES Fuse Blocks and Fuse Clips



EAGLE PLASTIC DEVICES FUSE BLOCKS

For quantities of 2000 and up, call for quote.

MOUSER STOCK NO.	Fig.	Description	Contact Plating	Price Each			
				1	100	500	1000
441-4454	A	6A/125VAC 5 X 20mm	Nickel	1.21	1.01	.92	.83
441-R345A-GR	B	8A/125/250VAC 5 X 20mm	Nickel	.93	.71	.65	.59
441-R345B-GR	C	10A/250VAC 1/4" x 1 1/4"	Nickel	.93	.71	.65	.59
441-EPD201NI	D	30A/250VAC 1/4" x 1 1/4"	---	1.31	.99	.76	.66
441-EPD200H	E	6.3A/250VAC 5 X 20mm	---	.51	.44	.38	.30
441-EPD201H	F	10A/250VAC 1/4" x 1 1/4"	---	.51	.44	.38	.30
441-EPD2005	G	6.3A/250VAC 5 X 20mm	---	.44	.34	.30	.28
441-EPD201V	H	10A/250VAC 1/4" x 1 1/4"	---	.51	.44	.38	.30

EAGLE PLASTIC DEVICES PC MOUNT FUSE CLIPS

1/4" PC Mount

For quantities of 2000 and up, call for quote.

MOUSER STOCK NO.	Fig.	Description	Contact Plating	Price Each			
				1	100	500	1000
44FH053	H	1/4", 15A, Ear type	Nickel	.22	.19	.17	.15
441-EPD205B	I	1/4", 15A, Ear type	Tin	.19	.16	.14	.14
441-EPD205D	J	1/4", 15A, Ear type	Tin	.19	.16	.14	.14
441-EPD205DHN	K	1/4", 15A, Ear type	Tin	.19	.16	.14	.14
441-EPD205E	L	1/4", 15A, Ear type	Tin	.19	.16	.14	.14
441-EPD205SPPN	M	1/4", 15A, Ear type	Tin	.19	.16	.14	.14
441-EPD218A	N	1/4" or 5mm, 10A	Tin	.19	.16	.14	.14
441-EPD218R	N	1/4" or 5mm, 10A	Tin	.19	.16	.14	.14

5mm PC Mount

For quantities of 2000 and up, call for quote.

MOUSER STOCK NO.	Fig.	Description	Contact Plating	Price Each			
				1	100	500	1000
44FH052	O	5mm	Silver	.11	.08	.07	.06
441-EPD203B	P	5mm, 10A, Ear type	Tin	.20	.17	.15	.13
441-EPD203D	Q	5mm, 6.3A	Tin	.20	.17	.15	.13
441-EPD203E	R	5mm, 15A, Ear type	Tin	.23	.19	.17	.15
441-EPD203H	S	5mm, 6.3A	Tin	.20	.17	.15	.13
441-EPD203K	T	5mm, 10A	Tin	.19	.16	.14	.14
441-EPD203LR	U	5mm, 10A, Ear type	Tin	.14	.12	.09	.07
441-EPD203P	V	5mm, 10A, Ear type	Tin	.14	.12	.09	.07
441-EPD203S	W	5mm, 10A, Ear type	Tin	.15	.13	.10	.08
441-EPD203SF	W	5mm, 10A, Ear type	Tin	.14	.12	.09	.07
441-EPD203SP	V	5mm, 10A, Ear type	Tin	.14	.12	.09	.07
441-EPD203T	X	5mm, 10A, Ear type	Tin	.15	.13	.10	.08
441-EPD450	Y	4.5 or 5mm, 10A	Tin	.14	.12	.09	.07
441-EPD450D	Z	4.5 or 5mm, 10A	Tin	.14	.12	.09	.07

3.6mm PC Mount

For quantities of 2000 and up, call for quote.

MOUSER STOCK NO.	Fig.	Description	Contact Plating	Price Each			
				1	100	500	1000
441-EPD301A	AA	3.6mm, 6.3A, Ear type	Tin	.15	.13	.10	.074
441-EPD301B	AA	3.6mm, 6.3A, Ear type	Tin	.16	.14	.11	.079

EAGLE PLASTIC DEVICES KITS

441-EPDKIT09 • 1/4" PCB Mnt fuse clip 240 PCS • 5mm PCB Mnt fuse clip 360 PCS • 4.5/5mm fuse clip 100 PCS • ATQ type blade fuse clip T/R 100 PCS • 5mm PCB Mnt fuse clip T/R 30 PCS • 3.6mm PCB Mnt fuse clip 100 PCS • AST Mini blade fuse clip 100 PCS • Multi clip 5mm/6.3mm 20 PCS	441-EPDKIT10 • 5 x 20mm fuse block 60 PCS • fuse block covers 60 PCS
441-EPDKIT11 • 5 x 20mm fuse block 60 PCS • Blade fuse block 60 PCS • fuse block covers 35 PCS	

* 6 Types of Each In Kit

For quantities of 50 and up, call for quote.

MOUSER STOCK NO.	Fig.	Description	Price Each			
			1	5	10	20
* 441-EPDKIT09	--	5X20mm, 6X32mm, PC Mnt Special	87.79	79.81	72.55	65.96
441-EPDKIT10	--	5X20mm, PC Mnt Types, Fuse Blk Covers	23.74	21.58	17.98	14.98
441-EPDKIT11	--	5X20mm, Blade Type, Fuse Block Covers	47.57	43.25	39.31	35.74

EAGLE PLASTIC DEVICES FUSE PULLER TOOLS

For quantities of 50 and up, call for quote.

MOUSER STOCK NO.	Fig.	Description	Price Each			
			1	5	10	20
441-EPD213	BB	Dual Fuse Puller	.48	.39	.35	.31
441-EPD223	CC	Dual Fuse Puller	.59	.49	.46	.43
441-EPD224	DD	Dual Fuse Puller	.54	.44	.41	.37