


RoHS Compliant This product is RoHS compliant.



ARGENTINA POWER CORD

- Features:**
- IRAM approval
 - CEE Color Code
 - Cordage Color - Black
 - Temp Rating: 70°C
 - Unshielded



For quantities of 50 and up, call for quote.

MOUSER STOCK NO.	Qualtek Part No.	Fig.	Length	Cordage	No. of Cond. AWG	Amps 250V	Price Each		
							1	10	25
562-390002-01	390002-01	A	2.5M	H05VV-F	3 x 1.00mm	10	9.12	8.71	8.30
562-390001-01	390001-01	B	2.5M	H05VV-F	3 x 1.00mm	10	6.50	5.90	5.61

ITALY POWER CORD

- Features:**
- Italian Agency approval
 - CEE Color Code
 - Cordage Color - Black
 - Temp Rating: 70°C
 - Unshielded



For quantities of 50 and up, call for quote.

MOUSER STOCK NO.	Qualtek Part No.	Fig.	Length	Cordage	No. of Cond. AWG	Amps 250V	Price Each		
							1	10	25
562-381002-D01	381002-D01	C	2.5M	H05VV-F	3 x 1.00mm	10	7.30	6.93	6.58
562-380003-E01	380003-E01	D	2.5M	H05VV-F	3 x 1.00mm	10	6.05	5.45	5.18
562-380007-01	380007-01	D	1.8M	H05VV-F	3 x 1.00mm	10	5.00	4.51	4.28

SWITZERLAND POWER CORD

- Features:**
- Switzerland Swiss Agency approval
 - CEE Color Code
 - Cordage Color - Black
 - Temp Rating: 70°C
 - Unshielded



For quantities of 50 and up, call for quote.

MOUSER STOCK NO.	Qualtek Part No.	Fig.	Length	Cordage	No. of Cond. AWG	Amps 250V	Price Each		
							1	10	25
562-378001-E01	378001-E01	E	2.5M	H05VV-F	3 x 1.00mm	10	6.29	5.98	5.68
562-378005-01	378005-01	E	1.8M	H05VV-F	3 x 1.00mm	10	6.11	5.55	5.28
562-377003-E01	377003-E01	F	2.5M	H05VV-F	3 x 1.00mm	10	6.05	5.50	5.23
562-377009-01	377009-01	F	1.8M	H05VV-F	3 x 1.00mm	10	5.00	4.51	4.28
562-378002-D01	378002-D01	G	2.5M	H05VV-F	3 x 1.00mm	10	7.06	6.56	6.10

CONTINENTAL EUROPE POWER CORDS

- Features:**
- CEE Color Code
 - Approvals: Germany, Denmark, Norway, Finland, France, Belgium, Netherlands, Sweden
 - Unshielded
 - Cordage Color: Black



† Right Angle For quantities of 50 and up, call for quote.

MOUSER STOCK NO.	Qualtek Part No.	Fig.	Length	Cordage	No. of Cond. AWG	Amps 250V	Price Each		
							1	10	25
562-360007-01	360007-01	H	2.5M	H03VVH2-F	2 X .075mm	2.5	2.84	2.71	2.60
562-363012	363012-D01	I	2.5M	H05VV-F	3 x 1.00mm	10.0	4.47	4.29	4.07
562-364002	364002-D01	J	2.5M	H05VV-F	3 x 1.00mm	10.0	5.45	5.17	4.81
562-366042	366042-D01	K	2.5M	H05VV-F	3 x 1.00mm	10.0	4.25	4.04	3.90
† 562-367003	367003-D01	L	2.5M	H05VV-F	3 x 1.00mm	10.0	6.07	5.65	5.32

TAIWAN POWER CORD

- Features:**
- Taiwan Agency approval
 - CEE Color Code
 - Cordage Color - Black
 - Temp Rating: 70°C
 - Unshielded



For quantities of 50 and up, call for quote.

MOUSER STOCK NO.	Qualtek Part No.	Fig.	Length	Cordage	No. of Cond. AWG	Amps 125V	Price Each		
							1	10	25
562-393001-01	393001-01	M	2.5M	VCTF	3 X 1.25mm	13	6.16	5.88	5.60

JAPANESE POWER CORD

- Features:**
- Japanese PSE approval
 - CEE Color Code
 - Cordage Color - Black
 - Temp Rating: 70°C
 - Unshielded



For quantities of 50 and up, call for quote.

MOUSER STOCK NO.	Qualtek Part No.	Fig.	Length	Cordage	No. of Cond. AWG	Amps 124V	Price Each		
							1	10	25
562-397002-01	397002-01	M	2.5M	VCTF	3 X 1.25mm	13	6.25	5.96	5.68

UNITED KINGDOM POWER CORDS

- Features:**
- United Kingdom, BSI approval
 - CEE Color Code
 - Cordage Color - Black
 - Temp Rating: 70°C
 - Unshielded
 - Plug supplied with 13A Fuse



For quantities of 50 and up, call for quote.

MOUSER STOCK NO.	Qualtek Part No.	Fig.	Length	Cordage	No. of Cond. AWG	Amps 250V	Price Each		
							1	10	25
562-369003	369003-E01	N	2.5M	H05VV-F	3 x 1.00mm	10.0	9.23	8.77	8.45
562-369004-E01	369004-E01	N	2.5M	H05VV-F	3 x 1.50mm	16	11.78	10.96	10.19
562-370001	370001-E01	O	2.5M	H05VV-F	3 x 1.00mm	10.0	11.11	10.68	10.26

AUSTRALIAN POWER CORDS

- Features:**
- Australia, New Zealand approval
 - CEE Color Code
 - Cordage Color - Black
 - Temp Rating: 70°C
 - Unshielded



For quantities of 50 and up, call for quote.

MOUSER STOCK NO.	Qualtek Part No.	Fig.	Length	Cordage	No. of Cond. AWG	Amps 125V	Price Each		
							1	10	25
562-373003-A01	373003-A01	P	2.5M	H05VV-F	3 x 1.00mm	10.0	6.99	6.64	6.37
562-373008-01	373008-01	P	1.8M	H05VV-F	3 x 1.00mm	10	5.05	4.60	4.37
562-374003-A01	374003-A01	Q	2.5M	H05VV-F	3 x 1.00mm	10.0	9.75	9.26	8.70
562-374009-01	374009-01	Q	1.8M	H05VV-F	3 x 1.00mm	10	6.10	5.52	5.24

BRAZIL POWER CORDS

- Features:**
- INMETRO, UCIEE approval
 - CEE Color Code
 - Cordage Color - Black
 - Temp Rating: 60°C
 - Unshielded



For quantities of 50 and up, call for quote.

MOUSER STOCK NO.	Qualtek Part No.	Fig.	Length	Cordage	No. of Cond. AWG	Amps 250V	Price Each		
							1	10	25
562-392001-01	392001-01	R	2.5M	H05VV-F	3 x 1.00mm	10	6.04	5.75	5.34

ISRAEL POWER CORDS

- Features:**
- Israel approved
 - CEE Color Code
 - Cordage Color - Black
 - Temp Rating: 70°C
 - Unshielded
 - Angled Plug



For quantities of 50 and up, call for quote.

MOUSER STOCK NO.	Qualtek Part No.	Fig.	Length	Cordage	No. of Cond. AWG	Amps 250V	Price Each		
							1	10	25
562-398001-01	398001-01	S	2.5M	H05VV-F	3 x 1.00mm	10	7.65	6.89	6.54
562-398002-01	398002-01	S	1.8M	H05VV-F	3 x 1.00mm	10	6.86	6.20	5.89