

B&K PRECISION Programmiers and Erasers

BK PRECISION PROGRAMMERS

Each programmer has been designed for ease-of-use and reliable performance. Whether you are working with PLCC, SOIC, TSOP, DIP, TOFP, SSOP, PSOP or QFP, B+K Precision has an extensive line of socket adapters to interface with any IC package. These programmers are a must for anyone that tests, repairs, or programs any electronic device that uses a memory IC. Fast and reliable, you can depend upon B+K Precision programmers.

Memory Programmer

Features:

- EPROM, EEPROM, Flash, NVRAM and serial EEPROM capability
- Low cost
- 32 pin DIL ZIF (Zero Insertion Force) socket accepts both 300/600 mil devices up to 32 pin
- Parallel printer port interface
- Easy to use control program, DOS and Windows 95/98/Me/NT/2000/XP compatible
- One year warranty
- Device library: 10,000

For quantities of 5 and up, call for quote.

MOUSER STOCK NO.	BK Precision Part No.	Fig.	Description	Price Each
615-848A	848A	A	EEPROM Programmer, Single Socket	283.46

A



Universal Device Programmer with USB Interface

Features:

- The 866B is a universal device programmer with an extensive device library that is constantly updated.
- This programmer has been designed for ease of use and reliable performance and it is ideal for use with Laptop/Notebook computers that do not have parallel port interfaces.
- Whether you are working with PLCC, SOIC, TSOP, DIP, TOFP, SSOP, PSOP or QFP, B+K Precision has an extensive line of socket adapters to interface with any IC package.
- This programmer is a must for anyone that Tests, Repairs, or Programs any electronic device that uses a memory IC.
- 48 pin DIL ZIF (Zero Insertion Force) socket accepts both 300/600 mil devices up to 48 pin
- Over 12,438 supported devices (9,734 devices supported via USB interface) as of 5/27/04
- Fast and accurate programming 48 pin ZIF socket, no adapter required for any DIP device up to 48 pins
- Connector for in-circuit programming (ISP) Windows 95/98/Me/NT/2000/XP compatible
- Device library: 45,000

For quantities of 5 and up, call for quote.

MOUSER STOCK NO.	BK Precision Part No.	Fig.	Description	Price Each
615-866B	866B	B	Universal Device Programmer with USB Interface	1095.00

B



Device Programmer with USB PC Interface

The model 844USB is a great low cost USB interface programmer designed for anyone who wants to read, copy, program or burn common IC's


Features:

- Extensive device libraries, >11510
- Low cost and high performance
- Free technical support
- 40 pin DIL ZIF (Zero Insertion Force) socket accepts both 300/600 mil devices up to 40 pins
- USB 2.0/1.1 Interface
- Small, fast and powerful programmer
- In circuit serial programming (ISP) capability
- Easy to use control program, Windows 95/98/Me/NT/2000/XP compatible

For quantities of 5 and up, call for quote.

MOUSER STOCK NO.	BK Precision Part No.	Fig.	Description	Price Each
615-844USB	844USB	C	USB Device Programmer	509.00

C



Universal programmer with 4 Programming Sockets

The model 859 is a universal multiprogrammer with 4 programming sockets and a constantly updated extensive device library. All four programming sockets are independent and it has been designed for ease of use and reliable performance. It is ideal for use with Laptop/Notebook computers that do not have parallel port interfaces. This programmer is a must for anyone that Tests, Repairs or Programs any electronic device that uses a memory IC.

Features:

- Fast programming speed(64-Mbit NOR Flash>50 sec/1Gbit NAND Flash>220 sec).
- Four Independent 48-pins powerful pin drivers, no adapter required for any <48-pin DIL devices.
- Connector for in-circuit programming (ISP).
- Dual connections to PC:USB or parallel (printer)port.
- USB 2.0/1.1 compatible interface.
- Alternatively high-speed IEEE 1284 (ECP/EPP) printer-port (LPT) interface.
- Easy to use Software compatible with Windows 98/Me/NT/2000/XP/2003/XPx64/Vista.
- Expandable numtprogramming possibility by attaching two programmers to one PC.
- Approved by CE laboratory to meet CE requirement.

For quantities of 5 and up, call for quote.

MOUSER STOCK NO.	BK Precision Part No.	Fig.	Description	Price Each
615-859	859	D	Universal Multiprogrammer w/4 Sockets	3928.76

D



BK PRECISION ERASERS

Features:

- Heavy duty EPROM eraser that can simultaneously erase up to 40 24 pin EPROMs. It has an all-metal case plus an advanced designed chip drawer that prevents UV radiation from being a hazard to the user. The chip drawer is lined with conductive foam to prevent electrostatic damage to the chips.

Specifications:

- Timer Setting: 30 min., 100-120VAC 50/60Hz
- UV Bulb Wattage: 10W
- Supplied: AC Power cord, Manual

For quantities of 5 and up, call for quote.

MOUSER STOCK NO.	BK Precision Part No.	Fig.	No. of EPROMs	Price Each
EPROM Eraser				
615-851	851	E	40	185.00
EPROM Eraser Lamp Replacements				
Description				
615-851LAMP	400-088-9-001	--	851 UV Lamp	30.00
615-850LAMP	400-087-9-001	--	850 PCB Bulb Assembly	30.00
EPROM Adapters				
615-70-0036	70-0036	--	32 Pin PLCC	153.15
615-70-0877	70-0023	--	28 Pin SOIC	142.30
615-70-0067	70-0067	--	40 Pin PLCC 44ZIF	115.00
615-70-0083	70-0083	--	48 To 52 Pin PLCC	219.00

E

