


# EAGLE PLASTIC DEVICES Control and Instrument Knobs



## SLIDE CONTROL KNOBS

Stylish and functional, these slide control knobs are available in several color combinations.


MOUSER STOCK NO.	Fig.	Body Color	Line Color	Shaft Size	Dimensions: in.			Price Each			
					A	B	C	1	10	100	500
450-SL2112	A1	Red	Black	1.2x8	.945	.591	.445	.52	.422	.388	.355
450-SL2212	A1	Yellow	Black	1.2x8	.945	.591	.445	.52	.422	.388	.355
450-SL2312	A1	Blue	Black	1.2x8	.945	.591	.445	.52	.422	.388	.355
450-SL2412	A1	Green	Black	1.2x8	.945	.591	.445	.52	.422	.388	.355
450-SL2512	A1	Gray	Black	1.2x8	.945	.591	.445	.52	.422	.388	.355
450-SL2612	A1	Black	White	1.2x8	.945	.591	.445	.52	.422	.388	.355
450-SL4512	B1	Gray	Black	1.2x8	1.02	.433	.433	.52	.422	.388	.355
450-SL4514	B2	Gray	Black	1.2x4	1.02	.433	.433	.52	.422	.388	.355
450-SL5512	B2	Gray	Black	1.2x4	.945	.354	.425	.52	.422	.388	.355
450-SL6112	B3	Red	White	1.2x18	.953	.453	.406	.55	.444	.40	.377
450-SL6312	B3	Blue	White	1.2x18	.953	.453	.406	.55	.444	.40	.377
450-SL6512	B3	Gray	Black	1.2x18	.953	.453	.406	.55	.444	.40	.377
450-SL6612	B3	Black	White	1.2x18	.953	.453	.406	.55	.444	.40	.377
450-SL6712	B3	White	Black	1.2x18	.953	.453	.406	.55	.444	.40	.377




## TWO-COLOR RUBBERIZED KNOBS

These rubberized two color knobs provide a clean, modern look with precise control. Available in several color combinations, these knobs provide a stylish look to any front panel.

MOUSER STOCK NO.	Fig.	Body Color	Line Color	Dimensions: in.			Price Each				
				Shaft	Dia.	Height	1	10	100	500	
<b>D Shaft (6mm)</b>											
450-4660	A	Gray	Black	.236	.52	.61	.66	.443	.408	.373	.341
450-4661	A	Gray	Red	.236	.52	.61	.66	.443	.408	.373	.341
450-4662	A	Gray	Yellow	.236	.52	.61	.66	.443	.408	.373	.341
450-4663	A	Gray	Blue	.236	.52	.61	.66	.443	.408	.373	.341
450-4664	A	Gray	Green	.236	.52	.61	.66	.443	.408	.373	.341
450-4667	A	Gray	Gray	.236	.52	.61	.66	.443	.408	.373	.341
450-4760	A	Black	White	.236	.52	.61	.66	.443	.408	.373	.341
450-4761	A	Black	Red	.236	.52	.61	.66	.443	.408	.373	.341
450-4762	A	Black	Yellow	.236	.52	.61	.66	.443	.408	.373	.341
450-4763	A	Black	Blue	.236	.52	.61	.66	.443	.408	.373	.341
450-4764	A	Black	Green	.236	.52	.61	.66	.443	.408	.373	.341
450-4765	A	Black	Gray	.236	.52	.61	.66	.443	.408	.373	.341
<b>D Shaft (6.4mm)</b>											
450-4641	B	Gray	Red	.252	.52	.61	.49	.426	.373	.341	.311
450-4642	B	Gray	Yellow	.252	.52	.61	.49	.426	.373	.341	.311
450-4643	B	Gray	Blue	.252	.52	.61	.49	.426	.373	.341	.311
450-4644	B	Gray	Green	.252	.52	.61	.49	.426	.373	.341	.311
450-4646	B	Gray	Black	.252	.52	.61	.49	.426	.373	.341	.311
450-4647	B	Gray	Gray	.252	.52	.61	.49	.426	.373	.341	.311
450-4741	B	Black	Red	.252	.52	.61	.49	.426	.373	.341	.311
450-4742	B	Black	Yellow	.252	.52	.61	.49	.426	.373	.341	.311
450-4743	B	Black	Blue	.252	.52	.61	.49	.426	.373	.341	.311
450-4744	B	Black	Green	.252	.52	.61	.49	.426	.373	.341	.311
450-4745	B	Black	Gray	.252	.52	.61	.49	.426	.373	.341	.311
450-4747	B	Black	White	.252	.52	.61	.49	.426	.373	.341	.311



MOUSER STOCK NO.	Fig.	Body Color	Line Color	Dimensions: in.			Price Each				
				Shaft	Dia.	Height	1	10	100	500	
<b>T18 (6mm, 18 Tooth Knurled Shaft)</b>											
450-1518	C	Gray	Red	.236	.52	.61	.49	.426	.373	.341	.311
450-2518	C	Gray	Yellow	.236	.52	.61	.49	.426	.373	.341	.311
450-3518	C	Gray	Blue	.236	.52	.61	.49	.426	.373	.341	.311
450-4518	C	Gray	Green	.236	.52	.61	.49	.426	.373	.341	.311
450-6518	C	Gray	Black	.236	.52	.61	.49	.426	.373	.341	.311
450-7518	C	Gray	Gray	.236	.52	.61	.49	.426	.373	.341	.311
450-1C618	C	Black	Red	.236	.52	.61	.49	.426	.373	.341	.311
450-2C618	C	Black	Yellow	.236	.52	.61	.49	.426	.373	.341	.311
450-3C618	C	Black	Blue	.236	.52	.61	.49	.426	.373	.341	.311
450-4C618	C	Black	Green	.236	.52	.61	.49	.426	.373	.341	.311
450-5C618	C	Black	Gray	.236	.52	.61	.49	.426	.373	.341	.311
450-7618	C	Black	White	.236	.52	.61	.63	.425	.392	.358	.327




## COLOR-CODED PLASTIC KNOBS AND CAPS

These push on control knobs can be customized by using color coded caps. Multiple colors are available from stock. Order color coded caps separately. \*T18 is a 6mm, 18 tooth knurled shaft.

MOUSER STOCK NO.	Fig.	Color	Shaft Type	Dimensions: in.			Price Each				
				Shaft	Dia.	Height	1	10	100	500	
450-AA150	A1	Black	D Shaft	.236	.59	.75	.34	.288	.244	.222	.199
450-AA151	A1	Lt. Grey	D Shaft	.236	.59	.75	.34	.288	.244	.222	.199
450-AA152	A2	Lt. Grey	T18 *	.236	.59	.75	.34	.288	.244	.222	.199
450-AA180	A3	Black	D Shaft	.252	.71	.63	.34	.288	.244	.222	.199
450-AA181	A2	Black	T18 *	.236	.71	.63	.34	.288	.244	.222	.199
450-AA190	A3	Black	D Shaft	.252	.79	.75	.34	.288	.244	.222	.199
450-AA191	A2	Dk. Grey	T18 *	.252	.79	.75	.34	.288	.244	.222	.199
450-AA192	A2	Black	T18 *	.252	.79	.75	.34	.288	.244	.222	.199
450-AA193	A4	Black	Brass- with set screw	.252	.79	.75	.84	.702	.637	.583	.530

MOUSER STOCK NO.	Fig.	Cap Color	Pointer Color	Fits Knob	Price Each			
					1	10	100	500
450-CP151	B	Red	White	450-AA150, 450-AA151, 450-AA152	.28	.233	.166	.133
450-CP153	B	Blue	White		.28	.233	.166	.133
450-CP155	B	Grey	White		.28	.233	.166	.133
450-CP156	B	Black	White		.28	.233	.166	.133
450-CP157	B	White	Black	.28	.233	.166	.133	
450-CP185	B	Grey	Black	450-AA180, 450-AA181	.28	.233	.166	.133
450-CP186	B	Black	White		.28	.233	.166	.133
450-CP191	B	Red	White	450-AA190, 450-AA191, 450-AA192, 450-AA193	.28	.233	.166	.133
450-CP192	B	Yellow	White		.28	.233	.166	.133
450-CP193	B	Blue	White		.28	.233	.166	.133
450-CP194	B	Green	White		.28	.233	.166	.133
450-CP195	B	Grey	White	.28	.233	.166	.133	
450-CP196	B	Black	White	.28	.233	.166	.133	



## TWO-COLOR KNOBS

"Soft Touch" Knobs  
These rubberized "soft touch" two color knobs provide a clean look with tactile control. Available in several pointer colors, these knobs provide a stylish look to any front panel.

MOUSER STOCK NO.	Fig.	Color	Pointer Color	Dimensions: in.			Price Each			
				Shaft	Dia.	Height	1	10	100	500
<b>T18 (6mm, 18 Tooth Knurled Shaft)</b>										
450-BA160	A1	Black	Red	.236	.63	.57	.60	.444	.40	.377
450-BA260	A1	Black	Yellow	.236	.63	.57	.60	.444	.40	.377
450-BA360	A1	Black	Blue	.236	.63	.57	.60	.444	.40	.377
450-BA460	A1	Black	Green	.236	.63	.57	.60	.444	.40	.377
450-BA760	A1	Black	White	.236	.63	.57	.60	.444	.40	.377
<b>D Shaft</b>										
450-BA161	A2	Black	Red	.236	.63	.57	.60	.444	.40	.377
450-BA261	A2	Black	Yellow	.236	.63	.57	.60	.444	.40	.377
450-BA361	A2	Black	Blue	.236	.63	.57	.60	.444	.40	.377
450-BA461	A2	Black	Green	.236	.63	.57	.60	.444	.40	.377
450-BA761	A2	Black	White	.236	.63	.57	.60	.444	.40	.377
450-BA600	A2	Black	None	.236	.63	.57	.60	.444	.40	.377

MOUSER STOCK NO.	Fig.	Color	Pointer Color	Dimensions: in.			Price Each			
				Shaft	Dia.	Height	1	10	100	500
450-WB118	B3	Black	Red line/top	.252	.67	.76	.75	.501	.457	.412
450-WB218	B3	Black	Yellow line/top	.252	.67	.76	.75	.501	.457	.412
450-WB318	B3	Black	Blue line/top	.252	.67	.76	.75	.501	.457	.412
450-WB418	B3	Black	Green line/top	.252	.67	.76	.75	.501	.457	.412