

# XELTEK Programmiers



RoHS Compliant This product is RoHS compliant.

Programmiers

Xeltek

## PROGRAMMERS

### SuperPro ISO1

#### Features:

- Supports 6,537 IC devices from 139 manufacturers
- High speed ARM9 CPU based hardware engine. Programming speed adjustable for complicated application environments brought by user target board, length of ISP cable etc.
- Supports ISP programming of devices with I2C, SPI, CAN, UART, BDW, MW, JTAG, or any other serial port.
- Comes with ATE interface.
- Supports Linux O/S
- Two operation modes: Stand-alone and PC-Host mode
- DLL, API or Virtual Com communication command set available for third party application (Optional)
- USB 2.0 interface to PC for data communication and control
- Over-current and ESD protection to protect your equipment
- Lightest ever: Mechanical size: 137mm (L) x 87mm (W) x 47mm (H)



RoHS Compliant



MOUSER STOCK NO.	Xeltek Part No.	Price Each
<a href="#">674-SP-ISO1-ISP</a>	SUPERPRO ISO1-ISP	1195.00


### SuperPro 500P Programmer

#### Features:

- Fastest cheapest programmer: With ARM7 MCU it gives ultra-fast programming experience
- Programs devices with Vcc as low as 1.2V
- Built-in 48 universal pin drivers
- CE and RoHS compliant



RoHS Compliant



MOUSER STOCK NO.	Xeltek Part No.	Price Each
<a href="#">674-SP500P</a>	SUPERPRO500P	845.00


### SuperPro 501S Programmer

#### Features:

- Supports over 35,000 devices
- Fastest cheapest stand-alone programmer: With ARM7 MCU it gives ultra-fast programming experience
- Two programmers in one, a double value: PC mode for engineering and stand-alone mode for production. The programmer operates in either PC hosted mode or stand-alone mode
  - Under PC hosted mode, a PC controls the programmer via a high-speed USB connection to program a chip
  - Under stand-alone mode, the user controls the programmer via 20-characters, 4-line LCD display with 6-KEY keypad
  - A CF (compact flash) card stores the project files
- Built-in 48 universal pin drivers
- CE and RoHS compliant



RoHS Compliant



MOUSER STOCK NO.	Xeltek Part No.	Price Each
<a href="#">674-SP501S</a>	SUPERPRO501S	995.00

### SuperPro 501S N\*Cluster

#### Features:

Supports over 29,000 devices.  
SuperPro 501S N4 Cluster is composed of x4 units of our newest and fastest SuperPro 501S programmer w/ 4 pieces of 512 CF cards. As a SuperPro 501S N\*Cluster owner, users get two programmers packaged into one! SuperPro 501S N\*Cluster owners, have the benefit of using it as:

1. A universal programmer for engineering application
2. Secondly, as a manufacturing programmer for volume production

For production operation, Superpro 501S N\*Cluster operates in stand-alone (without a PC attached) mode. Each unit supports manufactures including EPROM, EEPROM and Flash memory, PIC, AVR and other popular microcontrollers and PLDs. By operating multiple programmers simultaneously you can use them in high volume production environment



RoHS Compliant



MOUSER STOCK NO.	Xeltek Part No.	Price Each
<a href="#">674-SP501S-CLUSTER</a>	SUPERPRO501S-CLUSTER	3980.00

## SOCKET ADAPTERS



RoHS Compliant

MOUSER STOCK NO.	Xeltek Part No.	Package Type	Type	Pitch (mm)	Price Each
<a href="#">674-CX3001</a>	CX3001	QFP-32	COVER	0.8	260.00
<a href="#">674-CX3002</a>	CX3002	QFP-44	COVER	0.8	285.00
<a href="#">674-CX1004</a>	CX1004	TSOP-48	OPENTOP	0.5	235.00
<a href="#">674-CX1006</a>	CX1006	TSOP-40	OPENTOP	0.5	260.00
<a href="#">674-CX2032</a>	CX2032	PLCC-32	OPENTOP	1.27	185.00
<a href="#">674-CX2044</a>	CX2044	PLCC-44	OPENTOP	1.27	185.00
<a href="#">674-CX3011</a>	CX3011	QFP-64	COVER	0.5	400.00
<a href="#">674-CX3043</a>	CX3043	QFP-100	OPENTOP	0.5	400.00
<a href="#">674-SA026</a>	SA026	TSOP-24	OPENTOP	0.65	105.00
<a href="#">674-A245</a>	SA245A	QFP-44	CLAM SHELL	0.8	225.00
<a href="#">674-SA404A</a>	SA404A	SOIC-28	CLAM SHELL	1.27	115.00
<a href="#">674-SA409T</a>	SA409T	TSOP-40	CLAM SHELL	0.5	185.00
<a href="#">674-SA602A</a>	SA602A	SOP-8	OPENTOP	1.27	105.00
<a href="#">674-SA605B</a>	SA605B	SOIC-20	OPENTOP	1.27	115.00
<a href="#">674-SA636</a>	SA636	QFP-32	CLAM SHELL	0.8	185.00