

# TE D-Sub Connectors and Hardware Kits

RoHS Compliant This page of product is RoHS compliant.



## SERIES 109 CONNECTORS

(FOR MIL-C-24308)

- Shell: steel, cadmium plated
- Standard mount

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	TE Part No.	Fig.	Shell Size	No. of Positions	Price Each		
					1	10	100
<b>Plugs</b>							
571-1757819-1	1757819-1	A	1	9	8.26	7.22	5.84
571-1757819-2	1757819-2	A	2	15	9.52	7.98	6.93
571-1757819-3	1757819-3	A	3	25	10.87	8.98	7.80
571-1757819-4	1757819-4	A	4	37	12.87	10.53	9.07
<b>Receptacles</b>							
571-1757820-1	1757820-1	B	1	9	3.37	3.09	2.85
571-1757820-2	1757820-2	B	2	15	9.52	7.98	6.93
571-1757820-3	1757820-3	B	3	25	7.63	6.83	5.92
571-1757820-4	1757820-4	B	4	37	12.85	10.83	9.28

### Connector Contacts for Series 109 Connectors

- Wire Size: 20-24 AWG

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	TE Part No.	Fig.	Type	Price Each		
				1	100	1000
571-2050891	205089-1	C	Pin	.55	.488	.428
571-2050901	205090-1	C	Socket	.57	.527	.436

### Tools

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	AMP Part No.	Description	Price Each
571-910672	91067-2	Insertion/Extraction Tool	9.25
571-6019661	601966-1	Crimp Tool	667.11

## HARDWARE AND ACCESSORIES

### Male Screw Retainers Kits, Thread Size 4-40

Includes: male screw - retention clip - stainless steel

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	TE Part No.	Fig.	Chromate Color	Price Each		
				1	10	100
<b>For HDP-20, Metal Shell Connectors</b>						
571-5205980-1	5205980-1	D	Yellow	.95	.822	.706
571-5205980-4	5205980-4	D	Clear	1.07	.89	.788
<b>For HDF-20, Metal-Shell and All-Plastic Connectors</b>						
571-5746881-1	5746881-1	E	Yellow	1.98	1.93	1.53

### Female Screw Lock Kits, Thread Size 4-40

Includes two complete sets of: female screw, two flat washers, lock washer, and hex nut or square nut. Material and finish for all parts: cold rolled steel, zinc plated clear or yellow chromate.

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	TE Part No.	Fig.	Chromate Color	Price Each		
				1	10	100
<b>For HD-20 Right Angle Connectors, Plastic Shell</b>						
571-5207952-1	5207952-1	F	Yellow	2.98	2.75	2.27
571-5207952-3	5207952-3	F	Clear	2.65	2.40	2.22
<b>For HDE Connectors, Metal/All Plastic Shell</b>						
571-5745563-1	5745563-1	G	Yellow	2.10	2.06	1.66
571-5745563-3	5745563-3	G	Clear	1.94	1.79	1.55
<b>For HDP/HDF Connectors, Metal Shell/All Plastic</b>						
571-5205817-1	5205817-1	G	Yellow	1.06	.973	.903
571-5205817-3	5205817-3	G	Clear	1.87	1.58	1.26
<b>For HD Connectors, All Plastic with Integral Standoffs</b>						
571-5207719-1	5207719-1	G	Yellow	1.32	1.09	1.02
571-5207719-3	5207719-3	G	Clear	1.68	1.52	1.31

### Standard Spring Latch

Includes: two stainless steel spring latches

- For shell size 1-4

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	TE Part No.	Fig.	Price Per Pkg. of 2		
			1	10	100
571-745779-2	745779-2	H	1.21	1.18	1.09

### Locking Post Assembly Kit

Includes two complete assemblies of: 4-40 post, two flat washers, lock washer, and hex nut. Material for all parts: cold rolled steel, zinc plated yellow chromate.

For quantities greater than listed, call for quote.


MOUSER STOCK NO.	TE Part No.	Fig.	Price Per Pkg. of 2		
			1	10	100
571-5206514-1	5206514-1	I	2.67	2.34	2.00

### Slide Latch Kit for Use with Shell Size 2

Includes: slide latch - steel and two complete assemblies of screw, two washers, and hex nut - steel, zinc plated yellow chromate.

For quantities greater than listed, call for quote.

MOUSER STOCK NO.	TE Part No.	Fig.	Price Per Pkg. of 2		
			1	10	100
571-5745583-5	5745583-5	J	3.03	2.75	2.33



"D" Connectors

TE Connectivity