



## Trace Tech No-Clean Flux Pen

2507

TraceTech board repair system allows any level of technician to quickly perform quality board repairs in-house without the use of expensive equipment or time-consuming and unsightly jumpers. Meets IPC board repair standards. Other TraceTech pens are available to allow quick, convenient, and high quality board repair and rework.



### No-clean flux applicator pen for PCB rework and repair

Resin and halide-free no-clean flux has excellent wetting abilities and leave no problematic residues. Excellent for prototyping, rework, and repair and to provide extra wetting for lead-free wire solder.



- Excellent wetting
- Works with lead and lead-free solders
- Non-ozone depleting
- No cleaning necessary if fully activated
- Boost wetting for lead-free wire solder

### Product Packaging

2507-N  
Trace Tech No-Clean Flux Pen  
11.5 ml  
12 units/case

2507-N100  
No Clean Flux Dispensing Pen  
11.5 ml  
100 units/case



Chemical & Physical Properties	
Appearance	Clear, colorless liquid
Odor	Alcohol odor
Flash Point	53°F
VOC (EPA)	797 g/l
VOC (CARB)	
Boiling Point	80°C (176°F)
Density	

### Chemical Composition

CHEMICAL NAME	CAS #
2-Propanol	67-63-0

Non-ionic flux mixture (Proprietary  
non-hazardous blend)





---

## Environmental Policy

Techspray is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

---

## Resources

Techspray products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray products in the United States, call the technical sales department at 800-858-4043, email [tsales@techspray.com](mailto:tsales@techspray.com) or visit our web site at: [www.techspray.com](http://www.techspray.com).

### North America

Techspray  
P.O. Box 949  
Amarillo, TX 79105  
800-858-4043  
email: [tsales@techspray.com](mailto:tsales@techspray.com)

### Europe

ITW Contamination Control BV  
Saffierlaan 5  
2132 VZ Hoofddorp  
The Netherlands  
+31 88 1307 400  
email: [info@itw-cc.com](mailto:info@itw-cc.com)

### Countries Outside US

Call to locate a distributor in your country

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.