PIN RECEPTACLES

PIN RECEPTACLES
WITH ORGANIC FIBRE PLUG® SOLDER BARRIER
(SEE SPECIFIC CONTACT RANGE ON PAGES 254 - 262)

0337
0337-0-XX-XX-15-XX-10-0
Solder mount in Ø 1,68 ± 0,08 PTH
#15 Contact for Ø 0,51 - 0,81 pins
Also available on 8mm wide carrier tape:
6,000 parts per 330mm reel



4280
4280-0-XX-XX-16-XX-10-0
Solder mount in Ø 1,7 ± 0,08 PTH
#16 Contact for Ø 0,56 - 0,86 pins
Also available on 8mm wide carrier tape:
6,000 parts per 330mm reel



5280
5280-0-XX-XX-16-XX-40-0
Solder mount in Ø 1,7 ± 0,08 PTH
#16 Contact for Ø 0,56 - 0,86 pins
Also available on 16mm wide carrier tape:
2,200 parts per 330mm reel



0332
0332-0-XX-XX-18-XX-10-0
Solder mount in Ø 2,01 ± 0,08 PTH
#18 Contact for Ø 0,94 - 1,09 pins
Also available on 16mm wide carrier tape:
2,200 parts per 330mm reel



0479
0479-0-XX-XX-34-XX-10-0
Solder mount in Ø 1,96 ± 0,08 PTH
#34 Contact for Ø 0,81 - 1,17 pins
Also available on 16mm wide carrier tape:
2,200 parts per 330mm reel



0375
0375-0-XX-XX-02-XX-10-0
Solder mount in Ø 2,21 ± 0,08 PTH
#02 Contact for Ø 1,02 - 1,27 pins
Also available on 12mm wide carrier tape:
4,500 parts per 330mm reel



0353
0353-0-XX-XX-03-XX-10-0
Solder mount in Ø 2,69 ± 0,08 PTH
#03 Contact for Ø 1,02 - 1,52 pins
Also available on 12mm wide carrier tape:
1,300 parts per 330mm reel



0384
0384-0-XX-XX-23-XX-10-0
Solder mount in Ø 2,67 ± 0,08 PTH
#23 Contact for Ø 1,14 - 1,65 pins
Also available on 12mm wide carrier tape:
2,000 parts per 330mm reel



0376
0376-0-XX-XX-07-XX-10-0
Solder mount in Ø 3,38 ± 0,08 PTH
#07 Contact for Ø 1,65 - 2,08 pins
Also available on 16mm wide carrier tape:
1,500 parts per 330mm reel



0321
0321-0-XX-XX-08-XX-10-0
Solder mount in Ø 3,66 ± 0,08 PTH
#08 Contact for Ø 2,13 - 2,59 pins
Also available on 16mm wide carrier tape:
1,700 parts per 330mm reel



3435
3435-0-XX-XX-47-XX-04-0
Solder mount in Ø 1,17 ± 0,08 PTH
#47 Contact for Ø 0,64 - 0,91 and
0,64 square pins



SPECIFICATIONS:

Shell Material: Brass Alloy 360, 1/2 Hard

Contact Material: Beryllium Copper Alloy 172, HT

Solder Barrier: Organic Fibre Plug®

Dimensions: Millimeters

Tolerances On: Lengths: ± 0,13
Diameters: ± 0,051
Angles: ± 2°

RoHS-2 2011/65/EU

ORDER CODE: XXXX - 0 - XX - XX - XX - XX - XX - 0

BASIC PART #

SPECIFY PACKAGING:
43 Discrete Receptacles
67 Supplied on 330mm Reels

SPECIFY SHELL FINISH:
01 5,08µm TIN/LEAD OVER NICKEL
◆ **80** 5,08µm TIN OVER NICKEL (RoHS)

CONTACT:
#02, #07, #08, #15, #16, #18, #23, #34 or #47 CONTACT (DATA ON PAGES 254 - 262)

SPECIFY CONTACT FINISH:
◆ **27** 0,76µm GOLD OVER NICKEL (RoHS)
02 2,54µm TIN/LEAD OVER NICKEL
◆ **80** 5,08µm TIN OVER NICKEL (RoHS)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:
0375-0-67-80-02-27-10-0