

SCC ground cords provide a reliable efficient method for grounding table mats, floor mats, wrist straps and benches. The common ground cords provide a common ground point required by ESD S-6.1 and ANSI/ESD-S20.20.

## **CGC151M**

### *Common Ground Cord*

This common point ground cord connects two wrist straps and a work surface to ground, assuring that all parts are at the same ground potential. Easy to install. Simply snap it to a mat or work surface. Plug in the wrist strap coil cord, and connect the ring terminal to ground.



- Provides the common ground point required in EIA 625, ESDA S6 and ANSI/ESD-S20.20
- Tough vinyl cord and strain relief provide a long service life.
- Long, 15 foot cord.
- 3/8"(10mm) stud (male) for mat connection.
- #10 ring terminal for ground connection.

## **LPCGC151M**

### *Low Profile Common Ground Cord*

With a low profile top, this common point ground cord connects two wrist straps and a work surface to ground, assuring that all parts are at the same ground potential. Easy to install. Simply snap it to a mat or work surface. Plug in the wrist strap coil cord, and connect the ring terminal to ground. Provides holes for permanent mounting to a bench.



- Low profile design.
- Provides the common ground point required in EIA 625, ESDA S6 and ANSI/ESD-S20.20
- Tough vinyl cord and strain relief provide a long service life.
- Long, 15 foot cord.
- 3/8"(10mm) for mat connection.
- #10 ring terminal for ground connection.

## **FGC151M**

### *Mat Ground Cord*

Perfect for grounding floor mats, runners, and table mats. This 15 foot ground cord makes reaching ground easy. Easy to install. Simply snap it to a mat and connect the ring terminal to ground. The beveled cap prevents the snap from being removed by a chair or cart. Cord is terminated with a ring terminal.



- Tough vinyl cord and strain relief provide a long service life.
- Long, 15 foot cord.
- 3/8"(10mm) stud (male) for mat connection.
- #10 ring terminal for ground connection

#### **Item Numbers:**

CGC151M	Common Ground Cord w -3/8"(10mm) stud
LPCGC151M	Low Profile Common Ground Cord w -3/8"(10mm) stud
LPCGC151M-10	Low Profile Common Ground Cord w -3/8"(10mm) socket
FGC151M	Ground Cord w -3/8"(10mm) stud

#### **Specifications:**

Length:	15 ft
Snap:	3/8"(10mm)
Ground Connection:	#10 ring terminal
Insulation:	PU/PVCWire: 18 AWG 65 strand high flex
Resistor:	1 meg mat to gnd
Color:	Black

P R O D U C T   D A T A   S H E E T

## **Ground Cords**

**PRODUCT**  
GROUND CORDS

**ITEM NUMBER**  
SEE ABOVE

**DATASHEET**  
1138-A



US and Canada: 866-722-3736  
 Fax: 866-722-3735  
 Intl: 919-774-3808  
 Fax: 919-774-1287  
 3010 Lee Avenue Sanford, NC 27330  
 email: info@staticcontrol.com  
 www.**StaticControl.com** ©