

C1

HD D-sub 44P MALE CONNECTOR

C2

HD D-sub 44P MALE CONNECTOR

WIRING TABLE

PAIR NO.	C.1	C.2
1	1	1
	2	2
2	3	3
	4	4
3	5	5
	6	6
4	7	7
	8	8
5	9	9
	10	10
6	11	11
	12	12
7	13	13
	14	14
8	15	15
	16	16
9	17	17
	18	18
10	19	19
	20	20
11	21	21
	22	22

PAIR NO.	C.1	C.2
12	23	23
	24	24
13	25	25
	26	26
14	27	27
	28	28
15	29	29
	30	30
16	31	31
	32	32
17	33	33
	34	34
18	35	35
	36	36
19	37	37
	38	38
20	39	39
	40	40
21	41	41
	42	42
22	43	43
	44	44

TABLE.1

HARTING P/N	Length(mm)
33562130500023	500
33562131000024	1000
33562131500022	1500
33562132000025	2000
33562135000026	5000
33562121000027	10000

NOTES:

1.) CABLE MUST BE PERFORMED CONTINUITY TEST AND HI-POT TEST (300VDC).

2.) OPERATING TEMPERATURE = 0°TO +80°C

3.) WHITE LABEL CONTENT:

CWK/YR-XXXXX-X-XX HARTING P/N

4.) THE CABLE SHOULD BE PACKED BY A PLASTIC BAG AND STICK THE LABEL WITH P/N CONTENT ON IT, THEN PUT IT INTO THE CARTON(THE QTY ACCORDING TO ACTUAL CONDITION).

5.) EXPORT CARTON SHOULD BE STICKED THE LABEL WITH P/N AND QTY CONTENT.

All Dimensions in mm Original Size DIN A 3			Techn. Character.			Free size tolerances
				Dat.	Name	Scale
			Detail.	03/02/09	Bruce.T	/
			Insp.			HD D-sub 44P MALE DOUBLE ENDED CABLE ASSEMBLY, L=xMM
			Stand.			
			ZHUHAI HARTING LIMITED			TB 33 56 0004. 00
Mod.	Dat.	Name				Sub.

Page /