Rev	AWO #	Description	Date	Appr
-		RELEASED	2/21/20	

APPROVED: _____

DATE: _____ TITLE: _____



Poles	Dimensions	
	A	B
02	.250 [6.35]	.550 [13.97]
03	.500 [12.70]	.800 [20.32]
04	.750 [19.05]	1.050 [26.67]
05	1.000 [25.40]	1.307 [33.20]
06	1.250 [31.75]	1.550 [39.37]
07	1.562 [38.10]	1.800 [45.72]
08	1.750 [44.45]	2.050 [52.07]
09	2.000 [50.80]	2.300 [58.42]
10	2.250 [57.15]	2.550 [64.77]

SPECIFICATIONS:
Material:
Insulator: Nylon 66, rated UL 94V-2
Insulator color: Natural
Contacts: Phosphor Bronze, Tin plated
Electrical:
Current rating: 02~10P: 12 Amp Max (With UL1015, 12AWG)
Contact resistance: 20 mohms max
Insulation resistance: 1,000M ohms min
Dielectric withstanding voltage: 2,900 VAC for 1 minute
Temperature Rating:
-40°C to +105°C
Environmental:
Lead free, RoHS compliant.

RoHS COMPLIANT

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MM [INCHES]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS		DATE
DRAWN	LH	2/21/20
CHECKED	AY1	2/21/20
APPROVED		

ADAM TECH INTERCONNECTS
909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
WIRE TO BOARD, FEMALE, 6.35mm PITCH, WITH POLARIZING PEG, MALE PIN

SIZE	PART NO.	REV.
X	DME-XX-S2-P-S	-

REF: S00124T | SCALE: NTS | SHEET 1 OF 1