

Wiha ESD Safe Pliers & Cutters

ESD Safe Pliers

Needle Nose, Bent 90°



32748 ESD Safe Pliers, Needle Nose Pliers, Bent 90°, Smooth Jaws

Pliers drop-forged for an ideal material structure. Precisely aligned, jaws, hardened. Two component non-slip soft grip handle, ESD Safe Dissipative. ESD standard IEC 61340-5-1

#32748	mm	Inch	Head Wdth	Pkg.	lbs.
	145	5 3/4	12.0mm	1	.21

SHOP

ESD Safe Pliers

Short Round Nose Pliers



32750 ESD Safe Pliers, Short Round Nose Pliers, Smooth Jaws

Pliers drop-forged for an ideal material structure. Precisely aligned, jaws, hardened. Two component non-slip soft grip handle, ESD Safe Dissipative. ESD standard IEC 61340-5-1

#32750	mm	Inch	Head Wdth	Pkg.	lbs.
	120	4 3/4	9.5mm	1	.17

SHOP

ESD Safe Pliers

Short Flat Nose Pliers



32752 ESD Safe Pliers, Short Flat Nose Pliers, Smooth Jaws

Pliers drop-forged for an ideal material structure. Precisely aligned, jaws, hardened. Two component non-slip soft grip handle, ESD Safe Dissipative. ESD standard IEC 61340-5-1

#32752	mm	Inch	Head Wdth	Pkg.	lbs.
	120	4 3/4	9.5mm	1	.16

SHOP



32790 4 Piece ESD Safe Pliers Set In Custom Case Pliers drop-forged for an ideal material structure. Two component non-slip soft grip handle. ESD Safe Dissipative. ESD standard IEC 61340-5-1

#32790 4 piece ESD Safe Pliers Set

Set includes:

32716 4.5" Oval Side Cutters	32746 5.75" Long Nose Pliers
32752 4.75" Flat Nose Pliers	32728 4.375" Oblique Cutters

🔪 lbs. 2.06

SHOP



ESD standard
IEC 61340-5-1



SHOP

32791 11 Pc. Set, 4 ESD Safe Pliers, SYSTEM 4 Slotted & Phillips 5 Pc. Set & 2 ESD Safe Tweezers

Pliers drop-forged for an ideal material structure. Two component non-slip soft grip handle. ESD Safe Precision handle & 4 CVM tool steel blades. Tweezers anti-static conductive, ESD Safe Hypo allergenic, anti-magnetic stainless.

#32791 11 piece ESD Safe Pliers, Tweezers & SYS 4 precision

Set in custom case includes:

ESD Safe Pliers & Cutters

32716 4.5" Oval Side Cutters	32746 5.75" Long Nose Pliers
32752 4.75" Flat Nose Pliers	32728 4.375" Oblique Cutters

SYSTEM 4 Set in separate pouch

28000 ESD Safe Conductive Precision Handle

Slotted: 1.5, 2.0, 3.0 & 4.0

Phillips: 000, 00, 0 & 1

ESD Safe Tweezers: 44501 AA SA ESD 44510 7a SA ESD

🔪 lbs. 2.43