


Silicon LD-MOSFETs

Part Number	P _{OUT} (dBm) TYP	Linear Gain (dB) TYP	Test Conditions				Package Number
			Test f (GHz)	Test P _{IN} (dBm)	V _{DS} (V)	I _{DSQ} (mA)	
NE552R479A	26.0	11	2.45	19	3.0	200	79A
NE5511279A	40.0	15.0	0.9	27	7.5	400	79A
NE5520279A	32.0	10	1.8	25	3.2	700	79A
NE5520379A	35.5	16	0.9	25	3.2	V _{GS} = 2.5V	79A
	33.0	8.5	1.8			V _{GS} = 2.5V	

79A Package



1 HEADQUARTERS

4590 Patrick Henry Drive
Santa Clara, CA 95054-1817
Tel. (408) 988-3500
Fax. (408) 988-0279

Japan Branch Office
Shibuya-Ku, Tokyo
(03) 3486-1361

SALES OFFICES

2 Northern California

Santa Clara, CA
Tel. (408) 588-2247
Fax. (408) 588-2213

3 Southern California

Irvine, CA
Tel. (949) 829-8300
Fax. (949) 829-8992

4 Pacific Northwest and Western Canada

Bellevue, WA
Tel. (425) 883-9511
Fax. (425) 883-9656

5 South Central

Coppell, TX
Tel. (972) 745-1880
Fax. (972) 745-1855

6 Mid Central

Olathe, KS
Tel. (913) 780-1380
Fax. (913) 780-1382

Lakeville, MN
Tel. (952) 469-3962
Fax. (952) 469-9428

* CTC Office

Wauconda, IL
Tel. (847) 487-9906
Fax. (847) 487-9914

7 Northeast

Baltimore, MD
Tel. (410) 682-4111
Fax. (410) 682-4128

8 Metro New York

Hackettstown, NJ
Tel. (908) 850-7600
Fax. (908) 850-7696

9 Southeast

Snellville, GA
Tel. (770) 978-4443
Fax. (770) 978-4262

10 Florida

Altamonte Springs, FL
Tel. (407) 774-7682
Fax. (407) 774-6982

REPRESENTATIVES

11 Colorado/Utah

Albright Engineering
Englewood, CO
Tel. (303) 877-9524
Fax. (303) 768-8328

12 Illinois/Wisconsin

GTSCC
Hoffman Estates, IL
Tel. (847) 781-4010
Fax. (847) 781-4015

13 Indiana/Kentucky

TMC
Carmel, IN
Tel. (317) 844-8462
Fax. (317) 573-5472

14 Michigan

TMC
Sterling Heights, MI
Tel. (586) 731-3016
Fax. (586) 731-9652

15 Ohio

TMC
Cincinnati, OH
Tel. (513) 984-6720
Fax. (513) 936-6515

Independence, OH
Tel. (216) 520-0150
Fax. (216) 520-0190

16 Mexico

Vista Solutions
Zapopan, Jalisco, Mexico
Tel. 011-52-333-836-6319
Fax. 011-52-333-836-6329

17 South America

Vista Solutions
Sao Paulo, Brazil
Tel. 011-55-115-505-8011
Fax. 011-55-115-505-7160

