

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0192210250](#)
Status: **Active**
Overview: [Battery Cable Lugs](#)
Description: Compression Style Ring Tongue Terminal for 4/0 AWG Wire, Stud Size 3/8" (M9), Plated, Barrel Length 19.05mm


Documents:	
3D Model	Product Specification PS-19902-011-001 (PDF)
Drawing (PDF)	Product Specification PS-19902-013-001 (PDF)
3D Model (PDF)	Product Specification PS-19902-017-001 (PDF)
Product Specification PS-19901-017-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification		
CSA		LR18689
UL		E32244
General		
Product Family		Ring and Spade Terminals
Series		19221
Comments		Heavy Duty
Crimp Quality Equipment		Yes
Overview		Battery Cable Lugs
Product Name		Battery Cable Lug
Type		Ring
UPC		800753062498

Physical		
Barrel Type		Closed
Insulation		None
Material - Plating Mating		Tin
Net Weight		38.046/g
Packaging Type		Bag
Plating min - Mating		4.064µm
Plating min - Termination		4.064µm
Stud Size		3/8" (M9)
Termination Interface: Style		Crimp or Compression
Wire Size AWG		4/0

Solder Process Data		
Lead-freeProcess Capability		N/A
Material Info		
Engineering Number		BCL-4038-PL

Reference - Drawing Numbers		
Product Specification		PS-19901-017-001, PS-19902-011-001, PS-19902-013-001, PS-19902-017-001
Sales Drawing		SD-19221-011-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[19221](#) Series

Application Tooling | [FAQ](#)
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hand Crimp Tool for Eyelet Style Copper Lug Terminals 8-4/0 AWG	192840034
Manual Putt Pump Hydraulic System, Die set required	192860117
Die Set (large) for the HHLS Hydraulic Crimper	192900031
Manual tool for Crimping non-insulated 8AWG thru 4/0 Terminals	192940008

Hydraulic Dieless Crimping Tool	<u>638161700</u>
Square "Din" Style Die Set for BCL and VersaKrimp Un-insulated Ring Tongue Terminals and Splices, 4/0 AWG	<u>640038370</u>

This document was generated on 09/13/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19221-0250](#)