

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0511920600

Status:

Active

Overview:

HMC Heavy Duty Rectangular Connectors

Description:

HMC Rectangular Industrial Male Housing, Multi-Module Type, 6 Circuits

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)


Product Specification PS-58691-004-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	I/O Connectors
Series	51192
Application	Panel-Mount
Component Type	Housing
Overview	HMC Heavy Duty Rectangular Connectors
Product Name	HMC
Type	N/A
UPC	800753968615

Physical	
Boot Color	N/A
Circuits (Loaded)	N/A
Circuits (maximum)	6
Color - Resin	Natural
Durability (mating cycles max)	50
Flammability	94V-0
Gender	Male
Lock to Mating Part	Yes
Material - Plating Mating	N/A
Material - Resin	Nylon
Net Weight	3346.600/mg
Number of Rows	2
Orientation	Vertical
PCB Locator	No
Packaging Type	Bag
Panel Mount	N/A
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Polarized to Mating Part	Yes
Polarized to PCB	N/A
Ports	1
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-55° to +125°C
Termination Interface: Style	N/A
Waterproof / Dustproof	No
Electrical	
Current - Maximum per Contact	N/A
Shielded	No
Voltage - Maximum	250V AC / 300V DC

Material Info



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

51192 Series

Mates With

511930600 Housing

Use With

58687 Hood Bracket and 58691 PanelMount Bracket, 5558 GSX Terminal

Reference - Drawing Numbers

Product Specification
Sales Drawing

PS-58691-004-001
SD-51192-002-001

This document was generated on 12/13/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[51192-0600](#)