

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0537800570

Status:


Active

Overview:

PanelMate™ Wire-to-Board Connector System

Description:

1.25mm Pitch PanelMate™ Header, Surface Mount, Right Angle, 1.90mm Height, 5 Circuits



Series image - Reference only

- Documents:
- [3D Model](#)

[Drawing \(PDF\)](#)

[Product Specification PS-51146-010-001 \(PDF\)](#)

[Packaging Specification SPK-53780-001-001 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	PCB Headers
Series	53780
Application	Signal, Wire-to-Board
MolexKits	Yes
Overview	PanelMate™ Wire-to-Board Connector System
Product Name	PanelMate™
UPC	822348185146
Physical	
Breakaway	No
Circuits (Loaded)	5
Circuits (maximum)	5
Color - Resin	Natural
Durability (mating cycles max)	50
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	119.620/mg
Number of Rows	1
Orientation	Right Angle
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.25mm
Polarized to PCB	No
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-40°C to +85°C
Termination Interface: Style	Surface Mount
Electrical	
Current - Maximum per Contact	1.0A
Voltage - Maximum	125V
Material Info	

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -

ED/30/2017 (7 July

2017)

Halogen-Free

Status

Not Low-Halogen

Need more information on product

environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any

non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

53780 Series

Mates With

51146 PanelMate™ Wire-to-Board

Receptacle Housing

Reference - Drawing Numbers

Packaging Specification	SPK-53780-001-001
Product Specification	PS-51146-010-001
Sales Drawing	SD-53780-003, SD-53780-004

This document was generated on 08/29/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[53780-0570](#) [53780-0290](#) [53780-0990](#) [53780-0890](#) [53780-0790](#) [53780-2090](#) [53780-0590](#)