


## Advantages of Using Clips

- **Metal hold-down clips** are ideal for use where high heat or humid conditions are a factor, thus holding their shape and tension. The clips are made of stainless steel and are designed to withstand harsh environments.
- **Plastic ejector/hold-down clips** are ideal in applications where sockets are located in dense or tight areas. These clips allow for quick, safe and firm securing of relays in the sockets with the added benefit that the relay can be ejected with one finger. Plastic clips also aid in keeping operator's fingers away from live circuits. The optional snap-in identification tag allows for custom marking of sockets when used in multi-socket applications.
- **Plastic I.D. clips** are ideal for easy identification of circuits in multi-relay applications. They are designed for labeling and are not ideal for securing the relay in the socket.


### Plastic Ejector Clip




### Metal Hold-Down Clip




### Plastic I.D. Clip






**No Tools Needed!**



## The Complete System Solution!




SECTION 3

**Stainless Steel Hold-Down Clips** made for nearly every application. Ideal for use in harsh environments.


**I.D. Clips** allow for easy identification of circuits in multi-relay applications.

**Newly designed Plastic Hold-Down Clip** secures relays firmly and ejects relays easily.




Hold-down clips colored green for better viewing.

## Metal and Plastic Clips



- Stainless Steel Clips are Designed to be Corrosion Resistant in Harsh Environments and are Ideal for Use Under Shock and Vibration Conditions.



- Plastic Ejector/Hold-Down Clips are Ideal for Use in High-Density, Multi-Socket Applications.

- Plastic Identification Tag is Perfect for Use in Multi-Socket Applications for Custom Identification of Circuits.



**16-781SC**



**16-781IDC**



**16-782SC**



**16-782PC-1**



**16-782IDC**



**16-783SC**




**16-783IDC**



**16-784SC**



**16-784IDC**



**16-1332**




**16-1324**



**16-1342**



**16-1351**



**16-1344**



**16-TDR782SC**



**16-TDRPROSC**

| Socket Part Number | Clip Part Number             | Supersedes        | Relays                              | Remarks                        |
|--------------------|------------------------------|-------------------|-------------------------------------|--------------------------------|
| 70-124-1           | 16-1351                      | 16-722-2          | 788, 711, 388J (All)                | Front Back (North South) Mount |
| 70-124-2           | 16-1351                      | 16-722-2          | 788, 711, 388J (All)                | Front Back (North South) Mount |
| 70-178-1           | 16-1351                      | 16-722-2          | 788, 711, 388J (All)                | Front Back (North South) Mount |
| 70-178-2           | 16-1351                      | 16-722-2          | 788, 711, 388J (All)                | Front Back (North South) Mount |
| 70-378-1           | 16-1342                      |                   | 782 (All & Hermetic)                | Side Mount                     |
| 70-378-1           | 16-1324                      |                   | 782C and Hermetic Only              | Front Back (North South) Mount |
| 70-378-1           | 16-TDR782SC                  |                   | TDR782                              | Side Mount                     |
| 70-379-1           | 16-1342                      |                   | 782 (All & Hermetic)                | Side Mount                     |
| 70-379-1           | 16-TDR782SC                  |                   | TDR782                              | Side Mount                     |
| 70-401-1           | 16-1342                      |                   | 782 With .187 Term.                 | Side Mount                     |
| 70-401-1           | 16-1324                      |                   | 782C With .187 Term. Only           | Front Back (North South) Mount |
| 70-402-1           | 16-1342                      |                   | 782 With .187 Term.                 | Side Mount                     |
| 70-402-1           | 16-1324                      |                   | 782C With .187 Term. Only           | Front Back (North South) Mount |
| 70-459-1           | 16-1342                      | 16-1329           | 782 With .187 Term.                 | Side Mount                     |
| 70-461-1           | 16-1342                      | 16-1328           | 782 (All & Hermetic)                | Side Mount                     |
| 70-461-1           | 16-TDR782SC                  |                   | TDR782                              | Side Mount                     |
| 70-463-1           | 16-1351                      | 16-1329           | 788 (All), 785                      | Side Mount                     |
| 70-463-1           | 16-1344                      |                   | TDR (SOX/SRX) B                     | Side Mount                     |
| 70-464-1           | 16-1351                      | 16-1352           | 750 (All), 750H                     | Side Mount                     |
| 70-464-1           | 16-1344                      |                   | TDRSOXP, 712                        | Side Mount                     |
| 70-464-1           | 16-TDRPROSC                  |                   | TDRPRO                              | Side Mount                     |
| 70-465-1           | 16-1351                      | 13-1352           | 750 (All), 750H, 755                | Side Mount                     |
| 70-465-1           | 16-1344                      |                   | TDR (SRXP), 712                     | Side Mount                     |
| 70-465-1           | 16-TDRPROSC                  |                   | TDRPRO                              | Side Mount                     |
| 70-750DL8-1        | 16-1332                      |                   | 750 (All)                           | Front Back (North South) Mount |
| 70-750DL8-1        | 16-1344                      |                   | TDRSOXP                             | Side Mount                     |
| 70-750DL8-1        | 16-1351                      | 16-1352           | 750H                                | Side Mount                     |
| 70-750DL8-1        | 16-TDRPROSC                  |                   | TDRPRO                              | Side Mount                     |
| 70-750DL11-1       | 16-1332                      |                   | 750 (All)                           | Front Back (North South) Mount |
| 70-750DL11-1       | 16-1344                      |                   | TDRSRXP                             | Side Mount                     |
| 70-750DL11-1       | 16-1351                      | 16-1352           | 750H                                | Side Mount                     |
| 70-750DL11-1       | 16-TDRPROSC                  |                   | TDRPRO                              | Side Mount                     |
| 70-750E8-1         | 16-1351                      | 16-1352           | 750 (All), 750H                     | Side Mount                     |
| 70-750E8-1         | 16-1344                      |                   | 750 (All), TDRSRXP, 712             | Side Mount                     |
| 70-750E8-1         | 16-TDRPROSC                  |                   | TDRPRO                              | Side Mount                     |
| 70-750E11-1        | 16-1351                      | 16-1352           | 750 (All), 750H, 755                | Side Mount                     |
| 70-750E11-1        | 16-1344                      |                   | TDRSRXP, 712                        | Side Mount                     |
| 70-750E11-1        | 16-TDRPROSC                  |                   | TDRPRO                              | Side Mount                     |
| 70-750EL8-1        | 16-1351                      | 16-1352           | 750 (All), 750H                     | Side Mount                     |
| 70-750EL11-1       | 16-1351                      | 16-1352           | 750 (All), 750H, 755                | Side Mount                     |
| 70-781D5-1A        | 16-781SC                     | 16-1326           | 781 (All)                           | Side Mount                     |
| 70-781D5-1A        | 16-781IDC                    | 16-1327 (Plastic) | 781 (All)                           | Side Mount                     |
| 70-781F-1          | 16-781SC                     | 16-1326           | 781 (All)                           | Side Mount                     |
| 70-781T-1          | 16-781SC                     | 16-1326           | 781 (All)                           | Side Mount                     |
| 70-782D8-1         | 16-1342                      |                   | 782 With .187 Term.                 | Side Mount                     |
| 70-782D8-1         | 16-782IDC                    | 16-1349 (Plastic) | 782 (All)                           | Side Mount                     |
| 70-782D14-1        | 16-782SC                     |                   | 782, 4 Pole (Plain & Full Featured) | Side Mount                     |
| 70-782D14-1        | 16-782PC                     |                   | 782, 4 Pole (Full Featured)         | Side Mount                     |
| 70-782D14-1        | 16-1342                      |                   | 782 Hermetic Only                   | Side Mount                     |
| 70-782D14-1        | 16-TDR782SC                  |                   | TDR782                              | Side Mount                     |
| 70-782E14-1        | 16-782SC                     |                   | 782, 4 Pole (Plain & Full Featured) | Side Mount                     |
| 70-782E14-1        | 16-782PC-1                   |                   | 782, 4 Pole (Full Featured)         | Side Mount                     |
| 70-782E14-1        | 16-1342                      |                   | 782 Hermetic Only                   | Side Mount                     |
| 70-782E14-1        | 16-TDR782SC                  |                   | TDR782                              | Side Mount                     |
| 70-782EL8-1        | 16-782SC                     |                   | 782 2 Pole (All)                    | Side Mount                     |
| 70-782EL8-1        | 16-782PC-1                   |                   | 782, 2 Pole (Full Featured)         | Side Mount                     |
| 70-782EL8-1        | 16-TDR782SC                  |                   | TDR782                              | Side Mount                     |
| 70-782EL11-1       | 16-782SC                     |                   | 782, 3 Pole (All)                   | Side Mount                     |
| 70-782EL11-1       | 16-782PC-1                   |                   | 782, 3 Pole (Full Featured)         | Side Mount                     |
| 70-782EL14-1       | 16-782SC                     |                   | 782, 4 Pole (Plain & Full Featured) | Side Mount                     |
| 70-782EL14-1       | 16-782PC-1                   |                   | 782, 4 Pole (Full Featured)         | Side Mount                     |
| 70-782EL14-1       | 16-1342                      |                   | 782 Hermetic Only                   | Side Mount                     |
| 70-782EL14-1       | 16-TDR782SC                  |                   | TDR782                              | Side Mount                     |
| 70-783D11-1        | 16-783SC <i>COMING SOON!</i> |                   | 783 (All)                           | Side Mount                     |
| 70-783D11-1        | 16-783IDC                    | 16-1350 (Plastic) | 783 (All)                           | Side Mount                     |
| 70-784D14-1        | 16-784SC                     |                   | 784 (All)                           | Side Mount                     |
| 70-784D14-1        | 16-784IDC                    | 16-1351 (Plastic) | 784 (All)                           | Side Mount                     |
| 70-788EL11-1       | 16-1351                      |                   | 788 (All), 711                      | Side Mount                     |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[16-1326](#) [16-1340](#) [16-1239](#) [16-1321](#) [16-1328](#) [16-722-2](#)