

# Pole Mounting Kit *PMK Series*


## Junction and Wallmount Style - Steel



### Features

- Designed to mount outdoor rated enclosures - Hammond 1414N4, Eclipse, Eclipse Junior and 1418N4 Series
- Individual components allows user to choose mounting configuration and/o components to purchase
- Vertical channel can be lagged directly to pole or attached using optional stainless steel straps
- Vertical channel prevents enclosure from twisting
- Can be used on pole diameters from 4" and up
- Horizontal rails sold in pairs and comes with all hardware needed to secure the enclosure to the rails
- Stainless straps **sold separately** in quantities of 4
  - [PMSTRAP40](#) straps are rated for 450 lbs each and can be used for pole diameters up to 10"
  - [PMSTRAP55](#) straps are rated for 250 lbs each and can be used for pole diameters up to 15"

### Gallery



| Part No.         | Description                                    | Use with Hammond Series |                     |                     |                     |
|------------------|--|-------------------------|---------------------|---------------------|---------------------|
|                  |  | 1414N4                  | Eclipse Junior (EJ) | 1418N4              | Eclipse (EN4SD)     |
| <b>PMV1216GY</b> | Vertical Steel Channel - Qty 1                 | 12"-16" encl height     | 12"-16" encl height | 12"-16" encl height | 12"-16" encl height |
| <b>PMV2024GY</b> | Vertical Steel Channel - Qty 1                 | -                       | -                   | 20"-24" encl height | 20"-24" encl height |
| <b>PMV3036GY</b> | Vertical Steel Channel - Qty 1                 | -                       | -                   | 30"-36" encl height | 30"-36" encl height |
| <b>PMV4248GY</b> | Vertical Steel Channel - Qty 1                 | -                       | -                   | 42"-48" encl height | 42"-48" encl height |
| <b>PMH15GY</b>   | Horizontal Steel Channel - Qty 2               | 12"-16" encl width      | 12"-16" encl width  | 12"-20" encl width  | 12"-20" encl width  |
| <b>PMH25GY</b>   | Horizontal Steel Channel - Qty 2               | -                       | -                   | 24"-30" encl width  | 24" encl width      |
| <b>PMH35GY</b>   | Horizontal Steel Channel - Qty 2               | -                       | -                   | 36" encl width      | 30"-36" encl width  |
| <b>PMSTRAP40</b> | 0.50" x 39" length 316 stainless strap - Qty 4 |                         |                     |                     |                     |
| <b>PMSTRAP55</b> | 0.31" x 55" length 316 stainless strap - Qty 4 |                         |                     |                     |                     |



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[PMV4248GY](#) [PMV2024GY](#) [PMH25GY](#) [PMV1216GY](#) [PMV3036GY](#) [PMH15GY](#) [PMSTRAP55](#) [PMSTRAP40](#)