

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0015045401](#)  
**Status:** **Active**  
**Overview:** [SL Modular Connectors](#)  
**Description:** 2.54mm SL Interim Clip, 40 Circuits

**Documents:**

|                                |  |
|--------------------------------|--|
| <a href="#">3D Model</a>       | <a href="#">Product Specification PS-70400-001 (PDF)</a>       |
| <a href="#">Drawing (PDF)</a>  | <a href="#">Packaging Specification 700130000-PK-000 (PDF)</a> |
| <a href="#">3D Model (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a>           |

**Agency Certification**

|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

**General**

|                |                                       |
|----------------|---------------------------------------|
| Product Family | Accessories                           |
| Series         | <a href="#">70013</a>                 |
| Component Type | Interim Clip                          |
| Overview       | <a href="#">SL Modular Connectors</a> |
| Product Name   | SL                                    |
| UPC            | 800754224864                          |

**Physical**

|                     |           |
|---------------------|-----------|
| Circuits (Loaded)   | 40        |
| Circuits (maximum)  | 40        |
| Color - Resin       | Black     |
| Flammability        | 94V-0     |
| Lock to Mating Part | Yes       |
| Material - Resin    | Polyester |
| Net Weight          | 3.784/g   |
| Number of Rows      | 2         |
| Packaging Type      | Bag       |

**Solder Process Data**


|                             |     |
|-----------------------------|-----|
| Lead-freeProcess Capability | N/A |
|-----------------------------|-----|

**Material Info**

|                    |            |
|--------------------|------------|
| Engineering Number | 70013-0040 |
|--------------------|------------|

**Reference - Drawing Numbers**

|                         |                  |
|-------------------------|------------------|
| Packaging Specification | 700130000-PK-000 |
| Product Specification   | PS-70400-001     |
| Sales Drawing           | 700130000-SD-000 |



*Series image - Reference only*

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Compliant

Not Contained

**Search Parts in this Series**

[70013 Series](#)

**Use With**

[70066](#) SL Crimp Housing. [70058](#) SL Crimp Terminal. [70400](#) SL IDT Connector Assembly. [70430](#) SL FFC Connector. [70450](#) SL Crimp Housing

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[15-04-5401](#)