

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [34803-0212](#)
Status: **Active**
Description: CTX64 Female Terminal, D-Wind, Left Payoff, SAE 20

Documents:

Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-502306-001 (PDF)	Product Literature (PDF)
Application Specification AS-502306-001 (PDF)	

General

Product Family	Crimp Terminals
Series	34803
Application	Signal
Crimp Quality Equipment	Yes
Product Literature Order No	987650-4561
Product Name	CTX64
UPC	884982186828

Physical

Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.124/g
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.40 to 1.90mm
Wire Size AWG	20
Wire Size mm ²	0.50-0.75

Electrical

Current - Maximum per Contact	6A
Voltage - Maximum	14V DC

Material Info

Reference - Drawing Numbers

Application Specification	AS-502306-001
Product Specification	PS-502306-001
Sales Drawing	SD-31301-053, SD-34803-001



image - Reference only

EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Contains SVHC: No**
**Low-Halogen Status
Low-Halogen**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series

[34803Series](#)

Use With

[34729 2.54mm Pitch Stac64™ Right Angle
 Receptacle](#)

Application Tooling | FAQ

*Tooling specifications and manuals are
 found by selecting the products below.
 Crimp Height Specifications are then
 contained in the Application Tooling
 Specification document.*

Global

Description	Product #
Hand Crimp Tool for CTX64 Receptacle Terminal, 0.50, 0.75, 0.85mm ² and 20 AWG	0638193800
Fine Adjust Applicator for CTX64 Mat Seal Receptacle Terminals. For	0639032700

This document was generated on 06/30/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[34803-0212](#) [34803-0212 \(Mouser Reel\)](#) [34803-0212 \(Cut Strip\)](#)