

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0526020679

Status:


Active

Overview:

SlimStack™ 1.00mm Pitch Board-to-Board Connectors

Description:

1.00mm Pitch Receptacle, Dual Row Surface Mount, Vertical Stacking, Mated Stacking Height 20.00mm, 60 Circuits



Series image - Reference only

Documents:

3D Model

Drawing (PDF)

Product Specification 525840000-000 (PDF)

Packaging Specification SPK-52602-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	PCB Receptacles
Series	52602
Application	Board-to-Board, Signal
Overview	SlimStack™ 1.00mm Pitch Board-to-Board Connectors
Product Name	SlimStack
UPC	822348205035
Physical	
Circuits (Loaded)	60
Circuits (maximum)	60
Color - Resin	White
Durability (mating cycles max)	50
Glow-Wire Capable	No
Mated Height	20.00mm
Mated Width	6.60mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	874.920/mg
Number of Rows	2
Orientation	Vertical
PC Tail Length	1.80mm
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.80mm
Packaging Type	Tube
Pitch - Mating Interface	1.00mm
Plating min - Mating	0.254µm
Plating min - Termination	1.016µm
Polarized to PCB	Yes
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-55° to +85°C
Termination Interface: Style	Surface Mount
Electrical	
Current - Maximum per Contact	0.5A
Voltage - Maximum	100V
Material Info	
Reference - Drawing Numbers	
Packaging Specification	SPK-52602-001-001
Product Specification	525840000-000
Sales Drawing	SD-52602-001, SD-52602-002

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per	
-ED/88/2018 (15	
January 2019)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

52602 Series

Mates With

53408

This document was generated on 02/27/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[52602-0679](#)