

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0545962010**
Status: **Active**
Overview: Mini Mi II™ Wire Harness
Description: Mini Mi II Wire-to-Board Receptacle Housing Assembly, 1.25mm Pitch, Single Row, 20 Circuits

Documents:

3D Model	Product Specification PS-54596-021-001 (PDF)
Drawing (PDF)	Product Specification PS-54596-022-001 (PDF)
Product Specification PS-54596-005-001 (PDF)	Product Specification PS-54596-023-001 (PDF)
Product Specification PS-54596-006-001 (PDF)	Product Specification PS-55448-001-001 (PDF)
Product Specification PS-54596-007-001 (PDF)	Product Specification PS-55482-006-001 (PDF)
Product Specification PS-54596-018-001 (PDF)	Product Specification PS-55659-005-001 (PDF)
Product Specification PS-54596-019-001 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-54596-020-001 (PDF)	

General

Product Family	IDT and Solder Connectors
Series	<u>54596</u>
Crimp Quality Equipment	Yes
Overview	<u>Mini Mi II™ Wire Harness</u>
Product Name	Mini Mi II
UPC	800753280977

Physical

Circuits (Loaded)	20
Circuits (maximum)	20
Color - Resin	Natural
Gender	Female
Glow-Wire Capable	No
Lock to Mating Part	None
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	578.600/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.25mm
Plating min - Mating	0.914µm
Plating min - Termination	0.914µm
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	IDT or Pierce
Wire Insulation Diameter	0.80-0.90mm
Wire Size AWG	26, 28


Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	100V

Material Info

Reference - Drawing Numbers

Product Specification	PS-54596-005-001, PS-54596-006-001, PS-54596-007-001, PS-54596-018-001, PS-54596-019-001, PS-54596-020-001,
-----------------------	---



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Prop65

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Compliant

Not Contained

Search Parts in this Series

54596 Series

Mates With

55451 , 55447 , 55454 , 55659 , 55456 ,
55482 , 55450

Sales Drawing

PS-54596-021-001, PS-54596-022-001,
PS-54596-023-001, PS-55448-001-001,
PS-55482-006-001, PS-55659-005-001
SD-54596-004

This document was generated on 09/10/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[54596-2010](#)