


## Product data sheet

### Characteristics

# DZ5CE007D

single conductor insulated cable end - medium  
- 0.75 mm<sup>2</sup> - grey

Product availability: Non-Stock - Not normally stocked in distribution facility



### Main

|                           |                                           |
|---------------------------|-------------------------------------------|
| Commercial Status         | Commercialised                            |
| Range of product          | Cable ends                                |
| Product or component type | Cable end                                 |
| Cable end size            | Medium                                    |
| Standards                 | DIN 46228                                 |
| Type of packing           | String of bags                            |
| Quantity per set          | 10 sets of 100                            |
| Cable cross section       | 0 in <sup>2</sup> (0.75 mm <sup>2</sup> ) |

### Complementary

|                        |                               |
|------------------------|-------------------------------|
| Cable end type         | Single conductor              |
| Additional information | Without marker tag holder     |
| Colour                 | Grey                          |
| Bezel material         | Halogen-free plastic          |
| Tube material          | Copper conforming to ISO 1337 |
| Number of cables       | 1                             |
| AWG gauge              | 20                            |
| Bezel size             | Ø 3.1 mm                      |
| Tube diameter          | 0.06 in (1.6 mm)              |
| Length                 | 0.51 in (13 mm)               |
| Tube length            | 0.32 in (8.2 mm)              |
| CAD overall width      | 0.12 in (3 mm)                |
| CAD overall height     | 0.12 in (3 mm)                |
| CAD overall depth      | 0.51 in (13 mm)               |
| Product weight         | 0.22 lb(US) (0.1 kg)          |

### Environment

|                                       |                            |
|---------------------------------------|----------------------------|
| Product certifications                | UL                         |
| Ambient air temperature for operation | -4...221 °F (-20...105 °C) |

### Ordering and shipping details

|                       |                                                           |
|-----------------------|-----------------------------------------------------------|
| Category              | 22621 - IEC PANEL ACCESSORIES                             |
| Discount Schedule     | I                                                         |
| GTIN                  | 00785901871804                                            |
| Nbr. of units in pkg. | 1000                                                      |
| Package weight(Lbs)   | 0.01                                                      |
| Product availability  | Non-Stock - Not normally stocked in distribution facility |
| Returnability         | N                                                         |
| Country of origin     | FR                                                        |

### Contractual warranty

|        |           |
|--------|-----------|
| Period | 18 months |
|--------|-----------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[DZ5CE007D](#)