

Protect It! 230V Surge Protector with 8 French/Belgian Outlets, French Plug, 1140 Joules, Tel/Coax Protection

MODEL NUMBER: TLP82MASF



Description

Tripp Lite's Protect It!™ TLP82MASF offers economical AC surge suppression for full protection of 220-250V home computers, printers, scanners, and desk lamps. The TLP82MASF offers 8 French type E outlets and a 2 meter AC line cord. Internal safety covers protect against accidental contact with unused outlets.

Features

- Protect It!™ TLP82MASF offers economical AC surge suppression
- 1140 joules AC surge suppression shields equipment from surges and line noise
- 8 French outlets protects computers and peripherals
- 2 m cord with French plug
- Lighted ON/OFF switch with circuit breaker
- Network Protection
- Coax Protection
- Aerial Adapters
- Energy saving master/subordinate outlet array
- Internal safety covers protect against accidental contact with unused outlets

Specifications

OVERVIEW	
UPC Code	037332145383

Highlights

- 8 safety outlets
- 2 m cord
- Network protection
- 1 Line coax protection
- Protected/Grounded LED's
- 1140 joule rating
- Energy saving master/subordinate outlet array

Package Includes

- TLP82MASF surge suppressor
- 1.8 aerial cable and 2 aerial adapters
- 1.8 m gold coax cable
- 1.8 m network cable
- Instruction manual and warranty information



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

INPUT	
Nominal Input Voltage(s) Supported	230V AC
Recommended Electrical Service	230V (220-250V)
Maximum Input Amps	10
Voltage Compatibility (VAC)	220-250
Input Plug Type	French
Input Cord Length (ft.)	6
Right-Angle Plug	Yes
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Output (Watts)	2500
Output Receptacles	(8) French/Belgian
Circuit Breaker (amps)	10
Transformer Accommodation	(5) Yes
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Diagnostic LED Details	Protected/Grounded
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1140
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	Yes
Cable (Coax) Protection	Yes
Cable (Coax) Protection Details	1 line
Network (Ethernet) Protection	Yes
Network (Ethernet) Protection Details	1 line
PHYSICAL	
Color	Black
Antimicrobial Coating	No
Color (AC Line Cord)	Black



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Housing Color	Black
Integrated Keyhole Mounting Slots	No
Receptacle Color	Black
Shipping Dimensions (hwd / cm)	37.59 x 19.00 x 5.51
Shipping Dimensions (hwd / in.)	14.80 x 7.48 x 2.17
Shipping Weight (kg)	1.04
Shipping Weight (lbs.)	2.30
Unit Dimensions (hwd / cm)	31.60 x 11.71 x 4.90
Unit Dimensions (hwd / in.)	12.44 x 4.61 x 1.93
Unit Weight (kg)	0.95
Unit Weight (lbs.)	2.1
SPECIAL FEATURES	
Rotatable Outlets	No
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[TLP82MASF](#)