



MARQUARDT INNOVATIONS

➤ SWITCHES AND SOLUTIONS FOR OFF-ROAD VEHICLES



MARQUARDT



➤ WHERE SOPHISTICATED TECHNOLOGY ALLOWS ROBUST APPLICATIONS.

Push-button switch 1683

- Versions with dust and water protection IP 65/IP 67
- Single- and double-pole in the same compact design
- Optionally with illumination (LED, glow lamp, bulb)
- Double lifting, powerful switching system for currents up to 16 A



Rocker switch 3230

- Externally reliable, self-cleaning snap-action switching system
- Wide variety
- Up to four built-in LEDs



Snap-action switch 1045

- With dust and water protection IP 67
- Built-in separating aid for contact welding
- Rating range of DC signal currents up to 10 (3) A 250 V AC



Rocker switch 1838

- With dust and water protection IP 67
- Innovative sealing
- High currents up to 16 A
- Mechanical life of more than 1 million switching cycles

Micro-signal switches 1065/1075

- For signal currents
- Self-cleaning, redundant contact system
- Noiseless switching system with large overtravel
- Versions with centre 0 position, cable assembly or diagnostic capability
- With dust and water protection IP 67





➤ WHERE PRODUCT VARIETY ALLOWS TAILOR-MADE DESIGNS.

Rocker switch 1930

- ➔ With dust and water protection IP 67
- ➔ Innovative sealing
- ➔ Wide range of options available
- ➔ High currents up to 16 A
- ➔ Optionally with function lighting



Snap-action switches 1055

- ➔ Compact design
- ➔ With dust and water protection IP 67
- ➔ Long over-travel
- ➔ Wide variety
- ➔ Customer-specific cable assembly possible
- ➔ Mechanical life of more than 1 million switching cycles



Tact switch 3006

- ➔ SMT-compatible
- ➔ Low height, short stroke
- ➔ Versions with built-in LED
- ➔ Excellent haptics due to distinctive pressure point
- ➔ Different color and operating force versions



Push-button switch 1660/1670


- ➔ High-quality and robust design
- ➔ Dust and water protection IP 54
- ➔ Distinctive (marked) actuating characteristics



➤ WHERE RELIABLE QUALITY IS FUN.

Snap-action switch 1022

- ➔ With dust and water protection IP 67
- ➔ High switching reliability due to large switching forces
- ➔ Variable fastening possibilities



Key switch 3000/3003

- ➔ Distinctive actuating characteristics
- ➔ One or two operating positions
- ➔ For direct or indirect actuation
- ➔ Long actuating paths
- ➔ Optionally with LED



Rocker switch 3250

- ➔ Extremely reliable, self-cleaning snap-action switching system
- ➔ Dust and water protection IP 66/IP 68
- ➔ Wide variety
- ➔ Up to four built-in LEDs
- ➔ Wide range of accessories
- ➔ Individual rocker design possible



Universal passive entry module (PEM)

- ➔ Keyless standard system
- ➔ With dust and water protection IP 67
- ➔ Wide range of applications
- ➔ Suitable as basic or retrofitting equipment
- ➔ Voltage supply from 8 – 16 V
- ➔ Power consumption, typical 100 mA, maximum 8 A brief



Rocker switch 1830

- ➔ Broad rating range
- ➔ Very wide variety
- ➔ Optionally with covered switching system
- ➔ Designer versions available



BECAUSE CUTTING-EDGE TECHNOLOGY IS BASED ON KNOWLEDGE AND INGENUITY.

The Marquardt group was established in 1925 and, in spite of becoming a Global Player, has remained an independent family enterprise. With its two business areas – Automotive and Switches, Sensors & Controls, the Marquardt group of companies is active all over the world in all the important markets and has offices at 11 locations with more than 4500 employees in all.

Every year, we invest more than seven percent of our turnover in research and development – not to mention the use of modern development tools, simultaneous engineering and an efficient testing system. Moreover, our corporate culture offers ample scope for unfolding the inventive genius of our employees. As a result, new ideas come up time and again, which are materialized into marketable cutting edge technologies.

The Switches, Sensors & Controls division develops, produces and sells its products in a number of industries and applications. Apart from industrial applications, our products are used in power tools, household appliances, cleaning systems, drive technology, heating and air-conditioning technology as well as off-road vehicles. We have the necessary technical know-how, innovative strength, long-term experience and comprehensive manufacturing expertise required in these fields.

This yields innovative and reliable products that feature promising designs tuned to individual requirements. Our products range from the standard switch to complex customer-specific systems. They are suitable for small-scale and large-scale production. With distinct production engineering, worldwide manufacturing options, high quality standards and durability of our products, we achieve customer satisfaction and thereby ensure our competitive ability.


These customer- and market-specific solutions have made Marquardt a strong partner of the power tool and electrical industry and a technology leader. We are at your service in all the international markets.

Off-road vehicles have to prove their functional ability under extreme conditions. Drivers expect absolute reliability and maximum user-friendliness from the components and modules used.

Marquardt switches and solutions contribute greatly to this. They feature a robust technology, reliable quality and individual designs. Our rocker switches have a high level of dust and water protection, up to four built-in LEDs and a wide range of rocker designs. Thus, they guarantee maximum reliability, safety and individuality.

Decades of experience in the automotive industry and many new product developments make us a strong partner, who understands your requirements and transforms them into intelligent solutions.

MARQUARDT INTERNATIONAL.



SWITCHES, SENSORS & CONTROLS LOCATIONS.

>>> GERMANY

Marquardt Mechatronik GmbH
Schloss-Straße 16
78604 Rietheim-Weilheim
Phone +49 (0) 74 24/99-0
Fax +49 (0) 74 24/99-2399
marquardt@marquardt.de
Sales and Development

www.marquardt.de

>>> SWITZERLAND

Marquardt Verwaltungs-GmbH
Niederlassung Schaffhausen
Ernst-Müller-Straße 7
Post Box 952
CH-8201 Schaffhausen
Phone +41 (0) 52/644 3000
Fax +41 (0) 52/644 3060
marquardt@marquardt.ch
Sales, Development and Production

>>> FRANCE

Marquardt France S.A.R.L.
520, avenue Blaise Pascal – Lot n° 5
77557 Moissy Cramayel Cedex
Phone +33 (0) 1/64 13 60 70
Fax +33 (0) 1/64 13 60 71
info@marquardt.fr
Sales

>>> USA

Marquardt Switches Inc.
2711 Route 20 East
Cazenovia, N.Y. 13035-0465
Phone +01 (0) 315/6558050
Fax +01 (0) 315/6558042
info@marqswitch.com
Sales, Development and Production

>>> CHINA

Marquardt Switches
(Shanghai) Co., Ltd.
No. 650 Qingda Road
Heqing Industrial Zone
Shanghai (Pudong) 20 12 01
Phone +86 (0) 21/5897-3302
Fax +86 (0) 21/5897-2399
mscsh@marquardt.com.cn
Sales, Development and Production

>>> TUNISIA

S.A.E.E. S.A.R.L.
104 Avenue de l'U.M.A.
2036 La Soukra, Tunis
Phone +216 (0) 71/865-265
Fax +216 (0) 71/865-420
saee.marquardt@marquardt-tn.com
Production

>>> INDIA

Marquardt India Pvt. Ltd.
21, Govt. Industrial Estate
Kandivali (West) – Mumbai 400 067
Phone +91 (0) 22/28684519
Fax +91 (0) 22/28688510
sales@marquardtindia.com
Sales, Development and Production